



# ASUS Chromebook Plus Enterprise CX34 | CX3402

## Every experience, stepped up

ASUS Chromebook Plus Enterprise CX34 is powerful, portable and primed to push productivity further by offering double the speed, double the memory, and double the storage. With a stylish, eco-conscious, lightweight and durable design, it's the perfect choice for today's busy and energetic professionals. Packed with features that empower you to achieve more, from its 180° lay-flat hinge to fast and stable WiFi 6, ASUS Chromebook Plus Enterprise CX34 is expertly engineered to elevate every experience.



Up to Intel® Core™ i7 processor



Light weight



All-day long battery life



ASUS Antimicrobial Guard



US military grade durability



chromebook plus

### Portable productivity

- Compact and light design weighing 1.44 kg
- Up to 12th Gen. Intel® Core™ i7 processor
- Up to 16GB LPDDR5-4800MHz dual channel memory
- Up to 10hrs of all-day<sup>1</sup> battery life
- Intuitive and efficient control with touchscreen and extra-large 5.7" touchpad
- Fast Connection with Wi-Fi 6 technology
- Equipped with 128GB/256GB UFS or 512GB M.2 PCIe 4.0 SSD

### Immersive and reliability

- 14" inch 1920x1080 FHD display for immersive experience
- Level-up video experiences with FHD webcam
- Webcam shield to protect personal privacy
- ASUS<sup>2</sup> Antimicrobial Guard
- Military grade reliability (MIL-STD 810H Grade)

### Friendly flexibility

- 180-degree lay-flat hinge to meet every needs
- Full size backlit keyboard with 1.4 mm key travel offers an exceptional typing comfort
- Ultimate flexibility and connectivity provided by friendly full I/O ports in 14" body
- Advanced photo & video editing with tools like magic eraser to easily remove objects from picture
- Offline access to Google Drive files and Google Photos

<sup>1</sup> Battery life may vary based on device and upon usage and other conditions.

<sup>2</sup> The keyboard, touchpad and palm rest are protected with ASUS Antibacterial Guard.

## Warranty and Support



**3-Year global warranty** \*May vary by country  
100% free of charge, with no hidden costs.



**Pick Up & Return service**  
Enjoy a door-to-door service including pick up, repair, and return.



**Warranty extension**  
Extend service coverage to match the expected length of use time.

# SPECIFICATION



Model	CX3402CBA
Operating System	ChromeOS/ChromeOS with Chrome Enterprise Upgrade
CPU	Intel® Core™ i7-1255U processor 1.2 GHz (12MB cache, up to 4.6 GHz, 10 cores) Intel® Core™ i5-1235U processor 1.2 GHz (12MB cache, up to 4.2 GHz, 10 cores) Intel® Core™ i3-1215U processor 1.0 GHz (12MB cache, up to 4.2 GHz, 6 cores)
GPU	Intel® Iris® Xe graphics (Intel Core i7, Intel Core i5) Intel® UHD graphics (Intel Core i3)
Memory	Up to 16 GB LPDDR5 4800 MHz Onboard: 8 GB/16 GB LPDDR5 4800 MHz
Storage	128GB/256GB UFS or 512GB M.2 PCIe 4.0 SSD
Display	14.0" FHD (1920 x 1080) Value-IPS AG, NTSC45%, 250nits, Non-touch 14.0" FHD (1920 x 1080) Value-IPS AG, NTSC45%, 250nits, Touch
I/O Port	2 x USB 3.2 Gen 1 Type-C (Full function) 2 x USB 3.2 Gen 1 Type-A 1 x HDMI 1.4 1 x 3.5 mm audio combo jack
Video Camera	1080p FHD camera, Webcam Shield
Wireless	WiFi 6 (802.11ax) + Bluetooth® 5.2
Audio	2 x speaker 2 x multi-array microphone Google Assistant voice-recognition support
Weight	1.44 kg
Dimensions (WxDxH)	32.64 x 21.44 x 1.87 cm
Battery	50 Wh, 3-cell, Li-Polymer
Security	Titan C security chip, Webcam Shield
Keyboard	backlit keyboard*(optional) 1.5 mm key travel ; spill-resistant to 60cc* *Quantity used during testing, with duration of 3 minutes
NumberPad	Not available
Manageability	Google Admin console (sold separately)
AC adapter	USB Type-C®, 45 W; Output: 15 V DC, 3 A; Input: 100~240 V AC 50/60 Hz universal
Certificates	TCO 9.0/FSC MIX (Recycled 100%)/Energy star

## Disclaimer :

Chromebook Enterprise Series Service Package may differ from country to country. We recommend that you check with your local dealers for the specifications of the products available in your country.

## Recommend Accessory



Wireless mouse



Chromebook Sleeve



Type A to RJ45 dongle