



Poly Rove 20 DECT Phone Handset (8F3E4AA)

Overview

We've got you covered

Keep the conversation going whenever, wherever in the office. Built for on-site employees the Poly Rove 20 wireless DECT™ IP phone solution delivers the freedom to move and the flexibility to scale as you grow.

Clarity meets function

Designed for busy professionals, Poly Rove 20 handsets emphasize usability, functionality, and style. Enjoy HD voice for lifelike conversations, customizable line keys, and effortless call parking.

You grow, we scale

You shouldn't have to worry about outgrowing your communication solution or feel held back by its options. Poly Rove 20 wireless DECT™ IP phone solution has the flexibility to scale with handsets, bases, and repeaters as you grow.

Features

Privacy is ensured

Conversations are safe and secure with DECT™ wireless security. And it doesn't stop there - maintain DECT™ encryption even when you add a base or repeater to your solution.

Extended battery life

Enable employees on the move to communicate more effectively, respond faster to requests and alerts, and be more productive with up to 35 hours of talk time (Eco-mode) and up to 300 hours of standby time.

Grab a Poly headset and go

Communicate hands-free with a Poly wired headset using the dedicated 3.5 mm connection. Perfect for users who feel more comfortable wearing a headset.
[1]

Easy-to-clean handsets

Ideal for healthcare environments, these handsets are specifically designed for easy cleaning with smooth surfaces and no gaps between buttons.

Pro-grade features

Single-cell DECT™ handset with 4-line keys and easy call park functionality. Push-to-talk for inter-handset communication. And with the 2" TFT color LCD with backlight users will see productivity soar.

HD audio quality

HD voice enables more natural conversations to enhance productivity. Voices stay in the forefront – background noise suppression lets people on both sides of the call focus on the person speaking, not their surroundings.

[1] Poly wired headset sold separately.

Additional specifications

Audio	Full-duplex handsfree speakerphone with acoustic echo cancellation and background noise suppression
Audio codecs	G.165, 168 echo cancellation
Battery life	Up to 35 hours (talk time) using Eco mode; Up to 300 hours (standby time)
Battery type	Rechargeable Li-ion
Certifications and compliances	UL 62368-1
Certified collaboration software	Zoom
Color	Black
Country of origin	Product of China
DECT frequency	1880 to 1900 MHz
Display features	Adjustable font size selection (regular, medium, large)
Display size (diagonal)	5.1 cm (2")
Display size (diagonal)	2"
Energy star certified	ENERGY STAR® certified
Headset and handset compatibility	Compliant with ADA Section 508 Subpart B 1194.23 (all)
Headset ports	1 3.5 mm headset jack
Management Software	Polycom Device Management Service for Service Providers (PDMS-SP) Cloud Management
Manufacturer Warranty	Poly standard one-year limited warranty
Minimum dimensions (W x D x H)	55.2 x 127 x 26.3 mm
Minimum dimensions (W x D x H)	2.2 x 5 x 1 in
Native resolution	128 x 160
Network protocols, supported	Manual or dynamic host configuration protocol (DHCP) network setup; Time and date synchronization using SNTP
Operating humidity range	5 to 95%
Operating temperature range	14 to 131°F
Operating temperature range	-10 to 55°C
Package dimensions (W x D x H)	180 x 92.2 x 61 mm
Package dimensions (W x D x H)	7.1 x 3.6 x 2.4 in
Package weight	0.63 lb
Package weight	287 g
Panel technology	Color TFT LCD
Power	External universal AC adapter: 5V 1A DC

Security management	DECT™ security certified
Storage temperature range	-40 to 70°C
Storage temperature range	-40 to 158°F
Telephony and call handling features	4 line keys
UNSPSC code	43191606
UPC number	(ABA) 197497473193; (ABB) 197497473186; (ABG) 197497473179; (ABJ) 197497776973; (ABU) 197497473162; (UUF) 197497473155
VoIP features	Ten (10) service provider configuration profile assignments (ITSP Profile A – J)
Weight	0.36 lb
Weight	162 g
What's in the box	Safety information sheet; Handset; Quick start guide; AC power adapter; Charging cradle; Spare battery; Base station; Ethernet cable; Belt clip
Wireless range	Up to 50 m indoor
Wireless range (imperial)	Up to 165 ft indoor

Services

Poly Services

★ : Recommended

Poly Support Services

3 Year Poly+ Rove 20 Dect IP Phone Handset	P88090312 ★
1 Year Partner Poly+ Rove 20 Dect IP Phone Handset	P88090160
1 Year Poly+ Rove 20 Dect IP Phone Handset	P88090112
3 Year Partner Poly+ Rove 20 Dect IP Phone Handset	P88090362
5 Year Next Business Day HW Replacement Rove 20 Dect IP Phone Handset Poly DaaS Service	D88090DS5

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Jan 03, 2024 8:53 AM UTC+0000