



Poly Savi 8220 Stereo DECT 1880-1900 MHz Top +Charging Cradle (8Y9C4AA)



Overview

Power through the noise

Hearing every word clearly on a call is not a nice-to-have, it is a must-have. With the Poly Savi 8200 Office series, you can tune out noise and nearby conversations with noise-canceling microphone plus close conversation limiting.

Freedom to roam

Being able to talk for a long time on a single charge means work gets done. And with the freedom to roam up to 590 ft/180 m means you can keep the calls going, even away from the desk [1].

Multi-device connectivity

Today's enterprise and contact center professionals work on a range of devices. Savi 8200 Office Series headset systems have 3-way connectivity – computer, desk phone and mobile phone – for convenient conferencing on up to two devices at once.

Features

3-way connectivity

Manage all your calls with a compatible single base that offers 3-way connectivity – computer, desk phone and mobile.

Take it further

Everyone can move, multitask, and get more done with up to 13 hours of talk time on a single charge. Convenient voice prompts notify of mute status, wireless range limit and more.

Training made easy

Make training and collaboration easy with the ability to conference up to 4 headsets onto a single base.

Crystal-clear calls

Reduce background sounds with noise-canceling microphone and close conversation limiting.

Privacy is ensured

Privacy of your conversation is ensured: DECT™ security-certified headset.

Communications platforms

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.^[2]

[1] Line of sight from computer.

[2] Visit www.poly.com/savi-8200-office for more detail.

Specifications

Audio	Noise and echo reduction
Package dimensions (W x D x H)	190 x 210 x 55 mm
Package weight	300 g
Battery life	Up to 50 days (standby time); Up to 13 hours (talk time)
UPC number	(ABB) 197498537689; (UUF) 197498537696
Manufacturer Warranty	Poly standard two-year limited warranty
What's in the box	Headset (top only)

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Battery type	Rechargeable Li-ion
Button user controls	Power on/off; Call answer/end; Mute; Volume +/-; ANC on/off
Cartons per layer	6
Cartons per pallet	36
Certified collaboration software	Zoom
Charge time	3 hours
Color	Black
Connection type	DECT™
Country of origin	Made in Mexico
Ear cushions	Artificial leather (surface material)
Headphone type	On-ear (monoaural)
Impedance	32 ohms
Indicator light	On call
Management Software	Plantronics Hub (desktop)
Microphone bandwidth	35 Hz to 21 kHz
Microphone type	Omnidirectional
Multiple order quantity	12
Package dimensions (W x D x H)	7.48 x 8.26 x 2.16 in
Package weight	0.66 lb
Paired devices	Up to 2
Pallet (layers)	6
Pallet dimensions	40 x 48 59.84 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 152 cm
Pallet weight	357 kg
Pallet weight	787.05 lb
Products per pallet	432
Products per pallet layer	72
Sensitivity (microphone)	-40 +/-3 dB
Signal-to-noise ratio	>53 dB
Speaker bandwidth	20 Hz to 20 kHz (media mode)
Speaker size	32 mm
Supported bluetooth profiles	A2DP; AVRCP; HFP; HSP

UNSPSC code	43191638
Voice alerts	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low
Wireless range	Up to 180 m in open area; Up to 55 m in typical office environment
Wireless range (imperial)	Up to 590 ft in open area; Up to 180 ft in typical office environment

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Oct 15, 2024 10:47 AM UTC+0000