



SPECIFICATIONS

Panel Size	27" (69 cm)
Active Display Area (mm)	596.16(H) x 335.34(V)
Curvature	Flat
Panel Type	Rapid IPS
Panel Resolution	3840x2160 (UHD)
Pixel Pitch (H x V)	0.15525(H) x 0.15525(V)
Aspect Ratio	16:9
Brightness (nits)	400 (Typ.)
Contrast Ratio	1000:1 (Typ.)
DCR	100000000:1
Signal Frequency	180~352KHz(H) / 48~160Hz(V)
ACTIVATED RANGE	48~160Hz
Refresh Rate	160Hz
Response time	0.5ms (GtG, Min.)
DYNAMIC REFRESH RATE TECHNOLOGY	AMD FreeSync™ Premium
HDR Support	VESA DisplayHDR 400
Video ports	1 x DisplayPort (1.4a) 2 x HDMI™ (2.1) 1 x Type-C (DP alt.) w/ PD 65W
USB ports	2 x USB 2.0 Type-A 1 x USB 2.0 Type-B
Audio ports	1 x Headphone-out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	99% / 98% / 145%
Surface Treatment	Anti-Glare
Display Colors	1.07B, 10 bits (8 bits + FRC)
Power Type	External Adaptor, 19V / 6.32A
Power Input	100~240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	-30° ~ 30°
Adjustment (Pivot)	-90° ~ 90°
Adjustment (Height)	0 ~ 110 mm
Kensington Lock	Yes
Dimension (W x D x H)	613.5 x 227.8 x 406.6 mm 613.5 x 69.8 x 362.5 mm (without stand)
Carton Dimension (W X D X H)	WW carton: 847 x 145 x 491 mm Outer: 862 x 158 x 515 mm

FEATURES



Quantum Dot

Provide accurate color imagery and support a cinema-standard DCI-P3 color gamut.



Rapid IPS

Make sure the intensity and purity of colors when gaming.



Ultimate 4K gaming

Enjoy the extreme fluid gaming and astonishing details with 4K (3840 x 2160) resolution at 160Hz high refresh rate.



Adjustable Stand

Maximize your productivity and comfort with the adjustable stand.



Type-C 65W PD

Built-in a USB Type-C connection with 65W power delivery allows you to effortlessly connect to and charge your devices.



VESA Certified DisplayHDR 400



Provide eye-catching detail through contrast and shadows adjustment.

Frameless Design	Yes
PIP / PBP Function	Yes
VESA Mounting	75 x 75 mm
Weight (NW / GW)	6.4/9.3 kg
Note	Display Port: 3840 x 2160 (Up to 160Hz) HDMI™ 2.1: 3840 x 2160 (Up to 160Hz) Type C: 3840 x 2160 (Up to 160Hz) *Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

CONNECTIONS



1. 5-way Joystick Navigator
2. DC-in
3. USB 2.0 Type-B
4. 2 x USB 2.0 Type-A
5. 2 x HDMI™ (2.1)
6. DisplayPort (1.4a)
7. Type-C (DP alt.) w/ PD 65W
8. Headphone Out