



## SPECIFICATIONS

<b>Panel Size</b>	27" (69 cm)
<b>Active Display Area (mm)</b>	596.736(H) x 335.664(V)
<b>Curvature</b>	Flat
<b>Panel Type</b>	Rapid IPS
<b>Panel Resolution</b>	2560 x 1440 (WQHD)
<b>Pixel Pitch (H x V)</b>	0.2331(H)x0.2331(V)
<b>Aspect Ratio</b>	16:9
<b>Brightness (nits)</b>	300 (Typ.)
<b>Contrast Ratio</b>	1200:1
<b>DCR</b>	100000000:1
<b>Signal Frequency</b>	64.56~266.4KHz(H) / 48~180Hz(V)
<b>ACTIVATED RANGE</b>	48~180Hz
<b>Refresh Rate</b>	180Hz
<b>Response time</b>	1ms (GtG)
<b>DYNAMIC REFRESH RATE TECHNOLOGY</b>	Adaptive-Sync
<b>HDR Support</b>	HDR Ready
<b>Video ports</b>	1 x DisplayPort (1.4) 2 x HDMI™ (2.0b)
<b>USB ports</b>	N/A
<b>Audio ports</b>	1x Headphone out
<b>Viewing Angle</b>	178° (H) / 178° (V)
<b>Adobe RGB / DCI-P3 / sRGB</b>	90% / 94% / 125%
<b>Surface Treatment</b>	Anti-glare
<b>Display Colors</b>	1.07B (8 bits + FRC)
<b>Power Type</b>	External Adaptor
<b>Power Input</b>	100~240V, 50/60Hz
<b>Adjustment (Tilt)</b>	-5° ~ 20°
<b>Adjustment (Swivel)</b>	-30° ~ 30°
<b>Adjustment (Pivot)</b>	-90° ~ 90°
<b>Adjustment (Height)</b>	0 ~ 130 mm
<b>Kensington Lock</b>	Yes
<b>Dimension (W x D x H)</b>	613 x 228 x 539 mm 613 x 61 x 369 mm (without Stand)
<b>Carton Dimension (W X D X H)</b>	WW: 840 x 150 x 475 mm Outer: 858 x 165 x 500 mm
<b>Frameless Design</b>	Yes
<b>PIP / PBP Function</b>	N/A

## FEATURES



### Rapid IPS

Make sure the intensity and purity of colors when gaming.



### 180Hz High Refresh Rate

Experience smooth gaming with a blazing fast 180Hz refresh rate, that gives you the upperhand in fast moving games.




### 1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



### Console Mode

Perfectly support 120Hz at FHD/WQHD resolution with next-gen console like PS5 and Xbox series X/S.



### Adjustable Stand

Through adjustments of tilting, lowering and raising, and swiveling, easily change the position of the monitor for maximum ergonomics and optimum viewing experiences.



### Wide Color Gamut

Game colors and details will look more realistic and refined, to push game immersion to its limits.



### HDR Ready

MSI gaming monitor is equipped with HDR technology that can produce images with more details, wider range of colors. Windows 11 Auto HDR supported

<b>VESA Mounting</b>	100 x 100 mm
<b>Weight (NW / GW)</b>	6.3 / 8.4kg
<b>Note</b>	Display Port: 2560 x 1440 (Up to 180Hz) HDMI 2.0b: 2560 x 1440 (Up to 144Hz) Adobe RGB, DCI-P3 and sRGB and Rec.2020 follow CIE1976 Standard

## CONNECTIONS



1. 5-way joystick navigator
2. DC-in
3. 1 x Display Port (1.4)
4. 2 x HDMI™ (2.0b)
5. Headphone out
6. Kensington lock