



Prestige 14 H

PRESTIGE 14 H B12UCX-629US

Specification

Manufacturer Part #	PRE14H12629
OS	Windows 11 Pro
CPU	Intel® Core™ i5-12500H
CPU Speed	1.8 - 4.5GHz
Chipset	-
Color	Urban Silver
Screen Size	14" FHD+ sRGB100% 60hz 400nits 1W Panel
Resolution	(1920x1200) 16:10
GPU	NVIDIA® GeForce RTX™ 2050 Laptop GPU
Video Memory	4G GDDR6
Keyboard	White backlight keyboard
Speaker	2x Speakers 2W
Memory	16GB LPDDR5-4800MHz
HDD Capacity	512GB NVMe SSD
HDD Interface	NVMe
TPM	TPM 2.0
LAN	-
WLAN	Killer WiFi 6E AX1675 (2x2)
Bluetooth	BT 5.2
Card Reader	Micro SD
Webcam	IR FHD Type [30fps/1080p]
USB	1x USB 3.2 Gen2 (Type-A)
Type-C Port	2x Thunderbolt™ 4 [Support Power delivery, DP 1.4a, USB 4.0]
Video Port	HDMI 2.1 (4K @ 60Hz)
Audio Port	Mic-in/Headphone-out Combo
AC Power Adaptor	100W [USB-C]
Battery Pack	4 cell (72Whr) Li-Polymer
Dimension	12.36" x 8.96" x 0.70"
Weight	3.53 lbs
Manufacturer Warranty	3 year Limited warranty (Include 1 Year Global)