



L A P T O P S

Pulse 15

PULSE 15 B13VFK-2047US

Specification

Manufacturer Part #	PULSE15132047
OS	Windows 11 Pro
CPU	Intel® Core™ i7-13700H
CPU Speed	3.7-5.0 GHz
Chipset	-
Color	Black
Screen Size	15.6" FHD IPS-Level Panel 144Hz 45% NTSC
Resolution	(1920x1080) 16:9
GPU	NVIDIA® GeForce RTX™ 4060 Laptop GPU
Video Memory	8G GDDR6
Keyboard	4 zone RGB keyboard with Anti-Ghost key (99 Key)
Speaker	2x Speakers 2W
Memory	16GB (8GB*2) DDR5 5200MHz
HDD Capacity	1TB NVMe SSD Gen4x4
HDD Interface	NVMe
TPM	Intel ® PTT
LAN	Gb LAN
WLAN	Intel Wi-Fi 6 AX201(2*2 ax)
Bluetooth	BT 5.2
Card Reader	-
Webcam	720p HD Webcam
USB	2x USB 3.2 Gen1 1x USB 2.0
Type-C Port	1x USB 3.2 Gen1 w/DP 1.4
Video Port	v 2.1 8K@60Hz 4K@120Hz
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	240W
Battery Pack	4 cell , 90Whr Li-Polymer
Dimension	14.13"x 10.20"x 1.06"
Weight	5.07 lbs
Manufacturer Warranty	3 year Limited warranty (Include 1 Year Global)