

ThinkPad P14s Gen 5 (Intel) 21G20026US

Lenovo

PSREF
Product Specifications
Reference

PERFORMANCE

Processor

Intel® Core™ Ultra 7 165H, 16C (6P + 8E + 2LPE) / 22T, Max Turbo up to 5.0GHz, 24MB

AI PC Category

AI-Ready Workstations

NPU

Integrated Intel® AI Boost, up to 11 TOPS

Graphics

NVIDIA® RTX 500 Ada Generation 4GB GDDR6

Chipset

Intel® SoC Platform

Memory

2x 16GB SO-DIMM DDR5-5600 Non-ECC

Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

Max Memory^[1]

Up to 96GB (2x 48GB DDR5 SO-DIMM)

Storage

1TB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal 2.0

Storage Support^[2]

One drive, up to 2TB M.2 2280 SSD

Storage Slot

One M.2 2280 PCIe® 4.0 x4 slot

Card Reader

No card reader

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby Audio™

Camera

5.0MP + IR with Privacy Shutter and Human Presence Detection

Microphone

2x, Array

Battery

Integrated 75Wh

Power Adapter

135W USB-C® Slim (3-pin)

DESIGN

Display

14.5" WUXGA (1920x1200) IPS 300nits Anti-glare, 45% NTSC, 60Hz, Eyesafe®, TÜV Low Blue Light

Keyboard

Backlit, English

Case Color

Black

Case Material

Aluminium (Top), Aluminium (Bottom)

Pen

Pen Not Supported

Dimensions (WxDxH)^[3]

325.5 x 227.6 x 18.5 mm (12.81 x 8.96 x 0.73 inches)

Weight^[4]

Starting at 1.61 kg (3.55 lbs)

SOFTWARE

Operating System^[5]

Windows® 11 Pro, English

Bundled Software

Intel® Connectivity Performance Suite

CONNECTIVITY

Ethernet

100/1000M (RJ-45)

WLAN + Bluetooth^[6]

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3

WWAN

Non-WWAN

Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)
- 1x Security keyhole

Docking

Various docking solutions supported via Thunderbolt™ or USB-C®.

For more compatible docking solutions, please visit .

[Docking for ThinkPad® P14s Gen 5 \(Intel®\)](#)

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0 Enabled

Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Other Security

- IR camera for Windows® Hello (facial recognition)
- Ultrasonic Human Presence Detection for IR camera
- Camera privacy shutter
- Bottom cover tamper detection

MANAGEABILITY

System Management

Intel® vPro® Enterprise

SERVICE

Base Warranty

3-year, Courier or Carry-in

Included Upgrade

3Y Premier Support Upgrade from 3Y Courier/Carry-in

CERTIFICATIONS

Green Certifications^[7]

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- RoHS compliant
- TCO Certified 10.0

Other Certifications

- Eyesafe® Certified 2.0
- TÜV Rheinland® Low Blue Light

Mil-Spec Test

MIL-STD-810H military test passed

ISV Certifications

Please visit [ISV certifications for Lenovo® Workstations](#)

MODEL

TopSeller	: Yes	Announce Date	: 2024-05-21
EAN / UPC / JAN	: 198153472895	End of Support	: 2030-12-28



Product image is a sample, it may not match the real color of this model

Note:

^[1] 48GB memory module will be available in June 2024.....

· Lenovo reserves the right to change specifications without notice.

· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at

the time of sale of the product. For more information, go to:
<https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to
<https://psref.lenovo.com/Detail/2494?M=21G20026US>

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkPad Universal USB-C Dock

40AY0090US

THE SMARTER WAY TO WORK Introducing the ThinkPad Universal USB-C Dock. This advanced, universally compatible one-cable docking solution lets you work smarter, not harder. It comes with a vast array of ports, next-gen ...

Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Premier Support (5WS1M86981)
BETTER	3Y Premier Support Plus upgrade from 3Y Premier Support (5WS1L39490)
GOOD	4Y Premier Support upgrade from 3Y Premier Support (5WS1H31743)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference