



AOPEN

an Acer Group Company

CHROMEBOX COMMERCIAL 3



AOPEN Chromebox Commercial 3

Powerful, Commercial Grade ChromeOS Device, that drives up to 4 x 4k screens


Introducing the Chromebox Commercial 3 – a purpose-built Chrome solution designed to excel in enterprise, retail, digital signage, manufacturing, and challenging operating conditions where traditional consumer-grade Mini PCs fall short. It is meticulously engineered with a ruggedized design, constructed from resilient aluminum and SECC metal, ensuring durability and reliability even in demanding environments. Its fanless design guarantees consistent performance in continuous 24/7 use-case scenarios.

The Chromebox offers impressive 4K UHD video support and is adaptable to a wide range of applications, including kiosks and vending machines. It's backed by a commercial 3-year warranty, with the option to extend it to 5 years, providing you with a trusted and dependable technology solution tailored precisely to your unique needs.

The advantages of the Chromebox Commercial 3:

- Aluminum and SECC metal construction for durability.
- Solid-state and Fanless design, ideal for non-stop, 24/7 operation
- Runs up to 4* UHD (4k) display @60Hz in commercial environments (requires optional expansion port)
- Small form factor for easy installment behind displays or integration in kiosks
- 3 year warranty, extendable to 5 years for peace of mind
- Design to operate in a wide environmental temperature range of 0°C~50°C
- AC Power Auto Recovery (APAR) for always-on functionality

 chrome enterprise  Google for Education



Chromebox Commercial 3

OS		Chrome OS				
Dimension	W x H x D (mm)	200 x 38 x 186.2 mm (1.42L)		Front Panel I/O	USB 2.0 Port	-
	W x H x D (inch)	7.87 x 1.49 x 7.33 inch (1.42L)			USB 3.2 Port	3.2 Gen 2 X2 (BC1.2 charging, 5V/1.5A)
Weight	Net Weight	1.64 kgs / 3.62 lbs			USB Type-C	X1 (USB4 Gen 3 Data transfer/Power Delivery 15W/DisplayPort)
	Gross Weight	2.63 kgs / 5.79 lbs			Others	Audio Jack x1, Power Button x1, External Power Switch x1
CPU	Type	Intel® Celeron 7305 Processor, Core I3-1215U		Rear Panel I/O	DC Jack	X1
Memory	Channels	Dual Channel			HDMI 2.1 Port	X2
	Type	DDR4 SO-DIMM x2			USB2.0 Port	-
	Data Rate	3200 MHz			USB 3.2 Port	Gen 2 x 2
	Max Memory	4G/8G (4Gx2)			USB Type-C	x1 (USB4 Gen 3 Data transfer /Power Delivery 15W/DisplayPort)
Graphics		Intel® Iris Xe Graphics, integrated on CPU			RJ45 LAN Jack	X1
Audio		3.5 Audio Jack X1 (Combo)			Antenna Holes	X2
LAN		Giga Lan x 1, 10/100/1000Mbps			Kensington Lock Hole	X1
Wireless		WiFi 6E 802.11 b/g/n/ac/ax + BT5.2			Recovery Button	X1
Storage Bay	2.5" SATA HDD	-			Others	Configurable Port: HDMI2.1 / DP1.4a (Optional)
	M.2 SSD	EMMC 64G/128G		Power Supply	DC Adapter 19V/90W	
				Input Voltage	AC 100 ~ 240V	
Environment						
				MTBF	50,000 hrs	
				Operating Temperature	0°C ~ 50°C (32°F ~ 122°F)	
				Storage Temperature	-20°C ~ 60°C (-7°F ~ 140°F)	
				Relative Humidity	95% RH max	



*Please note that product specifications are subject to change without notice

