



L A P T O P S

Raider GE78 HX

RAIDER GE78 HX 14VGG-254US

Specification

Manufacturer Part #	RAIDERGE7814254
OS	Windows 11 Pro
CPU	Intel® Core™ i7-14700HX
CPU Speed	1.5-5.5 GHz
Chipset	-
Color	Black
Screen Size	17" 16:10 QHD+(2560 x 1600) 240Hz 100% DCI-P3 IPS-Level Panel
Resolution	(2560x1600) 16:10
GPU	NVIDIA® GeForce RTX™ 4070 Laptop GPU
Video Memory	8G GDDR6
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (99 Key)
Speaker	Dynaudio Speakers 2W*2 + 2W*4 woofer
Memory	16GB (8GB*2) DDR5
HDD Capacity	1TB NVMe SSD + 512GB NVMe SSD Gen4x4
HDD Interface	NVMe
TPM	Intel ® PTT
LAN	Killer E3100G
WLAN	Killer WiFi 7 BE1750
Bluetooth	BT 5.4
Card Reader	SD7.0
Webcam	IR FHD w/shutter
USB	1x USB 3.2 Gen 2 1x USB 3.2 Gen 1
Type-C Port	1x Thunderbolt™ 4; 1x USB 3.2 Gen 2/DP; 1x USB 3.2 Gen 2/DP&PD
Video Port	v2.1,
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	280W
Battery Pack	4 cell (99.9Whr) Li-Ion
Dimension	14.97"x 11.73"x 1.13"
Weight	6.61 lbs
Manufacturer Warranty	3 year on site warranty+ADP