



SPECIFICATIONS

Panel Size	24.5" (62.2cm)
Active Display Area (mm)	543.744(H) x 302.616(V)
Curvature	Flat
Panel Type	Rapid IPS
Panel Resolution	1920 x 1080 (FHD)
Pixel Pitch (H x V)	0.2832(H) x 0.2802(V)
Aspect Ratio	16:9
Brightness (nits)	250 Nits (Typ.)
Contrast Ratio	1000:1
DCR	100000000:1
Signal Frequency	78.4~210.58KHz (H) / 48~180Hz (V)
ACTIVATED RANGE	48~180Hz
Refresh Rate	180Hz
Response time	1ms (GtG)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
HDR Support	Yes
Video ports	1 x DisplayPort (1.2a) 2 x HDMI™ (2.0)
USB ports	N/A
Audio ports	1 x Headphone Out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	91% / 96% / 127%
Surface Treatment	Anti-glare
Display Colors	1.07B, 10 bits (8 bits + FRC)
Power Type	External Adaptor
Power Input	100 ~ 240V
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	N/A
Adjustment (Pivot)	N/A
Adjustment (Height)	N/A
Kensington Lock	Yes
Dimension (W x D x H)	560 x 421.4 x 220.1 mm
Carton Dimension (W X D X H)	642 x 162 x 407 mm 657 x 177 x 429 mm(outer box)
Frameless Design	Yes
PIP / PBP Function	N/A
VESA Mounting	75 x 75 mm

FEATURES



Rapid IPS

Make sure the intensity and purity of colors when gaming.



180Hz High Refresh Rate

Experience smooth gaming with a blazing fast 180Hz refresh rate, that gives you the upperhand in fast moving games.



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



Console Mode

Perfectly support 120Hz at QHD 2K resolution with next-gen console like PS5 and Xbox series X/S.



Frameless Design

With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.



Night Vision

Smart black tuner to brighten your day by bringing out the fine details in dark areas.



HDR Ready

Provide eye-catching detail through contrast and shadows adjustment.

Weight (NW / GW)	3.25 kg / 5.662 kg
Note	DisplayPort: 1920 x 1080 (Up to 180Hz) HDMI™: 1920 x 1080 (Up to 180z) *Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

CONNECTIONS



1. 5-Way Joystick Navigator
2. 2 x HDMI™ (2.0)
3. DisplayPort (1.2a)
4. Earphone out
5. DC-in
6. Kensington Lock