



---

# Lexmark CX963xse

Versatile. Simple. Sustainable.

---



## Lexmark CX963xse

With the new CX963xse color A3 multifunction printer, you get reassuring versatility, exceptional sustainability, and surprising simplicity from such sophisticated technology. Boost your productivity with vivid prints — up to 55 pages per minute\*. Intuitively navigate the 10-inch (25 cm) color touchscreen, and save time with single-pass two-sided scanning. Effortlessly create everything your business requires, and custom configure your multifunction printer with interchangeable options tailored to your needs.

### Versatile: Easy to Use

**Create everything your business requires and anything you can imagine** — from standard office documents to marketing brochures, booklets and posters — with broad media size support, high-volume printing, and exceptional paper handling and finishing capabilities.

**Print vivid, colorful visualizations, charts and documents** with professional color features (including PANTONE® calibration) and a full range of media sizes so you can effectively communicate your ideas.

**Easily incorporate your multifunction printer into your workspace** with a versatile, configurable design that saves space without sacrificing performance.

**Boost your productivity** with our rich suite of cutting-edge software and solutions with broad capabilities including scanning paper files directly into your cloud-based storage systems and automatically translating documents into 100+ languages.

**Further your organization's digital transformation** with direct integration into your critical workflows and core business systems using these IoT-enabled devices.



### Simple: Easy to Manage

**Quickly do what you need to do** using an intuitive operator panel and easy-to-follow navigation.

**Easily maintain your devices** with one-handed toner replacement, easy-to-reach serviceable areas, and alerts that are simple to understand.

**Enjoy the peace of mind of knowing you are protected** by the industry's most comprehensive security portfolio, right out of the box.

**Keep your business running** with exceptional reliability, industry-leading durability, and long-lasting toner and supplies.

**Rest easy that every aspect of your device is made to work together seamlessly** thanks to Lexmark's core technology ownership.

### Sustainable: Easy to feel good about

**Feel good about your purchase and help meet your own sustainability goals** with our world-class practices and independent third-party certifications.

**Do your part for the planet** with our industry-leading use of post-consumer recycled materials and our award-winning cartridge recycling program.

**Save energy — and money** — with technology that exceeds strict global standards for energy efficiency.

**Minimize your impact on the environment** with a company that focuses on sustainability throughout the product lifecycle from design through use, end of life and beyond.

This is a Class A device according to international electromagnetic emissions standards (i.e. FCC Rules, EN 55022/EN 55032, etc.). Class A products are intended for use in non-residential/non-domestic environments. Use of a Class A product in residential/domestic environments may cause interference to radio communications and require corrective measures.

\* Print speeds measured in accordance with ISO/IEC 24734 (ESAT). For more information see: [www.lexmark.com/ISOspeeds](http://www.lexmark.com/ISOspeeds).

\*\* Fax icon shown on the operator panel when Fax Server is enabled, Fax Over IP is configured, etherFAX is configured, or an optional Analog Modem is installed.

# Lexmark CX963xse



- 1 **Multifunction product with 10-inch (25 cm) touch screen**  
48.0 x 23.3 x 26.0 in.
- 2 **500-Sheet output bin**  
Dimensions included as part of base model
- 3 **150-Sheet multipurpose feeder**  
Dimensions included as part of base model
- 4 **550-Sheet tray**  
Dimensions included as part of base model
- 5 **550-Sheet tray**  
Dimensions included as part of base model
- 6 **2,000-Sheet tandem tray**  
Dimensions included as part of base model
- 7 **2 x 550-Sheet Tray**  
12.4 x 23.1 x 25.6 in.  
314 x 587 x 649 mm
- 8 **Cabinet**  
9.7 x 23.1 x 26.0 in.  
247 x 587 x 660 mm
- 9 **1500-Sheet High-Capacity Tray**  
11.4 x 13.5 x 21.4 in.  
290 x 342 x 545 mm

- 10 **Paper Transport**  
5.6 x 16.2 x 18.3 in.  
143 x 412 x 466 mm
- 11 **Folding Paper Transport**  
7.2 x 24.1 x 21.9 in.  
184 x 612 x 555 mm
- 12 **500-Sheet Staple Finisher**  
5.9 x 21.5 x 20.6 in.  
150 x 546 x 523 mm
- 13 **Offset Stacker**  
4.2 x 16.5 x 19.3 in.  
107 x 420 x 489 mm
- 14 **1250-Sheet Staple 2/3 Hole Punch Finisher**  
39.2 x 22.6 x 24.0 in.  
995 x 575 x 610 mm
- 15 **2250-Sheet Booklet Staple 2/3 Hole Punch Finisher**  
39.2 x 25.6 x 24.1 in.  
995 x 650 x 613 mm



P/N  
20L8550

**Hardware**  
Lexmark CX963xse

P/N  
20L7500  
25A0013

**Supplies**  
Staple Cartridges (4 pack)  
Lexmark 3-Pack 15K Finisher Staples  
77L0H10 Lexmark MX953, CS963, CX961, 962, 963, XC9635, 9645, 9655 Black 47.7K Toner Cartridge  
77L0H20 Lexmark CS963, CX961, 962, 963, XC9635, 9645, 9655 Cyan 46.9K Toner Cartridge  
77L0H30 Lexmark CS963, CX961, 962, 963, XC9635, 9645, 9655 Magenta 46.9K Toner Cartridge  
77L0H40 Lexmark CS963, CX961, 962, 963, XC9635, 9645, 9655 Yellow 46.9K Toner Cartridge  
77L0W00 Lexmark CS963, CX950, 951, 961, 962, 963, 833, XC9525, 9535, 9635, 9645, 9655, 8355 120K Waste Container  
77L0Z10 Lexmark MX953, CS963, CX950, 951, 961, 962, 963, 833, XC9525, 9535, 9635, 9645, 9655, 8355 Black 225K Imaging Unit  
77L0Z50 Lexmark CS963, CX950, 951, 961, 962, 963, 833, XC9525, 9535, 9635, 9645, 9655, 8355 3-Color 250K Imaging Kit  
77L0ZK0 Lexmark MX953, CS963, CX950, 951, 961, 962, 963, 833, XC9525, 9535, 9635, 9645, 9655, 8355 Black Return Program 225K Imaging Unit  
77L0ZV0 Lexmark CS963, CX950, 951, 961, 962, 963, 833, XC9525, 9535, 9635, 9645, 9655, 8355 3-Color Return Program 250K Imaging Kit  
77L10C0 Lexmark CS963, CX950, 951, 961, 962, 963, 833 Cyan Return Program 12K Toner Cartridge  
77L10K0 Lexmark MX953, CS963, CX950, 951, 961, 962, 963, 833 Black Return Program 15K Toner Cartridge  
77L10M0 Lexmark CS963, CX950, 951, 961, 962, 963, 833 Magenta Return Program 12K Toner Cartridge  
77L10Y0 Lexmark CS963, CX950, 951, 961, 962, 963, 833 Yellow Return Program 12K Toner Cartridge  
77L1HCO Lexmark CS963, CX961, 962, 963 Cyan Return Program 46.9K Toner Cartridge  
77L1HK0 Lexmark MX953, CS963, CX961, 962, 963 Black Return Program 47.7K Toner Cartridge  
77L1HMO Lexmark CS963, CX961, 962, 963 Magenta Return Program 46.9K Toner Cartridge  
77L1HY0 Lexmark CS963, CX961, 962, 963 Yellow Return Program 46.9K Toner Cartridge

P/N  
20L8800  
20L8801  
20L8802  
20L8803  
20L8804  
20L8810  
20L8811  
20L8812  
  
20L8813  
  
20L8814

**Paper Handling**  
550-Sheet Tray  
2 x 550-Sheet Tray  
2000-Sheet Tandem Tray - A4  
2000-Sheet Tandem Tray - Letter  
1500-Sheet High-Capacity Tray  
500-Sheet Staple Finisher  
Folding Paper Transport  
1250-Sheet Staple 2/3 Hole Punch Finisher  
1250-Sheet Staple 2/4 Hole Punch Finisher  
2250-Sheet Booklet Staple 2/3 Hole Punch Finisher

20L8815 2250-Sheet Booklet Staple 2/4  
Hole Punch Finisher  
20L8816 Offset Stacker  
20L8817 Paper Transport

**P/N** **Memory Options**  
27X0420 500GB Hard Disk Drive (SATA)  
57X0070 Removable Hard Disk Enclosure  
Kit

**P/N** **Application Solutions**  
57X0225 Desktop Contactless Reader  
57X0235 Contactless Front Solutions  
Module (Primary)  
57X0300 Contact Authentication Device  
57X0301 Contactless Authentication  
Device  
82S1203 IPDS License  
82S1204 Bar Code License

**P/N** **Connectivity**  
1021231 Parallel Cable (10-foot)  
1021294 USB Cable (2-meter)  
14F0100 RS-232C Serial Interface Card  
27X0142 Lexmark MarkNet™ N8230 Fiber  
Ethernet Print Server  
37X6146 Fax Card Option  
57X7040 English Keyboard Kit  
SPD0001 Surge Protective Device,  
110-120V

**P/N** **Furniture**  
20L8806 Cabinet  
20L8807 Keyboard Shelf

You can install one 1,500-Sheet high-capacity tray.

You can install one 500-Sheet staple finisher, one Offset stacker or one Folding paper transport unit.

You can install one 1,250-Sheet staple hole punch finisher or one 2,250-Sheet booklet staple hole punch finisher, but you must also install a Paper transport unit or Folding paper transport unit.

## Product Specifications

## Lexmark CX963xse

Printing	
Display	Lexmark e-Task 10.1-inch (25.6 cm) color touch screen
Print Speed	Up to: Black: 55 ppm <sup>1</sup> (Letter) / Color: 55 ppm <sup>1</sup> (Letter)
Time to First Page	As fast as: Black: 7.1 seconds / Color: 8.2 seconds
Print Resolution	Black: 1200 x 1200 dpi, 4800 Color Quality / Color: 4800 Color Quality, 1200 x 1200 dpi
Memory	Standard: 4 GB / Maximum: 4 GB
Hard Disk	Intelligent Storage Drive included; Magnetic Hard Disk available
Recommended Monthly Page Volume	7,000 - 50,000 pages <sup>2</sup>
Maximum Monthly Duty Cycle	Up to: 270 000 pages per month <sup>3</sup>
Copying	
Copy Speed	Up to: Black: 55 cpm <sup>1</sup> (Letter) / Color: 55 cpm <sup>1</sup> (Letter)
Time to First Copy	As fast as: Black: 8.5 seconds / Color: 9.5 seconds
Scanning	
Scanner Type / ADF Scan	Flatbed scanner with automatic document feeder / DADF (single pass Duplex)
A4/Ltr Duplex Scan Speed	Up to: Black: 240/240 sides per minute / Color: 240/240 sides per minute
A4/Ltr Simplex Scan Speed	Up to: Black: 120/120 sides per minute / Color: 120/120 sides per minute
ADF Paper Input Capacity	Up to: 300 pages 20 lb or 75 gsm bond
Supplies <sup>4</sup>	
Laser Cartridge Yields	up to: 46,900 <sup>5</sup> -page Color (CMY) Cartridges / up to: 47,700 <sup>5</sup> -page Black Cartridge
Imaging Unit Estimated Yield	Up to: 225,000 (black) and 250,000 (color) pages, based on 3 average letter/A4-size pages per print job and ~ 5% coverage
Cartridge(s) Shipping with Product	15,000 <sup>5</sup> -page Black Toner Cartridge <sup>5</sup> , 12,000 <sup>5</sup> -page Color (CMY) Toner Cartridges <sup>5</sup>
Paper Handling	
Included Paper Handling	500-Sheet Output Bin, 550-Sheet Tray, 2000-Sheet Tandem Tray/Caster, 550-Sheet Tray, 150-Sheet Multipurpose Feeder
Optional Paper Handling	2,250-Sheet Booklet Staple Hole Punch Finisher, 500-Sheet Staple Offset Finisher, Folding Paper Transport Unit, 1,250-Sheet Staple Hole Punch Finisher, Offset Stacker, 1,500-Sheet High-Capacity Tray, Paper Transport Unit, Cabinet, 2 x 550-Sheet Tray
Paper Input Capacity	Up to: Standard: 3250 pages 20 lb or 75 gsm bond / Maximum: 4750 pages 20 lb or 75 gsm bond
Paper Output Capacity	Up to: Standard: 500 pages 20 lb or 75 gsm bond / Maximum: 2650 pages 20 lb or 75 gsm bond
Media Types Supported	Vinyl Labels, Labels, Card Stock, Plain Paper, Envelopes, Glossy Paper, Refer to the Paper & Specialty Media Guide
Media Sizes Supported	A6, Oficio, 12 x 18", 7 3/4 Envelope, JIS-B4, 9 Envelope, JIS-B5, A3, Ledger, A4, Legal, SRA3, A5, Hagaki Card, Letter, B5 Envelope, C4 Envelope, Statement, C5 Envelope, Executive, DL Envelope, Folio, 10 Envelope
General Information	
Standard Ports	Gigabit Ethernet (10/100/1000), Front USB 2.0 Specification Hi-Speed Certified port (Type A), 802.11a/b/g/n/ac + Apple iBeacon, USB 2.0 Specification Hi-Speed Certified (Type B)
Optional Network Ports / Optional Local Ports	MarkNet N8230 Fiber Ethernet Print Server / Internal 1284-B Bidirectional Parallel, Internal RS-232C serial
Noise Level	Operating: 51 dBA (Print) / 52 dBA (Copy) / 50 dBA (Scan)
Specified Operating Environment	Altitude: 0 - 2896 Meters (9,500 Feet) / Humidity: 15 to 80% Relative Humidity / Temperature: 10 to 32.2°C (50 to 90°F)
Limited Warranty	See Statement of Limited Warranty: 1-Year Onsite Repair, Next Business Day
Size / Weight	H x W x D: 48.0 x 23.3 x 26.0 in. / 266.8 lb.
ENERGY STAR Typical Electricity Consumption	TEC: 0.82 kilowatt-hours per week

All information is subject to change without notice. Lexmark is not liable for any errors or omissions.

<sup>1</sup> Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: [www.lexmark.com/ISOspeeds](http://www.lexmark.com/ISOspeeds).

<sup>2</sup> "Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. <sup>3</sup> "Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. <sup>4</sup> Product functions only with replacement cartridges designed for use in a specific geographical region. See [www.lexmark.com/regions](http://www.lexmark.com/regions) for more details. <sup>5</sup> Average continuous black or continuous composite CMY declared cartridge yield up to this number of standard pages in accordance with ISO/IEC 19798.

This is a Class A device according to international electromagnetic emissions standards (i.e. FCC Rules, EN 55022/EN 55032, etc.). Class A products are intended for use in non-residential/non-domestic environments. Use of a Class A product in residential/domestic environments may cause interference to radio communications and require corrective measures.

© 2024 Lexmark. All rights reserved.

Lexmark, the Lexmark logo and Unison are trademarks of Lexmark International, Inc., registered in the United States and/or other countries.

Apple and AirPrint are trademarks of Apple Inc., registered in the U.S. and other countries. MOPRIA®, the Mopria® Logo™ and the Mopria® Alliance logos are registered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. ENERGY STAR and the ENERGY STAR mark are registered trademarks owned by the U.S. Environmental Protection Agency. EPEAT® is a trademark of the Green Electronics Council in the United States and other countries. All other trademarks are the property of their respective owners.

This product includes software developed by the OpenSSL Project for use in the Open SSL Toolkit (<http://www.openssl.org/>).



[lexmark.com](http://lexmark.com)

