



SPECIFICATIONS

PANEL SIZE	24.5"
PANEL RESOLUTION	1920 x 1080 (FHD)
REFRESH RATE	100Hz
RESPONSE TIME	1ms (MPRT) / 4ms (GTG)
PANEL TYPE	IPS
VIEWING ANGLE	178°(H) / 178°(V)
ASPECT RATIO	16:9
PIXEL PITCH (H X V)	0.2832(H) x 0.2802(V)
CONTRAST RATIO	1000:1
sRGB	109% (CIE 1976)
ACTIVE DISPLAY AREA (MM)	543.744(H) x 302.616(V)
SURFACE TREATMENT	Anti-glare
DISPLAY COLORS	16.7M
COLOR BIT	8 bits (6 bits + FRC)
VIDEO PORTS	1x HDMI™ 1.4b (FHD@100Hz) 1x DisplayPort (1.2a) 1x D-Sub (VGA)
AUDIO PORTS	1x Line-in
KENSINGTON LOCK	Yes
SPEAKER	2x 3W
BRIGHTNESS (NITS)	300 cd/m2
VESA MOUNTING	75 x 75 mm
POWER TYPE	External Adaptor (12V 2.5A)
POWER INPUT	100~240V, 50~60Hz
ADJUSTMENT (TILT)	-5° ~ 20°
DIMENSION (W X H X D)	560 x 438.4 x 182.0 mm (22.05 x 17.26 x 7.09 inch)
CARTON DIMENSION (W X H X D)	63.2 x 41.5 x 12.5 mm (24.9 x 16.4 x 4.9 inch)
WEIGHT (NW / GW)	3.03 kg (6.68 lbs) / 5.05 kg (11.14 lbs)
CERTIFICATES	CB/CE Energy Star
Compatibility	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.


FEATURES

- Anti-Flicker technology**
MSI Anti-Flicker technology provides a very comfortable viewing experience by reducing the amount of screen flicker.
- Less Blue Light**
Effectively reduce blue light which could cause serious long-term damage to your eyes.
- 100Hz High Refresh Rate**
Experience smooth gaming with a blazing fast 100Hz refresh rate, that gives you the upperhand in fast moving games.
- VESA Mountable**
To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.
- IPS Grade Panel**
Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best while creating your own on-line video.
- Built-In Speaker**
Built-in speakers allow you to listen clearly without connecting external speakers.
- EyesErgo**
An eye care solution designed with ergonomics in mind.
- Eye-Q Check**
Help have self-check eyes & remind to take a rest while using the monitor for a long time.
- Broadened Display**
View your applications, spreadsheets and more with a perfect screen size for work desk that aligns with the visual's comfort zone.

NOTE

HDMI™: 1920 x 1080 (Up to 100Hz)
DisplayPort: 1920 x 1080 (Up to 100Hz)
D-Sub (VGA): 1920 x 1080 (Up to 60Hz)
Adaptive Sync Support

CONNECTIONS



1. 1x DisplayPort (1.2a)
2. 1x HDMI™ 1.4b (FHD@100Hz)
3. 1x D-Sub (VGA)
4. 1x Line-in
5. 1x DC-in
6. 1x 5-way Navigator
7. 1x Kensington Lock