




SPECIFICATIONS

| | |
|-------------------------------|---|
| CPU | Intel® Core™ 7 processor 150U (12M Cache, 1.80 GHz up to 5.40 GHz) Intel® Core™ 5 processor 120U (12M Cache, 1.40 GHz up to 5.00 GHz) Intel® Core™ 3 processor 100U (10M Cache, 1.20 GHz up to 4.70 GHz) |
| OS | Windows 11 Home Windows 11 Pro - MSI recommends Windows 11 Pro for business |
| Chipset | Intel® SoC |
| Storage | 1x M.2 SSD (PCIe/SATA auto-switch) 1x 2.5" HDD / SSD |
| Graphics | Intel® UHD Graphics / Intel® Iris® Xe Graphics (Core™ 5 processor above with dual-channel memory) |
| Memory | 2x DDR5 5200MHz SO-DIMMs, up to 64GB |
| Panel Resolution | 23.8" IPS Grade Panel LED Backlight (1920*1080 FHD) with MSI Anti-Flicker technology |
| Touch Panel | In-cell 10-point Touch (Non touch for Modern AM242P 1M) |
| I/O | Side: 2x USB 3.2 Gen 2 Type C 2x USB 3.2 Gen 2 Type A 1x Mic-in /Headphone-out combo Rear: 1x HDMI™ -in 1x HDMI™ -out (supports 4K @60Hz as specified in HDMI™ 2.1) 2x USB 2.0 Type A 1x RJ45 LAN 1x Kensington Lock |
| Audio | 2x 2.5W |
| LAN | Realtek RTL8111H |
| Wireless LAN | Intel Wi-Fi 6E AX211 |
| Bluetooth | 5.3 (with Intel AX211) |
| Webcam | Built-in FHD Webcam which supports Windows Hello Removable webcam cover design |
| 5-WAY NAVIGATOR | Yes |
| Keyboard / Mouse | Optional |
| AC Adapter | 120W |
| AIO Wall Mount Kit III | 75 x 75 mm |
| Adjustment (Tilt) | -4° ~ 20°± 2° |
| Adjustment (Height) | 0 ~ 130 mm |

FEATURES

- 23.8" Full HD 1080P**
View your applications, spreadsheets and more with a perfect 23.8 inches screen and experience a breathtaking screen that comes with Full HD resolution
- Anti-Flicker technology**
MSI Anti-Flicker technology provides a very comfortable viewing experience by reducing the amount of screen flicker.
- Less Blue Light**
Effectively reduce blue light which could cause serious long-term damage to your eyes.
- Adjustable Stand**
Adjust the stand to the angle that is most suitable for you to keep yourself work comfortably.
- DDR5 Memory**
Elevate system performance with dual-channel DDR5 technology to enhance efficiency and stability for users.
- Instant Display**
When devices are connected to the HDMI™-in port, the monitor will be turn on immediately without booting up the system.
- USB 3.2 Gen 2 Type C & Type A**
Get all the performance benefits from USB 3.2 combined with the convenience of the reversible USB Type-C connector and universal Type-A.
- MSI Cloud Center**
MSI Cloud Center app brings you a private cloud and helps backup files of your mobile devices (Android & iOS)
- Tobii Aware Privacy Enhancement**
Tobii Aware supports the privacy screen and peeker detection technology to ensure a safer environment.
- VESA Mountable**
To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.
- Easy to upgrade**
Easy to access and upgrade components to keep the system up to date with the latest hardware.

CONNECTIONS



| | | | |
|---------------------------|--|--|-------------------------------|
| MANAGEMENT UTILITY | MSI Cloud Center: Backup all of the photos and videos of the mobile devices (Android & iOS) MSI Center: MSI AI Engine, Hardware Monitoring, Free Up Memory, Clean Up Disk, MSI Recovery, F3 Recovery, Devices Speed Up, Smart Priority, Smart Image Finder, Noise Cancellation, Live Update, Microsoft App Update, System Info, Troubleshooting, Contact Us, MSI Forum & Channel MSI Display Kit: Split Window, Display Setting (Orientation, resolution, refresh rate, size of text and app), Display Color Setting (Customizable Link App: Eye Saver Mode, Personal setting, Standard, Gaming, FPS, RTS/RPG, Cinema), Connect to wireless display, On-screen keyboard, Mouse Sensitivity, Power setting, Magnifier (Zoom in / Zoom out), Project way setting (internal/ Clone/ Extend/ External) | @60Hz as specified in HDMI™ 2.1) 11. 1x RJ45 LAN | 12. 1x Removable Webcam Cover |
| | SECURITY UTILITY & DEVICE | MSI Center: System Diagnosis Tobii Aware: Security and Privacy: Privacy Screen/ Auto Lock/ Peeker Detection Dim Screen: Energy saving Windows Snap dTPM 2.0 Support | |
| Net Weight | 6.16 kg (13.58 lbs) | | |
| Gross Weight | 8.45 kg (18.63 lbs) | | |
| Certificates | FCC, CB/CE, UL & CUL, VCCI, RCM, ENERGY STAR | | |
| DIMENSION (WxDxH) | 541.40 x 194.68 x 534.92 mm (21.31 x 7.66 x 21.06 inch) | | |