



BUSINESS & PRODUCTIVITY

Modern 15 H AI

MODERN 15 H AI C1MG-060US

Specification

Manufacturer Part #	MOD15H14060
OS	Windows 11 Pro
CPU	Intel® Core™ Ultra 9 - 185H
CPU Speed	2.3 - 5.1 GHz
Chipset	-
Color	Classic Black
Screen Size	15.6" FHD 60Hz 45% NTSC IPS-Level
Resolution	(1920x1080) 16:9
GPU	Intel® Arc Graphics
Video Memory	-
Keyboard	White backlight keyboard (99 Key)
Speaker	2x Speakers 2W
Memory	64GB (32GB*2) DDR5 5600MHz
HDD Capacity	1TB NVMe SSD
HDD Interface	NVMe
TPM	-
LAN	-
WLAN	Intel WiFi 6E AX211 (2x2)
Bluetooth	BT 5.3
Card Reader	Micro SD
Webcam	720p HD Webcam
USB	3x USB 3.2 Gen 1
Type-C Port	1x USB 3.2 Gen 2 Type C
Video Port	HDMI 2.1 (4K @ 60Hz)
Audio Port	Mic-in/Headphone-out Combo
AC Power Adaptor	90W [DC-in]
Battery Pack	3 cell (53Whr) Li-Polymer
Dimension	14.13" x 9.49" x 0.78"
Weight	4.19 lbs
Manufacturer Warranty	3 year Limited warranty (Include 1 Year Global)