




# HP Z24u G3 WUXGA USB-C Display (1C4Z6AA)



## Overview

### Exquisitely crafted for every detail

Meticulously crafted to surpass every design standard, the HP Z24u G3 WUXGA USB-C Display is composed of authentic aluminum and delivers an impressive, frameless viewing experience. Bring your ideas to life with remarkable color accuracy in precise WUXGA resolution. Refine your work experience and transform your PC into a powerhouse with this 24 inch diagonal screen monitor with USB-C 100W Power Delivery.

### Universally consistent colors

Out of the box, you get remarkable color accuracy from screen to screen[1]. Achieve precise, vibrant detail with 99% sRGB color gamut and WUXGA resolution.

### Always on low blue light

Experience exceptional vibrancy with HP Eye Ease, the always on low blue light filter that reduces blue light exposure with zero impact to true color accuracy.

### Design pushed to the edge

Meticulously crafted with a razor-thin profile and frameless design, this stunning 24-inch diagonal screen monitor effortlessly powers your PC or Mac®. Get ultimate comfort with 4-way ergonomic adjustability.

### Responsibly reimagined

Make a conscious choice with this monitor that's been built with the environment in mind. Its plastics consist of over 80% recycled materials[2] plus it has 100% sustainably sourced and recyclable packaging[3]. It is ENERGY STAR® certified and EPEAT® 2020 registered[4].

## Features

### Easily connect multiple monitors

Declutter your desk and connect a series of displays by daisy chaining with a single DisplayPort™ cable.<sup>[5]</sup>

### All the ports you need

Connect to a Workstation, a PC and additional displays.

### Easily mount a Mini

Mount your HPZ2 Mini or HP Desktop Mini directly to the monitor for a clean workspace.<sup>[6]</sup>

### HP Zero BrightDot Guarantee

Even if just a third of a pixel fails or is stuck in one position, HP will replace the entire display.<sup>[7]</sup>

### Optional integrated audio

Easily attach the Z Display Conferencing Speaker Bar for stereo quality audio and dual microphones.<sup>[8]</sup>

### 3-year limited warranty

The assurance of HP's three-year standard limited warranty.

---

*[1] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.*

*[2] Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 EPEAT standard.*

*[3] 100% outer box/corrugate cushion packaging made from sustainably sourced certified and recycled fibers. Fiber cushions made from 100% recycled wood fiber and organic material. Any plastic cushions are made from >90% recycled plastic. Excludes plastic bags and plastic foam sheeting.*

*[4] Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. Status varies by country. Visit [www.epeat.net](http://www.epeat.net) for more information.*

*[5] Requires an additional DisplayPort™ cable to daisy chain.*

*[6] Z2 Mini and Desktop mini and B550 Z Display G3 PC Mounting Bracket sold separately.*

*[7] The HP Pixel Policy allows no bright sub-pixel defects for this display. For complete details, see <http://support.hp.com/us-en/document/c00288895>.*

*[8] Z Display Conferencing Speaker Bar Sold Separately.*

## Specifications

<b>Display size (diagonal)</b>	24"
<b>Panel technology</b>	IPS
<b>Display size (diagonal)</b>	61 cm (24")
<b>Aspect ratio</b>	16:10 <sup>[1]</sup>
<b>Native resolution</b>	WUXGA (1920 x 1200) <sup>[1]</sup>
<b>Resolutions supported</b>	640 x 480; 800 x 600; 1024 x 768; 1280 x 800; 1280 x 1024; 1440 x 900; 1600 x 900; 1600 x 1200; 1680 x 1050; 1920 x 1080; 1920 x 1200
<b>Pixel pitch</b>	0.270 mm
<b>Brightness</b>	350 nits <sup>[1]</sup>
<b>Contrast ratio</b>	1000:1 <sup>[1]</sup>
<b>Response time (typical)</b>	5ms GtG (with overdrive) <sup>[1]</sup>
<b>Minimum dimensions (W x D x H)</b>	53.17 x 3.85 x 34.29 cm (Without stand.)
<b>Minimum dimensions (W x D x H)</b>	20.93 x 1.52 x 13.5 in (Without stand.)
<b>Dimensions With Stand (W x D x H)</b>	53.17 x 19.5 x 52.14 cm
<b>Weight</b>	5.3 kg (With stand.)
<b>Weight</b>	11.69 lb (With stand.)
<b>Display features</b>	Language selection; On-screen controls; Anti-glare; Height Adjust/Tilt/Swivel/Pivot
<b>Display Input Type</b>	1 HDMI 2.0; 1 USB Type-C™ (Alternative mode DisplayPort™ 1.4, Power Delivery up to 100W); 4 USB-A 3.2 Gen 1; 1 DisplayPort™ 1.4-in; 1 DisplayPort™ 1.4-out
<b>Onscreen controls</b>	Exit; Information; Management; Power control; Input control; Menu control; Brightness+; Image; Color
<b>Display colors</b>	Up to 16.7 million colors supported (through FRC technology)
<b>Display scan frequency (horizontal)</b>	30-80 KHz
<b>Display scan frequency (vertical)</b>	50-60 Hz
<b>Ports</b>	1 RJ-45
<b>Camera</b>	No integrated camera
<b>Power</b>	100 - 240 VAC 50/60 Hz
<b>Power consumption</b>	160 W (maximum), 32 W (typical), 0.5 W (standby)
<b>Operating temperature range</b>	5 to 35°C

<b>Operating humidity range</b>	20 to 80% non-condensing
<b>Certifications and compliances</b>	Australian-New Zealand MEPS; BIS; BSMI; CB; CCC; CE; CEL; CEL Grade 1; cTUVus; EAC; FCC; GS Mark; ISO 9241-307; KC/KCC; NOM; PSB; SEPA; TUV-S; VCCI; Vietnam MEPS; WEEE; Low blue light; Ukraine Energy label; WW application; UAE <sup>[5]</sup>
<b>Physical security</b>	Security lock-ready <sup>[2]</sup>
<b>Management Software</b>	HP Display Center; HP Display Manager
<b>UPC number</b>	(A2K) 195122260835; (A2N) 195122260842; (AB0) 195122260859; (AB1) 195122260866; (AB2) 195122260873; (AB4) 195122260880; (ABA) 195122260897; (ABB) 195122260903; (ABG) 195122260910; (ABJ) 4580511764432; (ABT) 195122260927; (ABU) 195122260934; (ABV) 195122260941; (ABY) 195122260958; (ACJ) 195122260965; (ACQ) 195122260972; (AH3) 195122260989; (AKL) 195122260996; (AR6) 195122261009; (UUF) 195122261016; (UUZ) 195122261023
<b>What's in the box</b>	Monitor; Documentation; VESA Mount adapter; Cable manager; 1 USB Type-C® to Type-C cable; AC power cord; DisplayPort™ 1.4 cable <sup>[4]</sup>

## Additional specifications

<b>Backlight type</b>	Edge-lit
<b>Bezel</b>	4-sided micro-edge
<b>Card reader</b>	No
<b>Color gamut</b>	99% sRGB; 85% DCI-P3
<b>Curvature</b>	Flat
<b>Datasheet photo 1</b>	AHID/d5914bfa09a6c4103c07ac941d812687abdc40a1
<b>Datasheet photo 2</b>	AHID/ab75642491ca0eac7b484dc0b49d41d2693d1f49
<b>Datasheet photo 3</b>	AHID/55281df42c90e5987257807a5ae7232b38363b00
<b>Datasheet photo 4</b>	AHID/b2e9263fe15d3ffc1a8af9815a4f9d5cfed34eee
<b>Detachable stand</b>	Yes
<b>Display area (imperial)</b>	20.41 x 12.76 in
<b>Display area (metric)</b>	51.84 x 32.4 cm
<b>Display contrast ratio (dynamic)</b>	10000000:1
<b>DisplayPort™</b>	1 DisplayPort™ 1.4
<b>DisplayPort™ Out</b>	1 DisplayPort™ 1.4-out
<b>Energy star certified</b>	ENERGY STAR® certified
<b>Ethernet</b>	1 RJ-45 (10/100/1000 Mbps)
<b>Flicker-free</b>	Yes
<b>HDCP</b>	Yes, DisplayPort™ and HDMI
<b>HDMI</b>	1 HDMI 2.0
<b>Hardness</b>	3H
<b>Height adjustment range</b>	150 mm
<b>Horizontal viewing angle</b>	178°
<b>Integrated privacy filter</b>	No
<b>Low blue light</b>	Yes, HP Eye Ease (TÜV Low Blue Light Hardware Solution certified)
<b>Microphone</b>	No
<b>Non-Operating Humidity Range</b>	0 – 95%
<b>Operating temperature range</b>	41 to 95°F
<b>Package dimensions (W x D x H)</b>	24.61 x 16.34 x 5.59 in
<b>Package dimensions (W x D x H)</b>	62.5 x 41.5 x 14.2 cm
<b>Package weight</b>	17.86 lb
<b>Package weight</b>	8.1 kg
<b>Panel bit depth</b>	8 bit (6 bit + 2 FRC)

<b>Pixels per inch (ppi)</b>	96 ppi
<b>Power supply type</b>	Internal
<b>Product dimensions with stand (W x D x H)</b>	20.93 x 7.68 x 20.53 in
<b>Recommended resolution</b>	WUXGA (1920 x 1200 @ 60 Hz)
<b>Resolution (maximum)</b>	WUXGA (1920 x 1200 @ 60 Hz)
<b>Screen treatment</b>	Anti-glare
<b>Speaker type</b>	No
<b>Storage temperature range</b>	5 to 95%
<b>Tilt</b>	-5 to +20°
<b>Total CO2e (kg) footnote number</b>	[60]
<b>Touch-enabled</b>	Not touch-enabled
<b>UNSPSC code</b>	43211902
<b>USB Type-A</b>	4 SuperSpeed USB Type-A 5Gbps signaling rate
<b>USB Type-C® video input</b>	1 SuperSpeed USB Type-C® 5Gbps signaling rate (Up to 100W USB Power Delivery, Alt Mode DisplayPort™ 1.4)
<b>VESA mounting</b>	100 mm x 100 mm (bracket included)
<b>Vertical viewing angle</b>	178°
<b>pivot</b>	±90
<b>swivel</b>	±45°

---

*[1] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.*

*[2] Lock sold separately.*

*[4] Included cables may vary by country.*

*[5] Monitors produced before June 1st 2024 comply with China regulation GB 21520-2015.*

---

## Accessories for PC

### Stands/Mounting Brackets

★ : Recommended

#### Mounting Brackets

HP B550 PC Mounting Bracket

16U00AA

#### Stands

HP Integrated Work Center for Desktop Mini and Thin Client

G1V61AA

### Security

#### Security Cables

HP Business PC Security Lock v3 Kit

3XJ17AA

### Audio Devices

#### PC Speakers

HP Z G3 Conferencing Speaker Bar

32C42AA

---

## Disclaimer — Copyright

USB-C® is a registered trademark of USB Implementers Forum. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. Missing Mac (Apple) ENERGY STAR. For trademark comments, see: <https://legal.int.hp.com/legal/pages/tradeack.aspx>.

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Jul 29, 2024 4:33 PM UTC+0000