

## PERFORMANCE

### Processor

Intel® Core™ Ultra 7 165H, 16C (6P + 8E + 2LPE) / 22T, Max Turbo up to 5.0GHz, 24MB

### NPU

Intel® AI Boost integrated in Intel® Core™ Ultra processor

### Graphics

NVIDIA® RTX 2000 Ada Generation 8GB GDDR6

### Chipset

Intel® SoC Platform

### Memory

64GB LPCAMM2 LPDDR5x-7467

### Memory Slots

One LPCAMM2 connector, dual-channel

### Max Memory

Up to 64GB (1x 64GB LPCAMM2), upgradable

### Storage

2TB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal 2.0

### Storage Support

Up to two drives, 2x M.2 SSD

- M.2 2280 SSD up to 8TB, 4TB each
- RAID 0/1 support

### Storage Slot

Two M.2 2280 PCIe® 4.0 x4 slots

### Card Reader

SD 7.0 Card Reader

### Audio Chip

High Definition (HD) Audio, Realtek® ALC3306 codec

### Speakers

Stereo speakers, 2W x2, Dolby Atmos®

### Camera

5.0MP + IR with Privacy Shutter and Human Presence Detection

### Microphone

2x, Array

### Battery

Integrated 90Wh

### Power Adapter

170W Slim Tip (3-pin)

## DESIGN

### Display

16" WQUXGA (3840x2400) OLED 400nits Anti-reflection / Anti-smudge, 100% DCI-P3, 60Hz, DisplayHDR™ 400, Dolby Vision®, TÜV Eyesafe®, Touch

### Touchscreen

Add-on Film Touch, 10-point Multi-touch

### Color Calibration

Factory Color Calibration

### Keyboard

Backlit, English

### Case Color

Black

### Case Material

Aluminium (Top), Aluminium (Bottom)

### Dimensions (WxDxH)

354.4 x 241.2 x 17.05 mm (13.95 x 9.49 x 0.67 inches)

### Weight

Starting at 1.82 kg (4.03 lbs)

## SOFTWARE

### Operating System

Windows® 11 Pro, English

### Bundled Software

Intel® Connectivity Performance Suite

## CONNECTIVITY

### Ethernet

No Onboard Ethernet

### WLAN + Bluetooth®

Intel® Wi-Fi® 7 BE200, 802.11be 2x2 + BT5.4

### WWAN

No support

### SIM Card

No physical SIM card inbox

### Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with USB PD 3.0 (135W input) and DisplayPort™ 1.4
- 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 (135W input) and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 8K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x SD Express 7.0 card reader
- 1x Security keyhole

### Docking

Various docking solutions supported via Thunderbolt™ or USB-C®.

For more compatible docking solutions, please visit .

[Docking for ThinkPad® P1 Gen 7](#)

## SECURITY & PRIVACY

### Smart Card Reader

No smart card reader

### Security Chip

Discrete TPM 2.0 Enabled

### Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

### Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

### Other Security

- Camera privacy shutter (camera models)
- IR camera for Windows® Hello (facial recognition)
- Ultrasonic Human Presence Detection for IR camera
- Bottom cover tamper detection

## MANAGEABILITY

### System Management

Intel® vPro® Enterprise

## SERVICE

### Base Warranty

3-year, Courier or Carry-in

### Included Upgrade

3Y Premier Support Upgrade from 3Y Courier/Carry-in

## CERTIFICATIONS

### Green Certifications

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- RoHS compliant
- TCO Certified 9.0

### Other Certifications

- Intel® Evo™ Platform
- Eyesafe® Certified 2.0

### Mil-Spec Test

MIL-STD-810H military test passed

### ISV Certifications

Please visit [ISV certifications for Lenovo® Workstations](#)

## MODEL

**TopSeller** : Yes **Announce Date** : 2024-05-28

**EAN / UPC / JAN** : 198153494248 **End of Support** : 2030-12-28

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkPad Hybrid USB-C with USB-A Dock (American Standard Plug Type B)

40AF0135US

- The ThinkPad Hybrid USB-C with USB-A dock is a productivity solution for any USB-C or USB-A laptop, including non-Lenovo laptops from Dell, HP, and Apple, providing power, display, and port expansion in any m...

## Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Premier Support (5WS1M86970)
BETTER	3Y Premier Support Plus upgrade from 3Y Premier Support (5WS1L39135)
GOOD	4Y Premier Support upgrade from 3Y Premier Support+3Y Lenovo Support (KYD + SBTY + International Upg) (5WSOW86674, 5PS1D67026)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference