



L A P T O P S

Stealth 14 AI Studio

STEALTH 14 AI STUDIO A1VGG-089US

Specification

Manufacturer Part #	STEALTH14A1089
OS	Windows 11 Pro
CPU	Intel® Core™ Ultra9-185H
CPU Speed	3.8-5.1 GHz
Chipset	-
Color	Star Blue
Screen Size	14" 16:10 QHD+ 2.8K OLED Panel 120Hz 100% DCI-P3
Resolution	(2880x1800) 16:10
GPU	NVIDIA® GeForce RTX™ 4070 Laptop GPU
Video Memory	8G GDDR6
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (83 Key)
Speaker	Sound by Dynaudio, 2x2W Speaker
Memory	64GB (32GB*2) DDR5 5600MHz
HDD Capacity	1TB NVMe SSD Gen4x4
HDD Interface	NVMe
TPM	Intel ® PTT
LAN	-
WLAN	Killer WiFi 7 BE1750
Bluetooth	BT 5.4
Card Reader	-
Webcam	1080p FHD with shutter
USB	1x USB 3.2 Gen1
Type-C Port	1x Thunderbolt™ 4 w/PD; 1x USB 3.2 Gen 2/DP
Video Port	v2.1,
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	240 W
Battery Pack	4 cell (72Whr) Li-Polymer
Dimension	12.4"x9.69"x0.75"
Weight	3.75lbs
Manufacturer Warranty	3 year Limited warranty (Include 1 Year Global)