



L A P T O P S

Cyborg 15 AI

CYBORG 15 AI A1VFK-099US

Specification

Manufacturer Part #	CYBORG15A1099
OS	Windows 11 Pro
CPU	Intel® Core™ Ultra 7-155H
CPU Speed	1.4-4.8 GHz
Chipset	-
Color	Translucent Black
Screen Size	15.6" FHD IPS-Level Panel 144Hz 45% NTSC
Resolution	(1920x1080) 16:9
GPU	NVIDIA® GeForce RTX™ 4060 Laptop GPU
Video Memory	8G GDDR6
Keyboard	Blue keyboard with Anti-Ghost key (83 Key)
Speaker	2x Speakers 2W, hi-Res Audio, DTS
Memory	32GB (16GB*2) DDR5 5600MHz
HDD Capacity	1TB NVMe SSD Gen4x4
HDD Interface	NVMe
TPM	Intel ® PTT
LAN	Gb LAN
WLAN	Intel Wi-Fi 6 AX201(2*2 ax)
Bluetooth	BT 5.3
Card Reader	-
Webcam	720p HD Webcam
USB	2x USB 3.2 Gen1
Type-C Port	1x USB 3.2 Gen1 w/DP1.4
Video Port	v2.1,
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	120W
Battery Pack	3 cell , 53.5Whr Li-Polymer
Dimension	14.15"x9.86"x0.9"
Weight	4.37 lbs
Manufacturer Warranty	3 year Limited warranty (Include 1 Year Global)