



L A P T O P S

Pulse 16 AI

PULSE 16 AI C1VGKG-065US

Specification

Manufacturer Part #	PULSE16C1065
OS	Windows 11 Pro
CPU	Intel® Core™ Ultra9-185H
CPU Speed	3.8-5.1 GHz
Chipset	-
Color	Black
Screen Size	16" QHD+ Wide View Angle 240Hz Thin Bezel 100% DCI-P3
Resolution	(2560x1600) 16:10
GPU	NVIDIA® GeForce RTX™ 4070 Laptop GPU
Video Memory	8G GDDR6
Keyboard	SteelSeries 24-Zone RGB with Anti-Ghost key (99 Key)
Speaker	2x2W Speaker Hi-Res Audio, Nahimic
Memory	64GB (32GB*2) DDR5 5200MHz
HDD Capacity	1TB NVMe SSD Gen4x4
HDD Interface	NVMe
TPM	Intel® PTT
LAN	Gb LAN
WLAN	Intel Wi-Fi 6E AX211(2*2 ax)
Bluetooth	BT 5.3
Card Reader	-
Webcam	720p HD with shutter
USB	3x USB 3.2 Gen1
Type-C Port	1x USB 3.2 Gen 2/DP(w/PD3.0 Chargin)
Video Port	v 2.1 8K@60Hz 4K@120Hz
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	240 W
Battery Pack	4 cell (90Whr) Li-Ion
Dimension	14.13"x10.49"x1.1"
Weight	5.51lbs
Manufacturer Warranty	3 year Limited warranty (Include 1 Year Global)