


# ASUS ExpertCenter PB63 series

High-performance and durable mini PC suited to a range of business applications



Chassis Intrusion



Wi-Fi 6E 802.11ax



Triple Storage



DDR5 Memory



MyASUS



Pad Lock Support



Kensington Lock



4K



3 Displays

## Desktop-grade performance in slim style

Powered by 14<sup>th</sup> Gen Intel® Core™ processor

- Support DDR5 memory and PCIe Gen4x4 SSD for great performance
- Support 3 display with 4K UHD resolution simultaneously

## ASUS ExpertCenter series features

### Trustworthy

- 24/7 testing reduce maintenance cost and improve cost effectiveness
- Kensington lock and Pad-lock design for more security
- Environmentally-friendly designs with Energy Star and EPEAT Gold

### Professionalism

- PB63's design is space-saving, secure with numerous ports on front and rear sides
- Wi-Fi 6E\* can easily handle the most data-intensive tasks
- ASUS Control Center option for IT Management



\*Models with WiFi 6E only available in certain regions or countries, and is dependent on local regulations.

### Flexibility

- Includes two DisplayPort™, eight USB ports, and additional configurable port (options: COM, VGA, DP 1.2, HDMI, 2.5G LAN)
- Offers Black and White options
- Accommodates up to three storages

# ASUS ExpertCenter PB63 series

## Overview:



## Accessories list:



- Power Cord
- AC Adapter
- Quick Start Guide & Warranty Card
- VESA Mount Kit (Optional)
- Keyboard & Mouse (Optional) Wired / Wireless

## Feature table:

Power	
PD input	N
Extended Power Button	N
BIOS	
AC Power loss	Y
HDMI-CEC	N
CrashFree	Y
EZ Flash	Y
BIOS Customization	Y
PXE/WOL	Y
USB Single Port Control	Y

Security	
fTPM 2.0	Y
dTPM 2.0	optional
Kensington lock	Y
Pad-lock Ring	Y
Chassis Intrusion	Y
Reliability	
24/7 Durability Test	Y
Military-grade Durability	Applying
Anti-Surge	Y
Fanless	N

Remote	
Watchdog timer	optional
MyASUS	
Smart Fan Control	Y
AI Noise Cancellation	Y
Wi-Fi Smart Connect	Y
Enterprise Support	
Windows Autopilot Registration Service	Y
ASUS Cooperate Stable Model	optional
ASUS Control Center	optional

\*For more information about Windows Autopilot Registration Service, please scan the QR code provided for reference.



# ASUS ExpertCenter PB63 series

Model		PB63 series
OS		Windows®11 64bit, Windows®11 Pro 64bit, or W/O OS
CPU		Intel Core i7-14700, Intel Core i5-14600, Intel Core i5-14500, Intel Core i5-14400, Intel Core i3-14100, Intel 300, Intel Core i7-13700, Intel Core i5-13500, Intel Core i5-13400, Intel Core i3-13100, Intel Pentium Gold G7400, Intel Celeron G6900
Chipset		Intel® B760 Chipset
Graphics		Integrated - Intel® UHD Graphics
Memory		2 x SO-DIMM, DDR5-4800/5600*MHz memory, up to 32GB*2 *5600MHz only support on i7 SKUs
Storage		2 x M.2 2280 PCIe Gen4x4, supports 128GB~2TB NVMe™ SSD 1 x 2.5" SATA 6Gb/s, supports 1TB 7200rpm 7mm HDD
Wireless Network		Intel® AX211 (Gig+), Wi-Fi 6E, Bluetooth 5.2, 2*2 Intel® AX201 (Gig+), Wi-Fi 6, Bluetooth 5.2, 2*2
LAN		1 x Intel® I219V, 1Gb LAN 1 x Intel® I225V, 2.5Gb LAN (Config. Port)
Interface	Front I/O	1 x USB 3.2 Gen2x2 Type-C 2 x USB 3.2 Gen1 Type-A 2 x USB 2.0 1 x Mic in 1 x Audio Jack (Line out/Mic in/Headphone out)  *All data transfer speed is according to ASUS testing result, actual performance may vary depending on objective environmental changes.
	Rear I/O	2 x USB 3.2 Gen2 Type-A 1 x USB 2.0 2 x DisplayPort 1.4 1 x Configurable (options: HDMI*/DP1.2/COM/VGA/2.5G LAN) 1 x RJ45 LAN 1 x Kensington Lock slot 1 x DC-in 1 x Padlock ring  * Supports up to 3 display simultaneously * Configurable HDMI2.1 support up to 4K@60Hz
TPM		fTPM 2.0 or TPM 2.0 chip (Optional)
BIOS Function		32 Mb Flash ROM, UEFI AMI BIOS, PnP, DMI2.0, WfM2.0, SM BIOS 3.6, ACPI 5.0, Multi-language BIOS, ASUS EZ Flash 3, My Favorites, Quick Note and ASUS DRAM SPD (Serial Presence Detect) memory information
Software		The following software are included in OS: MyASUS, ASUS Product registration program, Asus Control Center test, Watchdog timer
Support		Windows Autopilot Registration Service
Power Supply		20Vdc, 7.5A 150W Power Adapter ( i5, i7 CPU ) 20Vdc, 6.0A 120W Power Adapter ( i3, Pentium, Celeron CPU )
Physical	Dimension	175 x 175 x 44.2 mm (1.35L)
	Weight	1.14 kg (barebone)
Max Resolution	HDMI	4096 x 2160 @60Hz
	DP	5120*2160@60Hz
Temperature	Operating	0~50 Celsius
	Storage	-40~85 Celsius
Humidity		0%~95% Relative Humidity
Acoustic	Idle mode	22.4 dBA
	Full loading	44.8 dBA
Certificates		* Test results will vary slightly depending on the HDD/SSD SKU selected by customer BSMI / Energy Star / WiFi / RF / VCCI