

Product data sheet

Specifications



[TAA] APC Smart-UPS, Line Interactive, 2200VA, Rackmount 2U, 120V, 6 NEMA 5-15R+2 NEMA 5-20R outlets, SmartConnect Port+SmartSlot, AVR, LCD, TAA

SMT2200RM2UCUS

Overview

Lead time Usually in Stock

Main


Main Input Voltage	120 V
Main Output Voltage	120 V
Other Output Voltage	110 V
Kw Rating	1920 W
Rated power in VA	1920 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA 5-20P
output connection type	6 NEMA 5-15R
Number of rack unit	2U
Cable length	8 ft (2.4 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	Rack Mounting brackets
Range of Product	Smart-UPS

Complementary

Communication port type	SmartConnect Ethernet port SmartSlot
Software package	SmartConnect software for remote power monitoring feature availability varies by terms of use

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Extendable Run Time	0
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h

RBC Quantity	1
Battery Life	3...5 year(s)
Replacement battery	RBC43 
Battery Charge Power (Watts)	179 W rated

General

Number of power module	0
Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	Cloud-enabled monitoring
Redundant	No

Physical

color	Black
Height	3.4 in (8.6 cm)
Width	17.008 in (432.003 mm) 17.008 in (43.2 cm)
Depth	26.9 in (68.3 cm)
Net Weight	93.28 lb(US) (42.31 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes

Input

Efficiency at full load	75...154 V adjustable
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	2200 VA
Max Configurable Power (Watts)	1980 W
Transfer Time	6ms typical : 10ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	cULus ENERGY STAR V2.0 (USA)
Equipment protection policy	Lifetime : \$150000

Environmental

Acoustic level	55 dBA
Online Thermal Dissipation	215 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Communications & Management

Control panel	Multi-function LCD status and control console
Emergency Power Off (EPO)	Yes
Free slots	1
Communication port support	SmartConnect Ethernet port: for cloud monitoring feature availability varies by terms of use
Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rating	530 J
---------------------	-------

Ordering and shipping details

GTIN	731304740506
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0000000000 in (25.4 cm)
Package 1 Width	38.6 in (98 cm)
Package 1 Length	23.6 in (60 cm)
Package 1 Weight	109.64 lb(US) (49.73 kg)

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery, optional on-site warranties available, optional extended warranties available
----------	--

Sustainability


Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)



Transparency RoHS/REACH

Well-being performance

 Rohs Exemption Information [Yes](#)

Environmental Certifications

 Energy Star® [ENERGY STAR UPS V2.0 \(USA\)](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive [Compliant with Exemptions](#)

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information.

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

Technical Illustration

Dimensions



Image of product / Alternate images

Alternative

