



Prestige 16 Evo

PRESTIGE 16EVO A13M-408US

Specification

Manufacturer Part #	PRE16EVO13408
OS	Windows 11 Pro
CPU	Intel® Core™ i9-13900H
CPU Speed	2.6 - 5.4 GHz
Chipset	-
Color	Urban Silver
Screen Size	16" 16:10 QHD+ 100% sRGB 165Hz 400nits IPS-Level Panel
Resolution	(2560x1600) 16:10
GPU	Intel® Iris® Xe
Video Memory	-
Keyboard	White backlight keyboard (99 Key)
Speaker	2x Speakers 2W
Memory	32GB LPDDR5-4800MHz
HDD Capacity	1TB NVMe SSD
HDD Interface	NVMe
TPM	TPM 2.0
LAN	-
WLAN	Killer WiFi 6E AX1675 (2x2)
Bluetooth	BT 5.3
Card Reader	Micro SD
Webcam	IR FHD Type [30fps/1080p]
USB	2x USB 3.2 Gen2 (Type-A)
Type-C Port	2x Thunderbolt™ 4 [Support Power delivery, DP 1.4a, USB 4.0]
Video Port	HDMI 2.0 (4K @ 60Hz)
Audio Port	Mic-in/Headphone-out Combo
AC Power Adaptor	100W [USB-C]
Battery Pack	4 cell (81.77Whr) Li-Polymer
Dimension	14.09" x 10.18" x 0.66"
Weight	4.19 lbs
Manufacturer Warranty	3 year Limited warranty (Include 1 Year Global)