

PERFORMANCE

Processor

Intel® Core™ Ultra 5 135U, 12C (2P + 8E + 2LPE) / 14T, Max Turbo up to 4.4GHz, 12MB

AI PC Category

AI PC

NPU

Intel® AI Boost, up to 11 TOPS

Graphics

Integrated Intel® Graphics

Chipset

Intel® SoC Platform

Memory

16GB Soldered LPDDR5x-6400

Memory Slots

Memory soldered to systemboard, no slots, 8-channel

Max Memory

16GB soldered memory, not upgradable

Storage

512GB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal 2.0

Storage Support^[1]

One drive, up to 2TB M.2 2280 SSD

Storage Slot

One M.2 2280 PCIe® 4.0 x4 slot

Card Reader

None

Optical

None

Audio Chip

High Definition (HD) Audio, Realtek® ALC3306 codec

Speakers

Stereo speakers, 2W x2, Dolby Atmos®

Camera

FHD 1080p + IR Discrete with Privacy Shutter

Microphone

2x, Array

Battery

Integrated 57Wh

Power Adapter

65W USB-C® Slim (2-pin)

DESIGN

Display^[2]

14" WUXGA (1920x1200) IPS 400nits Anti-glare, 100% sRGB, 60Hz, Low Power, Touch

Touchscreen

On-cell, 10-point Multi-touch

Keyboard

Backlit, English

Touchpad

Trackpad

Case Color

Black, Paint

Case Material

Carbon Fiber (Top), Aluminium (Bottom)

Dimensions (WxDxH)^[3]

312.80 x 214.75 x 14.96 mm (12.31 x 8.45 x 0.59 inches)

Weight^[4]

Starting at 1.08 kg (2.37 lbs)

SOFTWARE

Operating System

Windows® 11 Pro, English

Bundled Software

Intel® Connectivity Performance Suite

CONNECTIVITY

Ethernet^[5]

No Onboard Ethernet

WLAN + Bluetooth^{[6][7]}

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3

WWAN

Quectel EM160R-GL, 4G LTE CAT16, with Embedded eSIM

SIM Card

None

NFC

None

Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)

Optional Ports (configured)

1x Nano-SIM Card Slot

Docking

Various docking solutions supported via Thunderbolt™ / USB-C®.

For more compatible docking solutions, please visit [Docking for ThinkPad® X1 Carbon Gen 12](#)

SECURITY & PRIVACY

Smart Card Reader

None

Security Chip

Discrete TPM 2.0 Enabled

Fingerprint Reader

Touch Style, Match-on-Chip, in Keyboard Key

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Other Security

- IR camera for Windows® Hello (facial recognition)
- Ultrasonic Human Presence Detection (FHD 1080p + IR camera models)
- Camera privacy shutter

MANAGEABILITY

System Management^[8]

Intel® vPro® Enterprise

SERVICE

Base Warranty

3-year, Courier or Carry-in

Included Upgrade

3Y Premier Support Upgrade from 3Y Courier/Carry-in

ACCESSORIES

Bundled Accessories^[9]

None

CERTIFICATIONS

Green Certifications^[10]

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant
- TCO Certified 9.0

Other Certifications

- Intel® Evo™ Platform
- Eyesafe® Certified 2.0

Mil-Spec Test

MIL-STD-810H military test passed

MODEL

TopSeller : Yes **Announce Date** : 2024-05-28

EAN / UPC / JAN : 198154165086 **End of Support** : 2030-07-08

Note:

[1] The storage capacity supported is based on the test results with current Lenovo storage offerings.

[2] IPS (in-plane switching) technology may refer to IPS,.....

· Lenovo reserves the right to change specifications without notice.
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to <https://psref.lenovo.com/Detail/2402?M=21KC00B3US>

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkPad Universal USB-C Dock

40AY0090US

THE SMARTER WAY TO WORK Introducing the ThinkPad Universal USB-C Dock. This advanced, universally compatible one-cable docking solution lets you work smarter, not harder. It comes with a vast array of ports, next-gen ...

Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Premier Support (5WS1M86992)
BETTER	3Y Premier Support Plus upgrade from 3Y Premier Support (5WS1L39253)
GOOD	4Y Premier Support upgrade from 3Y Premier Support (5WS0W86716)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference