



## SPECIFICATIONS

<b>Resolución de la pantalla</b>	2560 x 1440 (WQHD)
<b>Tasa de refresco</b>	100Hz
<b>ADOBE RGB / DCI-P3 / SRGB</b>	93% / 93% / 118%
<b>HDR SUPPORT</b>	DisplayHDR 400
<b>Puertos de audio</b>	1x Headphone-out
<b>KENSINGTON LOCK</b>	Yes
<b>SPEAKER</b>	2x 3W
<b>Brillo (Nits)</b>	400 cd/m2
<b>Regulable (inclinación)</b>	-5° ~ 20°
<b>ADJUSTMENT (HEIGHT)</b>	0 ~ 130 mm
<b>Tamaño de la caja (An x Al x Pr)</b>	841 x 448 x 131 mm (33.11 x 17.64 x 5.16 inch)
<b>ADJUSTMENT (PIVOT)</b>	-90° ~ 90°
<b>Certificados</b>	CB/CE Energy Star
<b>ADJUSTMENT (SWIVEL)</b>	-45° ~ 45°
<b>Compatibilidad</b>	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.
<b>ACCESSORIES</b>	1x HDMI Cable (2.0), 1x Power Cord, 1x Power Adaptor, 1x Quick Guide, 4x Stand Screw, 1x VESA Plate (to mount with Mini-PC), 4x VESA Plate Screw
<b>Tipo de panel</b>	IPS
<b>Peso (NW / GW)</b>	6.05 kg (13.34 lbs) / 8.9 kg (19.62 lbs)
<b>Obeservación</b>	HDMI™: 2560 x 1440 (Up to 100Hz) DisplayPort: 2560 x 1440 (Up to 100Hz) Adaptive Sync Support *Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard
<b>Tipo de alimentación</b>	External Adaptor 12V 4A
<b>Tamaño ( An x Al x Pr)</b>	613.5 x 543.3 x 226.9 mm (24.15 x 21.34 x 8.93 inch)
<b>Soporte VESA</b>	75 x 75 mm
<b>Tiempo de respuesta</b>	1ms (MPRT) / 4ms (GTG)
<b>Puertos de video</b>	2x HDMI™ 2.0b (2K@100Hz) 1x DisplayPort (1.2a)
<b>Bit de color</b>	10 bits (8 bits + FRC)

## FEATURES



### IPS Grade Panel

Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best while creating your own on-line video



### EyesErgo

EyesErgo

An eye care solution designed with ergonomics in mind.



### Less Blue Light PRO

Use a hardware solution to reduce the light emission in the blue-violet region of the blue light spectrum (wavelength 415 to 455 nm).




### Eye-Q Check

Help have self-check eyes & remind to take a rest while using the monitor for a long time.



### 100Hz High Refresh Rate

Experience smooth gaming with a blazing fast 100Hz refresh rate, that gives you the upperhand in fast moving games.



### Adjustable Stand

Adjust the stand to the angle that is most suitable for you to keep yourself work comfortably.

VESA CERTIFIED



### VESA Certified DisplayHDR 400

Provide eye-catching detail through contrast and shadows adjustment.



### VESA Mountable

To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.

<b>Colores de pantalla</b>	1.07B
<b>Tratamiento de la superficie</b>	Anti-glare
<b>Tamaño de píxel (H x V)</b>	0.2331(H) x 0.2331(V)
<b>Área de visualización activa (mm)</b>	596.736(H) x 335.664(V)
<b>Relación de contraste</b>	1300:1
<b>Relación de aspecto</b>	16:9
<b>Ángulo de visión</b>	178°(H) / 178°(V)
<b>Entrada de alimentación</b>	100~240V, 50~60Hz
<b>Tamaño del panel</b>	27"

## CONNECTIONS



1. 2x HDMI™ (2.0b)
2. 1x DisplayPort (1.2a)
3. 1x Headphone-out
4. 1x DC Jack 1x Kensington Lock
5. OSD Button