



SPECIFICATIONS

Panel Size	24.5" (62.22 cm)
Active Display Area (mm)	543.744(H) x 302.616(V)
Curvature	Flat
Panel Type	Rapid VA
Panel Resolution	1920 x 1080 (FHD)
Pixel Pitch (H x V)	0.2832(H) x 0.2802(V)
Aspect Ratio	16:9
Brightness (nits)	250 Nits (Typ.)
Contrast Ratio	3000:1
DCR	100000000:1
Signal Frequency	53.04KHz~1281KHz(H)/48-250Hz
ACTIVATED RANGE	48~250Hz
Refresh Rate	250Hz(OC)
Response time	0.5ms (GtG, Min.)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
HDR Support	HDR Ready
Video ports	1 x DisplayPort 1.4 2 x HDMI™ 2.0b (FHD@240Hz)
USB ports	N/A
Audio ports	1 x Headphone Out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	82%/78%/100%
Surface Treatment	Anti-glare
Display Colors	1.07B,10 bits(8 bits + FRC)
Power Type	Power Cable
Power Input	100 ~ 240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	N/A
Adjustment (Pivot)	N/A
Adjustment (Height)	N/A
Kensington Lock	Yes
Dimension (W x D x H)	557.1x220.1x418.5mm 557.1x66.4x326.9 (without stand)
Carton Dimension (W X D X H)	WW Carton:630 x 125 x 411mm Outer Carton:650 x 145 x 443mm
Frameless Design	Yes
PIP / PBP Function	Yes

FEATURES



Rapid VA Panel

Make sure the intensity and purity of colors when gaming.



250Hz High Refresh Rate

Experience smooth gaming with a blazing fast 250Hz refresh rate, that gives you the upperhand in fast moving games.



0.5ms (GtG, Min.) Response Time

Eliminate screen tearing and choppy frame rates with 0.5ms (GtG, Min.) Response Time.



Console Mode

Perfectly support 120Hz at QHD 2K resolution with next-gen console like PS5 and Xbox series X/S.



Frameless Design

With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.



AI Vision

Smart black tuner to brighten your day by bringing out the fine details in dark areas.

VESA Mounting	100 x 100 mm
Weight (NW / GW)	3.24kg / 5.13kg
Note	DisplayPort: 1920 x 1080 (Up to 250Hz) HDMI™: 1920 x 1080 (Up to 240Hz) *Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

CONNECTIONS



1. 5-Way Joystick Navigator
2. AC-in
3. HDMI™ 2.0b(FHD@240Hz)
4. DisplayPort 1.4
5. Earphone out
6. Kensington Lock