



[DOWNLOAD SPECS](#)

## PIXMA TS9520a

---

### PRINT

---

**Printer Functions** Print, Copy, Scan

---

**Print Features** AirPrint<sup>5</sup>, Auto 2-Sided (Duplex) Printing, Auto Photo Fix, Black Ink / Color Ink Only Printing, Borderless Printing<sup>7</sup>, Business Card Printing, Canon PRINT app<sup>4</sup>, Disc Label Printing, Document Printing, Easy-PhotoPrint Editor Software/app<sup>10</sup>, Greeting Cards, ID Card Printing, Label Printing, Memory Card Printing<sup>8</sup>, Mopria Print Service<sup>6</sup>, Pattern Paper Printing, Photo Printing, PIXMA Cloud Link<sup>4</sup>, Square Media Printing, Template Printing, Wireless Printing<sup>2</sup>

---

**Printing Capability** Single Sided (Simplex/Duplex) Printing

---

**Print Speed (ESAT) \*3** Black Document (Letter) Simplex: Approx. 15.0 ipm<sup>3</sup>  
Color Document (Letter) Simplex: Approx. 10.0 ipm<sup>3</sup>

---

**Print Resolution** Up to 4800 x 1200 dpi<sup>11</sup>

---

**Number of Nozzles** Color (C/M/Y): 3,072  
Pigment Black: 1,024  
Total: 4,096

---

**Media Handling** Rear Paper Tray: 100 Sheets of Plain Paper OR  
Photo Paper: 20 Sheets of 4" x 6" / 10 Sheets of 5" x 7"  
Front Paper Cassette: 100 Sheets of Plain Paper

---

**Supported Paper / Media Sizes** Rear Tray: LTR, Legal, A4, A5, B5, 4" x 6", 5" x 7", 7" x 10", 8" x 10", Square 3.5" x 3.5", 5" x 5"  
Custom Size: 2.2" - 8.5" / Length: 5" - 14"  
Cassette: LTR, A4, A5, B5

---

**Supported Borderless Printing \*7** 3.5" x 3.5", 4" x 4", 4" x 6", 5" x 5", 5" x 7", 8" x 10", Letter, 11" x 17", 12" x 12", Legal, U.S. #10 Envelopes

---

**Canon Paper / Media Compatibility** Plain: Plain Paper, Canon High Resolution Paper;  
Super High Gloss: Photo Paper Pro Platinum;  
Glossy: Photo Paper Plus Glossy II, Photo Paper Glossy;  
Semi-Gloss: Photo Paper Plus Semi-Gloss, Photo Paper Pro Luster;  
Matte: Matte Photo Paper;  
Other: Greeting Cards, Plastic ID Cards, Printable CD/DVD/Blu-ray Discs, T-Shirt Transfers, U.S. #10 Envelopes

---

**Supported Media Thickness / Weight** Cassette: Plain Paper: 64 - 105 g/m<sup>2</sup>  
Rear Tray: Plain Paper: 64 - 105 g/m<sup>2</sup> OR  
Canon Paper: Max. approx. 300 g/m<sup>2</sup> (Photo Paper Pro Platinum PT-101)

---

**Memory Card Support** SD™, SDHC™, SDXC™, miniSD™, miniSDHC™, microSD™, microSDHC™, microSDXC™

---

## COPY

---

**Copy Features** 4-on-1 / 2-on-1 Copy, Auto Document Feeder (ADF), Auto Exposure Copy, Booklet Layout Copy, Borderless Copy, Collated Copy (ADF Only), Disc Label Copy, Document Removal Reminder, Fit-to-Page, Frame Erase Copy, ID Card Copy, Large (Oversized) Document Copy, Manual 2-Sided Copy With ADF, Multiple Copy (Up To 99 Pages), Photo Fade Restoration, Preset Copy Ratios, Reduction/Enlargement (25% - 400%), Standard Copy, Two-Sided Copy

---

**Copy Speed (ESAT)** FCOT (Color): Approx. 19 Seconds<sup>3</sup>

---

**Maximum Document Size** Flatbed: Letter / A4  
ADF: Legal

---

## SCAN

---

**Scan Features** Auto Document Feeder (ADF), Auto Scan Mode<sup>3</sup>, Attach to Email, Document Removal Reminder, Multi-Page PDF, Save to PC, Scan to Canon PRINT app<sup>4</sup>, Wireless Scanning<sup>2</sup>

---

**Scanner Type** Contact Image Sensor (CIS)

---

**Scanning Method** Flatbed & ADF (Auto Document Feeder)

---

**Scanning Resolution** Flatbed: 1200 x 2400 dpi (Optical)<sup>13</sup>  
ADF: 600 x 600 dpi (Optical)<sup>13</sup>

---

**Maximum Color Scanning Bit Depth** 16-bit Internal (Per RGB Channel)  
8-bit External (Per RGB Channel)

---

**Maximum Document Size** Flatbed: 8.5" x 11.7" (Letter / A4)  
ADF: 8.5" x 14.0" (Legal)

---

**ADF Sheet Capacity** Letter Size: 20 Sheets Plain Paper  
Legal Size: 5 Sheets of Legal Plain Paper

---

## INK INFORMATION

---

**Ink Type** PGI-280 Pigment Black Ink  
CLI-281 Dye Based Ink

---

**Ink Cartridges & Fill Volume** PGI-280 PGBK: 11.2 ml (Std.) | 18.5 ml (XL) | 25.7 ml (XXL)  
CLI-281 BK, C, M, Y: 5.6 ml (Std.) | 8.3 ml (XL) | 11.7ml(XXL)

---

**Page Yield** Standard: 200 (Black) / 250 (Color) Pages<sup>25</sup>  
XL: 400 (Black) / 500 (Color) Pages<sup>25</sup>  
XXL: 600 (Black) / 800 (Color) Pages<sup>25</sup>

---

**Print Longevity** The ChromaLife100 System protects your photos from fading up to: 100 Years Album Life, or 30 Years Behind Glass (Light Fastness), or 20 Years Without The Glass (Gas Fastness)<sup>14</sup>









---

<b>Connectivity Options</b>	Hi-Speed USB Ethernet Wi-Fi® (802.11b/g/n/ac wireless networking, 2.4 GHz) <sup>2</sup> Memory Card Slot <sup>8</sup>
-----------------------------	--

---

## WIRELESS INFORMATION

---

<b>Standard</b>	IEEE 802.11b/g/n/ac wireless networking, 2.4 GHz <sup>2</sup>
-----------------	---

---

## OS COMPATIBILITY

---

<b>Windows *15</b>	Windows® 10, Windows® 8.1, Windows® 7 SP
--------------------	--

---

<b>Mac *16</b>	Mac OS® X v10.10.5 - macOS v10.12
----------------	-----------------------------------

---

<b>Mobile Operating Systems *17</b>	iOS®, Android, Windows 10 Mobile
-------------------------------------	----------------------------------

---

<b>Chromebook Compatible *18</b>	Yes
----------------------------------	-----

---

<b>Smart Assistant Support *19</b>	Amazon Alexa
------------------------------------	--------------

---

<b>Mobile Printing Solutions and Apps (iOS / Android)</b>	Canon PRINT app <sup>4</sup> , Easy-PhotoPrint Editor app <sup>10</sup> , Creative Park <sup>20</sup>
---	---

---

<b>Software (Windows / Mac) *15 *16</b>	PIXMA TS9520a Wireless Inkjet All-In-One Printer Driver, Scan Utility (Win/Mac) / Scan Utility Lite (Mac Only), Easy-PhotoPrint Editor Software <sup>10</sup> , Master Setup My Printer (Windows Only), Network Tool, Quick Menu
---	--

---

## GENERAL

---





---

<b>General Features</b>	5-Color Individual Ink System, Auto Power On/Off, Auto Print Head Alignment, Canon PRINT app <sup>4</sup> , CREATIVE PARK, Document Removal Reminder, Energy Star® Certified <sup>21</sup> , Hybrid Ink System, PIXMA Cloud Link <sup>4</sup> , Quiet Mode, Wireless Connect <sup>22</sup>
-------------------------	--

---

<b>Display</b>	4.3" Color Touch LCD Display
----------------	------------------------------

---

<b>Supported Languages</b>	33 Supported Languages: Japanese, English (mm & inch), German, French, Italian, Spanish, Portuguese, Dutch, Danish, Norwegian, Swedish, Finnish, Russian, Ukrainian, Polish, Czech, Slovenian, Hungarian, Slovakian, Croatian, Romanian, Bulgarian, Turkey, Greek, Estonian, Latvian, Lithuanian, Simplified Chinese, Korean, Traditional Chinese, Thai, Indonesia, Vietnamese
----------------------------	--

---

## POWER INFORMATION

---

<b>Energy Efficiency</b>	Rated EPEAT Silver <sup>24</sup> , Energy Star® Certified <sup>21</sup>
--------------------------	---

---

<b>Auto Power On / Off Capable</b>	Yes
------------------------------------	-----

---

<b>Input Voltage</b>	AC 100 - 240 V, 50 / 60 Hz
----------------------	----------------------------

---

<b>Power Consumption</b>	14W (1.2W Standby / 0.3W Off)
--------------------------	-------------------------------

---

<b>TEC (Typical Electricity Consumption)</b>	0.2kWh/week
--	-------------

---

## OPERATING ENVIRONMENT

---

<b>Operating Temperature</b>	41° - 95° F (5° - 35° C)
------------------------------	--------------------------

---

<b>Operating Humidity</b>	10 - 90% RH
---------------------------	-------------

---

## PRINTER INFORMATION

---







**Printer Size (Closed) L x W x H**

18.5" (L) x 14.5" (W) x 7.6" (H)<sup>23</sup>

---

**Printer Weight**

21.3 lbs.

---

**Printer Box Dimensions**

21.7" (L) x 10.7" (W) x 19.0" (H)

---

**Printer Box Weight**

27.3 lbs.

---









