





MAXHUB UC P30

The MAXHUB UC P30 is a 4K dual-eye tracking camera designed for medium and large rooms. It features a built-in dual 4K camera and a range of AI-driven features, including Auto Framing, Speaker Tracking, and Presenter Tracking, which allow it to reproduce every moment and detail precisely. The camera supports a 4K video stream, captures every detail of the meeting, and offers multiple installation options for flexibility.




Dual Lens 4K Camera

120° FOV wide angle lens detects participants in real-time while directing the PTZ Camera with best view.



12x Optical Zoom

The 12X optical zoom, powerful 8MP camera and 4K resolution offer the range and picture quality to produce the highest quality output.



AI Powered

Auto Framing
Speaker Tracking
Presenter Tracking



Manage And Control

Remotely manage and control via MAXHUB Pivot or room control on MAXHUB Microsoft Teams Rooms products.



Privacy Guarantee

When not in use, PTZ camera tilts downward and electric privacy cover would remain closed.



Flexible Installation

With PoE+, a single Cat5e/Cat6e cable supports IP Streaming and power.

Dual Camera**PTZ Camera**

Image sensor	Sony 4K , 8.42M pixel
Video outputs (USB 3.0)	H.264/MJPEG up to 2160p@30fps, YUV up to 1080p@30fps
Video outputs (USB 2.0)	H.264/MJPEG up to 1080p@30fps ;
Video outputs (HDMI)	H.264/MJPEG up to 2160@30fps ;
Video outputs (IP)	H.264/MJPEG up to 2160p@30fps (first stream); H.264/MJPEG up to 72p@30fps (second stream)
Optical zoom	12 x
Digital zoom	3 x
FOV	DFOV 90°/ HFOV 80°/ VFOV 49.2°
Lens focal length	4.8mm ~ 57.8mm
Lens F#	1.8 ~ 3.6
Motorized Pan & tilt	Pan: ±170°, Tilt: ±90°;
Preset number	10 via IR remote, 128 via RS232
Image flip and image mirror	Yes

Panoramic Camera

8MP, Sony Sensor
120° DFOV
Manual Tilt: ± 10°
Electric Privacy Cover
Camera LED Indicator

AI Feature

Auto Framing
Speaker Tracking
Presenter Tracking

IO Ports

USB 3.0 Type-C ×1 (Device)
USB 2.0 Type-A ×1 (host)
Mic in (3.5mm) ×1
HDMI 1.4 out ×1
RJ45 ×1 (IP Steam, POE+)
RS232 ×1 (VISCA/Pelco-D/Pelco-P protocol)
1 × Security Lock Slot

What's In The Package

UC P30 unit × 1
USB Cable C-A (5m) × 1
Power Adapter × 1
Remote Control × 1
Mounting kits × 1
Quick Start guide × 1

Power

Power supply	DC in 12V, 2A / POE+ in (Max 25W)
Power consumption	≤ 22W

Mechanical Specification

Product Dimension	181 × 151.5 × 178.4mm / 7.13 × 5.96 × 7.02 inch
Package Dimension (1pcs)	295 × 245 × 243mm / 11.61 × 9.65 × 9.57 inch
Package Dimension (4pcs)	610 × 510 × 265mm / 24.02 × 20.08 × 10.43 inch
Net Weight (1pcs)	2.3 kg / 5.34 lbs
Gross Weight (1pcs)	3.95 kg / 8.71 lbs
Gross Weight (4pcs)	16.9 kg / 37.26 lbs

Statement

Size and weight vary by configuration and manufacturing process, please refer to the actual product. The product images are for illustrative purposes only and may slightly differ in appearance, colour, size, etc. from the actual product. The description, illustrations, etc. in this document may subject to change in accordance with the latest product specification and performance. Should the above-mentioned change in the document become necessary, the document may be updated without written notice.

Version 2.1