


5753RK

Creative Touch 5-Series



- **Integrated Google Play Store**
- **Embedded 18W speakers and 8W subwoofers for impressive sound quality as well as 8 array Microphone**
- **Android 13 OS for improved multitasking & security**
- **Optional Sensor Box - NFC reader & air quality sensors**



Create. Connect. Inspire. Teacher led technology

Optoma's interactive displays are designed to fit the needs of teachers and students seamlessly. By listening to educators and gathering customer feedback, Optoma creates solutions that remove the challenging barriers facing teachers today. The result; intuitive user-friendly software to work in harmony with the way you educate - Create. Connect. Teach.

Google EDLA certification means a full library of Apps are at your disposal via the pre-installed Google Play Store.

Specifications

UPC: 796435 69 065 6, EAN: 5055387667884, Colour: Grey



Display	
Back light	Direct type LED
Size (diagonal)	75"
Resolution	3840(H)*2160(V) Pixel (UHD 4K)
Brightness	420 cd/m ²
Contrast ratio	5,000:1
Viewing angle	178°
Response time	8ms
Life	50,000 hours
Display colours	1.07
Speaker count	2
Watts per speaker	18W
Surface hardness	7H
Glass	Toughened, Anti-glare/Fingerprint / HAZE: 3-8%
Haze	3-8%
Ambient light sensor	Yes
Air gap	0.60mm
Pencil hardness	9H
Touch resolution	32768 x 32768

Physical spec	
Dimensions (W x D x H) mm	1709 x 86 x 1031
Wall-hanging screw spec	M8*25mm
VESA holes	800*400
In the box	European standard power cord (3m) American standard power cord (3m) U.K standard power cord (3m) USB cable (3m) USB-C cable (1.5m) HDMI cable (3m) 2x Writing Pen Remote control Battery Pen holder Quick start guide

Connections	Inputs 4 x HDMI 2.0, 1 x DisplayPort, 1 x Audio 3.5mm, 1 x S/PDIF, 1 x USB-A service, 4 x USB 3.0, 1 x RS232, 1 x RJ45, 2 x USB-C, 1 x OPS slot Outputs 1 x HDMI 2.0, 1 x Audio 3.5mm, 2 x USB-B interactive, 1 x RJ45
-------------	---

Operating conditions	0°C- 40°C
Net weight	51.4 kg
Gross weight	60.7 kg
Wireless - antenna	Optional Accessory
Wireless - technology	802.11ac/b/g/n/a/ax
Wireless - operating frequency	2.4Ghz/5GHz

Touch system	
System	Windows10/Windows8/Windows7/Windows XP /Linux/Mac (1 Touch point only)/Android/Chrome
Touch accuracy	1.00mm
Touch point	Up to 20 points touch and 40 points touch (Windows)
Touch tool	Finger, Passive infra-red pen
Pen/finger detection	Yes

Power	
Power supply	100-240V ~ 50/60Hz
Power consumption (standby)	0.5W
Power consumption (max)	494W
Power consumption - average (watts)	307
Power consumption - Energy Star (watts)	137

Operation System	
System version	Android 13
CPU	Octa-core (A76*4 + A55*4)
GPU	Mali G610 MC4
RAM	8GB
Storage	64GB
OSD / display languages	17 languages: Arabic, Czech, Danish, Dutch, English, French, German, Italian, Polish, Portuguese, Romanian, Russian, Chinese (simplified), Spanish, Swedish, Chinese (traditional), Turkish

