

## Lenovo ThinkVision S22i-30 Monitor

# Made for the modern workplace.

### So clear, you can see the difference



- See all your documents and spreadsheets in high detail on the ThinkVision S22i-30 with its 21.5-inch FHD screen.
- Easily collaborate with your team using the In-Plane Switching (IPS) display's wide-viewing angles.
- Work content looks rich and smooth with the monitor's 99% sRGB color space coverage, 1000:1 contrast ratio, and 75 Hz refresh rate.
- Leverage our Natural Low Blue Light technology to reduce eye strain without experiencing any color distortion.

### Professionally designed for professional work

- Add to your desk's aesthetic with ThinkVision S22i-30's slim, 3-side NearEdgeless design and upgraded cable management.
- Enjoy a modern work experience with the integrated flexible phone holder and joystick control to change monitor settings.
- Keep up with all professional commitments while doing your part for the environment with the monitor's recyclable cushion packaging.

### Ample connectivity that powers productivity

- Connecting to any input device becomes hassle-free with the availability of both VGA and HDMI ports.
- Experience higher flexibility with the monitor's VESA compatibility.
- Adjusting the monitor to suit your ergonomics becomes simpler with the easy-to-assemble tilt stand.



### Display

**Panel Size**  
21.5-inch

**Screen Dimensions**  
488.0 mm x 290.3 mm

**Panel Type**  
3-side NearEdgeless,  
In-Plane Switching

**Active Area**  
476.1 mm x 267.8 mm

**Backlight**  
WLED

**Aspect Ratio**  
16:9

**Resolution**  
1920 x 1080

**Pixel Pitch**  
0.2480 mm x 0.2480 mm

**Dot/Pixel Per Inch (DPI/PPI)**  
102

**Viewing Angle (H x V @ CR 10:1)**  
178° / 178°

**Response Time**  
4ms (Extreme Mode),  
6ms (Normal Mode)

**Refresh Rate**  
75 Hz

**Brightness (Typical)**  
250 cd/m<sup>2</sup>

**Contrast Ratio (Typical)**  
1000:1

**Dynamic Contrast Ratio (Typical)**  
3M:1

**Color Gamut (Coverage Ratio)**  
99% sRGB (CIE 1931)

**Color Support (Typical)**  
16.7 Million

**Color Depth**  
8-bit (6+FRC)

**Anti-glare**  
Yes

### Connectivity

**Video Signal**  
1 x HDMI 1.4<sup>1</sup>  
1 x VGA

**Audio Signal**  
1 x Audio Out (3.5 mm)

### Special Features

**Natural Low Blue Light**  
Yes

### Power

**Power Consumption (Typ. / Max)**  
15.1W / 21.0W

**Power Consumption Sleep/Off Mode**  
< 0.5W

**Power Consumption Switch-Off Mode**  
< 0.3W

**ENERGY STAR Power Consumption (Pon / E<sub>TEC</sub>)**  
13.1W / 42.6kWh

**Power Supply**  
Internal

**Voltage Required**  
AC 100 to 240 V (50-60 Hz)

### Mechanical

**Tilt Angle (Front / Back)**  
-5° / 22°

**VESA Mount Capability**  
Yes (100 x 100 mm)

**ThinkCentre M Series Tiny Support<sup>2</sup>**  
Yes, by 4XFON03161

**Kensington Lock Slot**  
Yes (2.5 mm x 6 mm)

**Cable Management**  
Yes

**Bezel Color**  
Raven Black / Storm Grey

**The Minimum Thickness of Head**  
6.9 mm

**Bezel Width (Side)**  
1.5 mm

**Bezel Width (Top)**  
1.5 mm

**Bezel Width (Bottom)**  
22.0 mm

### Dimension

**Size Packed (W x D x H, mm/inch)**  
580.0 x 115.0 x 355.0 mm  
22.83 x 4.53 x 13.98 inches

**Size Unpacked w/ Stand (Highest Position) (W x D x H, mm/inch)**  
488.0 x 182.9 x 408.6 mm  
19.21 x 7.20 x 16.09 inches

**Size Unpacked w/ Stand (Lowest Position) (W x D x H, mm/inch)**  
488.0 x 182.9 x 408.6 mm  
19.21 x 7.20 x 16.09 inches

**Size Unpacked w/o Stand (Head Only) (W x D x H, mm/inch)**  
488.0 x 41.0 x 297.3 mm  
19.21 x 1.61 x 11.70 inches

**Weight Packed (kg / lb)**  
4.6 kg / 10.1 lbs.

**Weight Unpacked (kg / lb)**  
3.1 kg / 6.8 lbs.

**Weight (Monitor Head Only) (kg / lb)**  
2.3 kg / 5.1 lbs.

### What's in the Box

**Monitor with Stand**  
Yes

**Power Cable (Cable Length)**  
1 x Power Cable (1.8 m)

**HDMI Cable (Cable Length)**  
1 x HDMI 1.4 Cable (1.8 m)

**Quick Setup Guide**  
Yes

**Tools**

1 x Screw

### Certification

**ENERGY STAR Certification**  
Yes

**TCO**  
9.0

**TCO Edge**  
2.0

**EPEAT**  
Gold

**Windows Certification**  
Windows 10, Windows 11

**EU Energy Level Certification**  
Yes (Level-E)

**China Energy Efficiency Standard**  
Tier 2

**TÜV Rheinland Eye Comfort**  
Eye Comfort 2.0

**TÜV Rheinland Low Blue Light**  
Yes

**TÜV Low Blue Light (Hardware Solution)**  
Yes

**Eyesafe Display Certification**  
Yes (Eyesafe 2.0)



<sup>1</sup> Supports 1920 x 1080 @ 75 Hz as specified in HDMI 1.4. | <sup>2</sup> Sold separately.