



Modern 15

MODERN 15 B12M-454US

Specification

Manufacturer Part #	MOD1512454
OS	Windows 11 Home
	(MSI recommends Windows 11 Pro for business)
СРИ	Intel® Core™ i7-1255U
CPU Speed	1.7 - 4.7GHz
Chipset	
Color	Classic Black
Screen Size	15.6" FHD, 60Hz 45%NTSC IPS-Level
Resolution	1920x1080
	16:9
GPU	Intel® Iris® Xe
Keyboard	White backlight keyboard (99 Key)
Speaker	2x Speakers 2W
Memory	16GB (16GB*1)
	DDR4 3200MHz Onboard
HDD Capacity	512GB NVMe SSD
HDD Interface	NVMe
LAN	
WLAN	Intel Wi-Fi 6 AX201(2*2 ax)
Bluetooth	BT 5.2
Card Reader	Micro SD
Webcam	720p HD Webcam
USB	1x USB 3.2 Gen 2; 2x USB 2.0
Type-C Port	1x USB 3.2 Gen 2 Type C
Video Port	HDMI 1.4 (4K @ 30Hz)
Audio Port	Mic-in/Headphone-out Combo
AC Power Adaptor	65W [DC-in]
Battery Pack	3 cell (39.3Whr) Li-Polymer
Dimension	14.13" x 9.49" x 0.78"
Weight	3.85 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)