



## SPECIFICATIONS


面板尺寸	24.5"
最佳解析度	1920 x 1080 (FHD)
更新頻率	100Hz
反應時間	1ms (MPRT) / 4ms (GTG)
面板類型	IPS
亮度	300 cd/m2
可視角度	178°(H) / 178°(V)
螢幕比例	16:9
靜態對比度	1000:1
sRGB	103% (CIE 1976)
顯示區域(MM)	543.744(H) x 302.616(V)
像素 (H X V)	0.2832(H) x 0.2802(V)
表面處理	Anti-glare
色彩顯示	16.7M
COLOR BIT	8 bits (6 bits + FRC)
影像連接埠	1x HDMI™ 1.4b (FHD@100Hz) 1x DisplayPort (1.2a) 1x D-Sub (VGA)
音頻接孔	1x Line-in
肯辛頓鎖孔	Yes
SPEAKER	2x 3W
VESA安裝	75 x 75 mm
電源規格	External Adaptor (12V 2.5A)
HDR SUPPORT	HDR Ready
電源輸入	100~240V, 50~60Hz
調整 (仰角)	-5° ~ 20°
調整 (左右旋轉)	-45° ~ 45°
調整 (垂直旋轉)	-90° ~ 90°
調整 (高度)	0~130 mm
尺寸 (寬X高X深)	560 x 411.5 x 227 mm (22.05 x 16.2 x 8.94 inch)
紙箱尺寸 (寬 X 高 X 深)	632 x 415 x 125 mm (24.9 x 16.4 x 4.9 inch)
重量	2.7 kg (5.95 lbs) / 5.05 kg (11.14 lbs)
影像輸出兼容性	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook
	* All trademarks and the registered trademarks are the property of their respective owners.

## FEATURES

- Anti-Flicker technology**  
MSI Anti-Flicker technology provides a very comfortable viewing experience by reducing the amount of screen flicker.
- Less Blue Light**  
Effectively reduce blue light which could cause serious long-term damage to your eyes.
- IPS Grade Panel**  
Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best while creating your own on-line video.
- VESA Mountable**  
To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.
- Built-In Speaker**  
Built-in speakers allow you to listen clearly without connecting external speakers.
- 100Hz High Refresh Rate**  
Experience smooth gaming with a blazing fast 100Hz refresh rate, that gives you the upperhand in fast moving games.
- EyesErgo**  
An eye care solution designed with ergonomics in mind.
- Eye-Q Check**  
Help have self-check eyes & remind to take a rest while using the monitor for a long time.
- Broadened Display**  
View your applications, spreadsheets and more with a perfect screen size for work desk that aligns with the visual's comfort zone.

認證	CB/CE Energy Star
ACCESSORIES	1x HDMI (1.4), 1x Power Cord, 1x Power Adaptor, 1x Quick Guide, 4x Stand Screw, 1x VESA Plate, 4x VESA Plate Screw
備註	HDMI™: 1920 x 1080 (Up to 100Hz) DisplayPort: 1920 x 1080 (Up to 100Hz) D-Sub (VGA): 1920 x 1080 (Up to 60Hz) Adaptive Sync Support

## CONNECTIONS



1. 1x DisplayPort (1.2a)
2. 1x HDMI™ 1.4b (FHD@100Hz)
3. 1x D-Sub (VGA)
4. 1x Line-in
5. 1x DC Jack
6. 1x 5-way Navigator
7. 1x Kensington Lock