

RoboSHOT 30E-M HD PTZ Camera **SKU: 999-21132-001W**

Specifications

Dimensions &
Measurements

Depth	6.75
Height	6.94
Operating Temperature	32° to 104°F (0° to 40°C)
Product Weight	4.85
Shipping Weight	5.9 kg (13 lbs)
Width	7.05

Characteristics &
Features

Browser-based User Interface for Remote Control	Built-in
Camera Type	PTZ
Color	White
Compatible With	Vaddio
Control Method	• IR Remote • Touch Screen • Web UI
Estimated Room Size	• Large Room • Medium Room
Field of View	70.2° Wide End to 3.1° Tele End
Field of View Wide	Greater than 70
Focus System	• Auto • Manual

Gain	• Auto • Manual
Image Sensor Type	1/2.5-type Exmor R CMOS sensor
Input Ports	• Network • USB 3.0
Invertible	Yes
Manufacturer	Vaddio
Max Resolution	1080p 60
Minimum Illumination	• 1 Lux (F1.6) • 100+ Lux Recommended
OneLINK Compatibility	No
Output Ports	• Network • USB 3.0 Type B
Pan and Tilt Range	• Pan: $\pm 150^{\circ}$ • Tilt: $+90^{\circ}$ to -30°
Pan and Tilt Speed	0.35°/sec - 120°/sec
Pixels	8.51 Megapixel (8.57 Total MP)
Power Cord	EU Cord, UK Cord
Power Supply	PoE+ Midspan Power Injector
Power Type	PoE+
Preset Positions	16 Custom Home Position
PTZ Motors	Silent BLDC Direct Drive Motors
Quick-Connect Compatibility	No
Signal Type	• USB 2.0 • USB 3.0
Solution Type	Camera Only
Special Features	Vaddio Special Offer

TAA Compliant	Yes
Tri-Sync Motion	Yes
UPC	840077508166
White Balance	• Auto • Manual • One Push
Zoom	30x zoom, 20x optical zoom + 10x IntelliZoom

Certifications & Warranties

Certifications	• CE • Certified for Microsoft Teams • FCC • RoHS • TAA • UL Listed
Warranty	3 years

Source: https://www.legrandav.com/products/cameras/hd_ptz_camera/roboshot-30e-m/999-21132-001w