



Poly Savi 8220 UC DECT 1920-1930 MHz Single Ear Headset TAA (8L7E2AA)



Overview

Speak with confidence. Enjoy hybrid freedom.

Hybrid workers, get ready for true wireless freedom. The portable, comfortable Poly Savi 8200 UC Series headset offers the ultimate in long-range DECT™ technology with USB plug-and-play convenience. These light, home- and office-ready headsets tune out nearby noise and keep every conversation secure, private, and clear with close conversation limiting noise cancellation. Wherever you work, the Savi 8200 UC Series keeps you sounding your best all day long.

Long-range wireless DECT™ technology up to 137 m/ 450 ft line of sight

Stay productive with the freedom to move with long-range wireless DECT™ technology up to 137 m/450 ft line of sight.

Connects to PC/Mac via D400 USB adapter

Plug-and-play connectivity to PC/Mac via universal D400 USB adapter.

Designed for portability: use at home and in the office

Designed to make hybrid work easier and more productive with portable design, included travel case and charge cable.

Three-way connectivity with Savi 8200 Office Series compatibility

Manage all your office calls with a compatible single base that offers 3-way connectivity—computer, desk phone, and mobile.[1]

Features

DECT™ security-certified headset

Privacy of your conversation is ensured: DECT™ Security-certified headset.

Noise-canceling microphone with close conversation limiting

Block background sounds with noise-canceling microphone and close conversation limiting.

Flexible microphone boom and positioning guides

Optimize your audio quality with flexible microphone boom and positioning guides.

Active noise canceling

Stay in the zone with active noise canceling.

SoundGuard DIGITAL Sound leveling and acoustic limiting

Optimal listening comfort with SoundGuard Digital sound leveling and acoustic limiting that protects against sounds above 118 dBA.

[1] Sold separately.

Specifications

Audio	Active noise cancellation (ANC)
Package weight	300 g
Battery life	>13 hours (talk time, over-the-head); >50 hours (standby time)
Special features	Adjustable headband
UPC number	197497815078
Manufacturer Warranty	Poly standard two-year limited warranty
What's in the box	Charging stand; Wireless headset; USB charging cable; Travel case; USB Type-A DECT™ adapter; USB Type-A to USB Type-C® adapter

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Battery type	Rechargeable Li-ion polymer
Button user controls	Power on/off; Call answer/end; Mute; Volume +/-; ANC: off, low, high
Cartons per layer	10
Cartons per pallet	80
Certified collaboration software	Zoom
Charge time	3 hours
Color	Black
Connection type	DECT™
Connects to	PC
Country of origin	Made in Mexico
ECCN	5A992
Ear cushions	PC (polycarbonate) (surface material)
HTS code	8517620090
Headphone type	On-ear (stereo)
Impedance	32 ohms
Indicator light	On call
Management Software	Plantronics Hub (desktop)
Microphone bandwidth	35 Hz to 21 kHz
Microphone type	Omnidirectional
Multiple order quantity	1
Package dimensions (W x D x H)	7.48 x 8.26 x 2.16 in
Package weight	0.66 lb
Paired devices	Up to 2
Pallet (layers)	8
Pallet dimensions	40 x 48 x 58.66 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 149 cm
Pallet weight	787.05 lb
Pallet weight	357 kg
Products per pallet	400
Products per pallet layer	50
Sensitivity (microphone)	-40 +/-3 dB
Signal-to-noise ratio	>53 dB

Speaker size	32 mm
Supported bluetooth profiles	AVRCP 1.6
UNSPSC code	43191638
Voice alerts	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low
Wireless range	Up to 180 m in open area; Up to 55 m in typical office environment
Wireless range (imperial)	Up to 590 ft in open area; Up to 180 ft in typical office environment

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

Hybrid Work Solutions

Audio

★ : Recommended

Audio Accessories

Poly APA-23 Electronic Hookswitch TAA	85Q50AA
Poly APA-24 Electronic Hookswitch TAA	85Q52AA
Poly APC-43 Electronic Hookswitch (Bagged) TAA	85Q56AA
Poly APC-43 Electronic Hookswitch TAA	85Q55AA
Poly APC-45 Electronic Hookswitch TAA	85Q57AA
Poly APC-82 Electronic Hookswitch TAA	8H981AA
Poly APD-80 Electronic Hookswitch TAA	85Q58AA
Poly APN-91 Electronic Hookswitch TAA	85Q59AA
Poly APP-51 Electronic Hookswitch TAA	85Q60AA
Poly APS-11 Electronic Hookswitch TAA	85Q78AA
Poly APT-31 Electronic Hookswitch TAA	85Q84AA
Poly APU-72 Electronic Hookswitch TAA	85Q95AA
Poly APU-75D Electronic Hookswitch TAA	85Q99AA
Poly APU-76 Electronic Hookswitch TAA	85R00AA
Poly APV-63 Electronic Hookswitch TAA	85R01AA
Poly APV-66 Electronic Hookswitch TAA	85R02AA
Poly EHS 3.5mm to 3.5mm Cable	85R17AA
Poly HL10 Extended Arm	8L554AA
Poly HL10 Handset Lifter	784Q1AA
Poly HL10 Handset Lifter TAA	8R713AA
Poly HL10 Handset Lifter with Straight Plug TAA	784Q2AA
Poly HL10 Lifter Arm +Ring Detector Accessory	8A7E3AA
Poly RD-1 Electronic Hookswitch	85R71AA
Poly Savi 7410/7420 Office Charging Cradle	8L556AA
Poly Savi 8200 5 Unit Charge Base	85R34AA
Poly Savi 8200 Leatherette Ear Cushions (2 Pieces)	85Q63AA
Poly Savi 8200 USB-A Headset Charging Cable	85R35AA
Poly Savi 8210 Battery with Removal Tool	85R37AA
Poly Savi 8210 Monaural DECT 1880-1900 MHz Top +Charging Cradle	8Y9C3AA
Poly Savi 8210 Top and Charging Cradle	85T30AA

Poly Savi 8210/8220 Universal Power Supply -9V 500mA	783M9AA
Poly Savi 8220 Battery with Removal Tool	85R39AA
Poly Savi 8220 Stereo DECT 1880-1900 MHz Top +Charging Cradle	8Y9C4AA
Poly Savi 8220 Top and Charging Cradle	85T31AA
Poly Savi 8240/8245 Battery	85R41AA
Poly Savi 8240/8245 Deluxe Charging Cradle	85R44AA
Poly Savi 8240/8245 Fit	85R45AA
Poly Savi 8240/8245 Foam Sleeves for Earloop (20 Pieces)	85Q65AA
Poly Savi 8240/8245 Standard Charging Cradle	85R47AA
Poly Savi 8240/8245 USB-A Charging Cable for Headset and Battery	85R43AA
Poly Savi 8245 Deluxe Cradle with Battery	85R49AA
Poly Savi 8245 Headset Cradle and Wearing Accessories	85T32AA
Poly Savi 8400/7400 Office DECT 1880-1900 MHz Base	8L569AA
Poly Savi 8400/7400 Office DECT 1920-1930 MHz Base	8L571AA
Poly Savi 8400/7400 Office Microsoft Teams Certified DECT 1880-1900 MHz Base	8L558AA
Poly Savi 8400/7400 Office Microsoft Teams Certified DECT 1920-1930 MHz Base	8L562AA
Poly Savi 8410/8420 Office Charging Cradle	8L573AA
Poly Savi 8440/8445 Office Charging Cradle	8L577AA
Poly Savi D400 UC DECT 1880-1890 MHz Dongle	8J8V9AA
Poly Savi D400 UC DECT 1880-1900 MHz Dongle	8J8V7AA
Poly Savi D400 UC DECT 1893-1906 MHz Dongle	8J8V6AA
Poly Savi D400 UC DECT 1910-1920 MHz Dongle	8J8V8AA
Poly Savi D400 UC DECT 1920-1930 MHz Dongle	85T33AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1880-1900 MHz Dongle	8J8W1AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1893-1906 MHz Dongle	8J8W0AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1910-1920 MHz Dongle	8J8W2AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1920-1930 MHz Dongle	85T34AA
Poly Savi Hard Case	85R51AA
Poly Savi Office Power Supply with Right Angled Plug -9V 1000mA	8L5A2AA
Poly Savi Office S2 Telephone Cable	85R55AA
Poly Savi Office Straight Plug Online Indicator	85R52AA
Poly Savi Office Telephone Interface Cable	85R57AA
Poly Savi Office USB-A PC Connection Cable	85R54AA
Poly Savi Office Universal AC Power Supply with Straight Plug -9V 1000mA	85R59AA

Poly Savi Office Universal AC Power Supply with Straight Plug -9V 500mA	85R61AA
Poly Savi Universal Power Supply -9V 500mA	85R63AA
Poly Savi W8210/8220 Charging Cradle	85R65AA
Poly USB-A to USB-C Adapter	85Q48AA
Poly USB-C to USB-A Adapter	85Q49AA

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Aug 18, 2024 6:36 PM UTC+0000