

PERFORMANCE

Processor

Intel® Core™ i7-14700, 20C (8P + 12E) / 28T, Max Turbo up to 5.4GHz, P-core 2.1 / 5.3GHz, E-core 1.5 / 4.2GHz, 33MB

Graphics

Intel® Arc™ A310 LP 4GB GDDR6

Chipset

Intel® Q670 Chipset

Memory

2x 16GB UDIMM DDR5-5600

Memory Slots

Two DDR5 UDIMM slots, dual-channel capable

Max Memory^[1]

Up to 64GB DDR5

Storage

512GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Storage Support^{[2][3]}

Up to three drives, 1x 3.5" HDD + 1x 2.5" HDD + 1x M.2 SSD

- 3.5" HDD up to 2TB
- 2.5" HDD bay is only for customer self upgrade
- M.2 SSD up to 2TB each

Card Reader

None

Optical

DVD±RW

Audio Chip

High Definition (HD) Audio, Realtek® ALC623-CG codec

Speakers

1Wx1

Power Supply

260W 90%

DESIGN

Keyboard

USB Traditional Keyboard, Black, English

Mouse

USB Calliope Mouse, Black

Optional Bay

None

Expansion Slots

- One PCIe® 3.0 x16, low-profile, length ≤ 155mm, height ≤ 70mm
- One PCIe® 3.0 x1, low-profile, length ≤ 155mm, height ≤ 70mm
- Two M.2 slots (one for WLAN, one for SSD)

Case Color

Black

Stand

None

Dust Filter

None

Form Factor

SFF (8.2L)

Dimensions (WxDxH)^[4]

92.5 x 297.7 x 339.5 mm (3.6 x 11.7 x 13.4 inches)

Weight^[5]

Around 5.3 kg (11.7 lbs)

CONNECTIVITY

Ethernet

Integrated 100/1000M

WLAN + Bluetooth®

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3, vPro®

Front Ports

- 1x USB-C® (USB 5Gbps / USB 3.2 Gen 1), with 15W charging
- 4x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x headphone / microphone combo jack (3.5mm)
- 1x microphone (3.5mm)

Rear Ports

- 4x USB-A (Hi-Speed USB / USB 2.0)
- 1x HDMI® 2.1 TMDS
- 1x DisplayPort™ 1.4a (HBR2, DSC)
- 1x Ethernet (RJ-45)

Optional Rear Ports (configured)

None

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Fingerprint Reader

No fingerprint reader

Physical Locks

- Kensington® Security Slot™, 3 x 7 mm
- Padlock Loop

Smart Cable Clip

None

Chassis E-Lock

None

Chassis Intrusion Switch

None

MANAGEABILITY

System Management^[6]

Intel® vPro® Enterprise

SERVICE

Base Warranty

3-year, Onsite

Included Upgrade

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 3
- GREENGUARD®
- RoHS compliant
- TCO Certified 9.0

Mil-Spec Test

MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Solar Radiation, Contamination by Fluids, Salt Fog)

SOFTWARE

Operating System

Windows® 11 Pro, English

Bundled Software

None

ACCESSORIES

Bundled Accessories

None

MODEL

TopSeller : Yes **Announce Date** : 2024-07-30

EAN / UPC / JAN : 198154814571 **End of Support** : 2030-11-15

Note:

[1] The max memory is based on the test results with current Lenovo memory offerings.

[2] The max capacity of each disk type is based on the test results with current Lenovo storage offerings.

[3] 2.5" HDD bay is optional part, only for customer self upgrade purpose and the hard drive is sold separately. Two onboard SATA ports support up to two drives of 2.5" HDD, 3.5" HDD and ODD.

[4] The system dimensions may vary depending on configurations.

[5] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[6] Intel vPro offers a superset of DASH's defined capabilities.

· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to

<https://psref.lenovo.com/Detail/2459?M=12U3001JUS>

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Kensington MicroSaver 2.0 Cable Lock from Lenovo

4XEON80914

Protect your device. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...

Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39202)
BETTER	3Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39468)
GOOD	3Y Premier Support Upgrade from 3Y Onsite (5WS0U26647)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference