

HP Elite t755 Thin Client (AF9B3UT)



Overview

Optimal thin client performance, reliability, and security

Enable productivity with the performance and reliability of the HP Elite t755 Thin Client, featuring advanced security from both cyber- and physical-based attacks for IT peace of mind. Built to support demanding performance with the progressive 6-core 45w AMD Ryzen™ V2546 Processor[1], helping users tackle mission-critical tasks.

Unleash maximum performance

Elevate efficiency with the progressive 45w AMD Ryzen™ V2546 Processor.[1] Optimized for mission-critical workflows, this fast-performing processor supports seamless productivity.

Built for mission-critical work

Empower your workforce with thin clients well-equipped with industrial-grade components for reliability and longevity while delivering a seamless user and management experience. Future-ready with expanded peripheral support and device management options.

Comprehensive security

Fortify critical security apps, data, and projects at the endpoints, wiping out data after each thin client log-in session. Get advanced protection from remote cyber- and physical attacks with a read-only OS and physical intrusion detection.

Help protect our shared future

The HP Elite t755 Thin Client uses at least 50 percent post-consumer recycled plastics, the keycaps contain 50 percent PCR DVDs[2], and the outside box and cushions are 100 percent sustainably sourced or recycled.[3]

[1] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. AMD's numbering is not a measurement of clock speed.

[2] 100 percent outer box packaging made from sustainably sourced certified and recycled fibers. Fiber cushions made from 100 percent recycled wood fiber and organic material. Any plastic cushions are made from >90% recycled plastic.

[3] Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 standard.

Specifications

Operating system	IGEL OS
Processor	AMD Ryzen™ Embedded V2546 (up to 3.95 GHz max boost clock, 8 MB L3 cache, 6 cores, 12 threads)
Memory	16 GB DDR4-3200 MHz RAM (2 x 8 GB)
Memory Slots	2 SODIMM
Internal Storage	256 GB PCIe® NVMe™ SSD
Graphics (discrete)	AMD Radeon™ RX 6300 Graphics (2 GB GDDR6 dedicated)
Graphics	Integrated
Graphics (integrated)	AMD Radeon™ Graphics
Audio	Internal amplified speaker system for basic audio playback
Minimum dimensions (W x D x H)	5 x 21 x 21 cm (Vertical orientation.)
Minimum dimensions (W x D x H)	1.97 x 8.26 x 8.26 in (Vertical orientation.)
Weight	1.4 kg (Weight will vary depending on configuration.)
Weight	3 lb (Weight will vary depending on configuration.)
Keyboard	HP 125 Wired Keyboard
Pointing device	HP 125 Wired Mouse
Ports	1 USB Type-C® 10Gbps signaling rate; 2 USB Type-A 5Gbps signaling rate
Expansion slots	1 half-height PCIe x16 (x8)
Ports	2 USB Type-A 5Gbps signaling rate; 2 USB 2.0 Type-A; 4 DisplayPort™ 1.2; 1 RJ-45; 1 4.5 mm power adapter; 1 security lock slot
Protocols	Amazon WorkSpaces through PCoIP; Citrix® HDX; Citrix® ICA; VMware Horizon® View™ through RDP/PCoIP, and Blast Extreme; Remote Desktop Services Remote FX (RFX), RDP; Azure Virtual Desktop; Windows 365
Power	90 W smart external power adapter
Ecolabels	EPEAT® registered
Energy star certified	ENERGY STAR® certified
Browser supported	Mozilla Firefox (for models with HP ThinPro); Microsoft Edge (for models with Windows 10 IoT Enterprise LTSC 2021)
UPC number	(ABA) 198701413264; (ABC) 198701122043

Additional specifications

Datasheet photo 1	AHID/51b294c061b0d7ad7905c27166bdf71b97750e75
ECC memory	non-ECC
Graphics card brand	AMD
Graphics card family	Radeon™
Graphics card memory size	2
Graphics card memory size uom	GB
Graphics card memory type	GDDR6
I/O Port location	Front
I/O Port location	Back
Keyboard connectivity	Wired
Memory layout (slots & size)	2 x 8 GB
Memory module type	DIMM
Memory size	16
Memory size uom	GB
Memory speed	3200
Memory speed uom	MHz
Memory type	DDR4
Model Number	RX 6300
Number of memory slots	2
Processor Brand	AMD
Processor cache	8 MB L3
Processor core	6
Processor family	Ryzen™
Processor maximum frequency	3.9
Processor maximum frequency uom	GHz
Processor threads	12
Software included	HP Device Manager
Software included	HP User State Tool
Software included	Microsoft SCCM/EDM Agent
Software included	HP ThinUpdate
Software included	HP Smart Zero Client Services
Software included	HP True Graphics
Software included	HP Easy Shell

Software included	HP Easy Update
Software included	HP USB Port Manager
Software included	HP Write Manager
Software included footnote number	[6,12,15]
Software included footnote number	[6,12,15]
Software included footnote number	[6,12,15]
Software included footnote number	[6,12,15]
Software included footnote number	[6,12,15]
Software included footnote number	[6,12,15]
Software included footnote number	[6,12,13,15]
Software included footnote number	[6,8,12,15]
Software included footnote number	[6,11,12,15]
Software included footnote number	[6,12,15]
Standard memory note	Transfer rates up to 3200 MT/s.
Storage capacity	256
Storage capacity uom 01	GB
Storage interface 01	PCIe®
Storage interface protocol 01	NVMe™
Storage type	SSD
Storage type 01	SSD
UNSPSC code	43211506

Accessories for PC

Components/Upgrades

★ : Recommended

Graphics

AMD Radeon RX 6300 2 GB GDDR6 FH DP+HDMI PCIe x16 Graphics	7Y6P7AA
--	---------

Memory

HP 16GB DDR4-3200 SODIMM	13L75AA
--------------------------	---------

HP 16GB DDR4-3200 SODIMM	13L75AT
--------------------------	---------

HP 8GB DDR4-3200 SODIMM	13L77AA
-------------------------	---------

Internal ports/Modules/Controllers

HP PCIe x1 Parallel Port Card	N1M40AA
-------------------------------	---------

HP PCIe x1 Parallel Port Card	N1M40AT
-------------------------------	---------

HP USB to Serial Port Adapter	J7B60AA
-------------------------------	---------

Intel I226-T1 2.5GbE Ethernet Network Adapter	9P1U8AA
---	---------

Keyboards/Other Input Devices

Wired Keyboards

HP 125 Wired Keyboard	266C9AA
-----------------------	---------

HP Wired Desktop 320K Keyboard	9SR37AA
--------------------------------	---------

HP Wired Desktop 320K Keyboard	9SR37UT
--------------------------------	---------

Wired Combo

HP 225 Antimicrobial Wired Mouse and Keyboard Combo	286K3AA
---	---------

HP 225 Wired Mouse and Keyboard Combo	286J4AA
---------------------------------------	---------

HP Wired Desktop 320MK Mouse and Keyboard	9SR36AA
---	---------

HP Wired Desktop 320MK Mouse and Keyboard	9SR36UT
---	---------

Wireless Combo

HP 235 Wireless Mouse and Keyboard Combo	1Y4D0AA
--	---------

HP 235 Wireless Mouse and Keyboard Combo	1Y4D0UT
--	---------

HP 655 Wireless Keyboard and Mouse Combo	4R009AA
--	---------

HP 655 Wireless Keyboard and Mouse Combo	4R009UT
--	---------

HP 655 Wireless Keyboard and Mouse Combo (Bulk 10)	4R009A6
--	---------

HP Wireless Rechargeable 950MK Mouse and Keyboard

3M165AA

Wireless Keyboards

HP 455 Programmable Wireless Keyboard

4R177A6

HP 455 Programmable Wireless Keyboard

4R177AA

HP 975 Dual-Mode Wireless Keyboard

3Z726AA

HP 975 Dual-Mode Wireless Keyboard

3Z726ET

Mice/Pens/Other Pointing Devices

Wired Mice

HP 125 Wired Mouse

265A9AA

HP 125 Wired Mouse

265A9AT

HP 125 Wired Mouse

265A9UT

HP 125 Wired Mouse (Bulk120)

265A9A6

HP 128 LSR WRD Mouse (Bulk120)

265D9A6

HP 128 Laser Wired Mouse

265D9AA

HP 155 Wired Mouse

5B8B7AA

HP Wired Desktop 320M Mouse

9VA80AA

HP Wired Desktop 320M Mouse

9VA80UT

Wireless Mice

HP 435 Multi-Device Wireless Mouse

3B4Q5AA

HP 635 Multi-Device Wireless Mouse

1D0K2AA

HP 635 Multi-Device Wireless Mouse

1D0K2ET

HP 715 Rechargeable Multi-Device Mouse

6E6F0AA

HP 715 Rechargeable Multi-Device Mouse

6E6F0ET

HP 715 Rechargeable Multi-Device Mouse

6E6F0UT

HP 925 Ergonomic Vertical Mouse

6H1A5AA

HP 925 Ergonomic Vertical Mouse

6H1A5ET

HP 935 Creator Wireless Mouse

1D0K8AA

HP 935 Creator Wireless Mouse

1D0K8ET

HP 935 Creator Wireless Mouse

1D0K8UA

HP Wireless Premium Mouse

1JR31AA

HP Wireless Premium Mouse

1JR31UT

Video Devices

Video Devices

HP 325 FHD Webcam	53X27AA
HP 325 FHD Webcam	53X27PT
HP 435 FHD Webcam	77B10AA
HP 965 4K Streaming Webcam	695J5AA

Port Replicators/Dongles/Docking

Port Replicators

HP 4K USB-C Multiport Hub	6G842AA
HP 4K USB-C Multiport Hub	6G843AA
HP 4K USB-C Multiport Hub	6G843UT
HP USB-C to USB-A Hub	Z6A00AA
HP Universal USB-C Multiport Hub	50H55AA
HP Universal USB-C Multiport Hub	50H55PT
HP Universal USB-C Multiport Hub	50H55UT
HP Universal USB-C Multiport Hub	50H98AA

Cables/Cable Adapters/Dongles

HP DisplayPort Cable Kit	VN567AA
HP DisplayPort To VGA Adapter	AS615AA
HP DisplayPort To VGA Adapter	F7W97AA
HP DisplayPort to DVI-D Adapter	FH973AA
HP DisplayPort to HDMI True 4K Adapter	2JA63AA
HP Pavilion USB-C to HDMI 2.0 Adapter	2PC54AA
HP USB 3.0 to Gigabit RJ45 Adapter G2	4Z7Z7AA
HP USB-C to DP Adapter	N9K78AA
HP USB-C to HDMI 2.0	1WC36AA
HP USB-C to RJ45 Adapter G2	4Z527AA
HP USB-C to RJ45 Adapter G2	4Z534AA
HP USB-C to USB 3.0 Adapter	N2Z63AA
HP USB-C to VGA Adapter	N9K76AA
HP USB-C to VGA Display Adapter	P7Z54AA

Docking

HP USB-C Dock G5	26D32AA
------------------	---------

HP USB-C Dock G5	5TW10AA
HP USB-C Dock G5	5TW10ET

Audio Devices

PC Speakers

HP Bluetooth Speaker 365	567D3AA
--------------------------	---------

Headset Devices

HP Stereo 3.5mm Headset G2	428H6AA
HP Stereo 3.5mm Headset G2	428K7AA
HP Stereo 3.5mm Headset G2	428K7PT
HP Stereo USB Headset G2	428H5AA
HP Stereo USB Headset G2	428K6AA
HP Stereo USB Headset G2	428K6PT

Stands/Mounting Brackets

Mounting Brackets

HP Quick Release Bracket 2	6KD15AA
HP Quick Release Bracket 2	6KD15AT
Thin Client Recessed VESA Spacer Bulk Kit	1R2G8A6

Disclaimer — Copyright

Bluetooth is a trademark of its proprietor, used by HP Inc. under license. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. Bluetooth is a trademark of its proprietor and used by HP Inc. under license. AMD and Radeon are trademarks of Advanced Micro Devices, Inc.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Aug 09, 2024 1:08 PM UTC+0000