



L A P T O P S

Raider GE68 HX

RAIDER GE68HX 13VG-068US

Specification

Manufacturer Part #	RAIDERGE6813068
OS	Windows 11 Home (MSI recommends Windows 11 Pro for business)
CPU	Intel® Core™ i9-13950HX
CPU Speed	2.2-5.5 GHz
Chipset	-
Color	Black
Screen Size	16" QHD+, Wide View Angle 240Hz Thin Bezel, 100% DCI-P3
Resolution	2560x1600 16:10
GPU	NVIDIA® GeForce RTX™ 4070 Laptop GPU
Video Memory	8G GDDR6
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (84 Key)
Speaker	Sound by Dynaudio, 4x2W Speaker
Memory	32GB (16GB*2) DDR5 5600MHz
HDD Capacity	1TB NVMe SSD Gen4x4
HDD Interface	NVMe
LAN	Killer E3100G
WLAN	Killer WiFi 6E AX1675(i)
Bluetooth	BT 5.3
Card Reader	SD7.0
Webcam	1080p FHD with shutter
USB	2x USB 3.2 Gen 2
Type-C Port	1x Thunderbolt™ 4 w/DP; 1x USB 3.2 Gen 2/DP, 1x USB 3.2 Gen 2/DP&PD
Video Port	HDMI v2.1,
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	280W
Battery Pack	4 cell (99.9Whr) Li-Ion
Dimension	14.06"x 11.18"x 1.10"
Weight	5.95 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)