

NEXSYS™ 1000VA, 15 Amp Online UPS Backup Power System, Bank Outlet Control **SKU: UPX-OL1000R-2**



NEXSYS is built on a promise that we've kept for over two decades – more than half the life of the company – that our power products are designed, engineered, and built for AV. It's one thing to say it, it's another thing to prove it. And our NEXSYS Online UPSs prove it, we promise. They are built with premium components to keep your AV systems running as smoothly as you'd expect.

- 8 Outlets with Bank Control
- (2) outlet banks with 4 outlets each
- 1000VA and 15 Amp
- **An Out-of-Box(y) Experience.** Everything is assembled and connected right from the factory saving you time during your installations
- Rack ears are pre-installed with the “4-Post” mounting brackets ready to be rack mounted even if you have a 3rd pair of rackrail
- The battery is already connected so just plug it in
- **Customization is a Breeze.** The NEXSYS Power Management Software on your PC allows you to customize and configure various settings and notifications if you don’t like our default settings - we won’t be offended
- **Pure Power.** All NEXSYS Online Double Conversion UPSs have a Pure Sine Wave output providing the cleanest power to your connected equipment, especially the most sensitive equipment
- **No time to wait.** Absolute zero transfer time because the connected equipment is ALWAYS powered from the battery. Keep in mind, that batteries in Online UPSs do need to be replaced more frequently, but NEXSYS will give you the heads up when that time comes.
- **“NEXSYS, alert me when...”** Set reminders or notifications for things like battery replacement, etc. via email or on the UPS
- **Swap it like it’s hot.** Hot-swappable battery from the front access panel for easy service without disrupting the system
- The IEC Input allows for better cable management of the power cord if shorter or longer cords are required
- Includes a 6’ (1.8m) SignalSAFE™ IEC power cord
- Energy Star Certified
- The ONLY Online UPS with Energy Star in the AV market
- U.S. Department of Energy Compliant for energy efficiency

Specifications

Dimensions & Measurements

AC Voltage Output	110-127 VAC
Amps	15 Amp
Cord Length	1.83 m (6 ft)
Depth	40.64 cm (16 in)
Height	8.89 cm (3.5 in)
Mounting Depth Max	86.36 cm (34 in)
Mounting Depth Min	22 in
Operating Temperature	32° - 104°F (0° - 40°C)
Product Weight	15.01 kg (33.1 lbs)
Shipping Weight	17.43 kg (38.4 lbs)
VA Rating	1000VA
Watts	1000 W
Width	48.26 cm (19 in)

Characteristics & Features

Color	Black
Mounting Points	4
Network Card Included	No
Network Enabled	Yes
Outlet Control Type	Bank
Outlet Count	8
Plug Type	NEMA 5-15P
Receptacle Type	NEMA 5-15R
TAA Compliant	No
Topology	Online
UPC	656747397806

Certifications & Warranties

Certifications

- CSA
- cTUVus
- Department of Energy
- Energy Star 2.0
- FCC
- REACH
- RoHS

Source: https://www.legrandav.com/products/power/ups_backup_systems/nexsys-online-ups-backup-power-systems/upx-ol1000r-2