



SPECIFICATIONS

Panel Size	27" (69 cm)
Active Display Area (mm)	596.16(H) x 335.34(V)
Curvature	Flat
Panel Type	Rapid IPS
Panel Resolution	3840x2160 (UHD)
Pixel Pitch (H x V)	0.15525(H) x 0.15525(V)
Aspect Ratio	16:9
Brightness (nits)	400 Nits (Typ.)
Contrast Ratio	1000:1 (Typ.)
DCR	100000000:1
Signal Frequency	180~352KHz(H) / 48~160Hz(V)
ACTIVATED RANGE	48 to 160Hz
Refresh Rate	160Hz
Response time	0.5ms (GtG, Min.)
DYNAMIC REFRESH RATE TECHNOLOGY	AMD FreeSync™
HDR Support	VESA DisplayHDR 400
Video ports	1x DisplayPort (1.4a) 2x HDMI™ (2.1) 1x Type-C (DP alt.) w/ PD 15W charging
USB ports	N/A
Audio ports	1 x Headphone-out
Viewing Angle	178°(H) / 178°(V)
Adobe RGB / DCI-P3 / sRGB	93% / 98% / 133%
Surface Treatment	Anti-glare
Display Colors	1.07B (8bits + FRC)
Power Type	External Adopter 19V 3.42A
Power Input	100-240V~ 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	-30° ~ 30°
Adjustment (Pivot)	-90° ~ 90°
Adjustment (Height)	0 ~ 130 mm
Kensington Lock	Yes
Dimension (W x D x H)	613.5 x 227.8 x 406.6 mm
Carton Dimension (W x H x D)	847 x 145 x 491 mm 862 x 158 x 515 mm (outer box)
Frameless Design	Yes

FEATURES



Rapid IPS

Make sure the intensity and purity of colors when gaming.



Ultimate 4K gaming

Enjoy the extreme fluid gaming and astonishing details with 4K (3840 x 2160) resolution at 160Hz high refresh rate.



Adjustable Stand

Make tilt and height adjustments effortlessly to optimize the monitor's position for enhanced ergonomics.



Frameless Design

With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.



Console Mode

Perfectly support 120Hz at QHD 2K resolution with next-gen console like PS5 and Xbox series X/S.

VESA CERTIFIED



VESA DisplayHDR True Black 400

It has passed the VESA DisplayHDR True Black 400 Certification, meaning it can provide a display with the most realistic colors.

PIP / PBP Function	Yes
VESA Mounting	75 x 75 mm
Weight (NW / GW)	6.4 / 8.8kg
Note	DisplayPort: 3840 x 2160 (Up to 160Hz) Type C (DP alt.): 3840 x 2160 (Up to 160Hz) HDMI™: 3840 x 2160 (Up to 160Hz) Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

CONNECTIONS



1. 5-Way Joystick Navigator
2. DC Jack
3. Headphone Out
4. 2 x HDMI™ (2.1)
5. 1 x DisplayPort (1.4a)
6. USB Type-C (PD15W)
7. Kensington Lock