



Exceptional efficiency and premium black & white laser performance for small offices

Monochrome Laser All-in-One Printer

Exceptionally efficient, Brother MFC-L2900DW Wireless Compact Monochrome (Black & White) All-In-One Laser Printer is an affordable solution for high-volume printing, copying, scanning and faxing.

- Printing up to 36ppm¹
- 3.5" touchscreen enables printing from and scanning to Cloud-based apps⁶
- 50-page Automatic Document Feeder with Single Pass Duplex Copy and Scan¹²
- Built-in dual band wireless module (2.4GHz / 5GHz), Ethernet and mobile device printing⁷
- Refresh EZ Print Subscription Ready

MFC-L2900DW

Advance Specification Sheet

brother
at your side

Specifications:

Print	
Print Technology	Electrophotographic Laser
Simplex Print Speed (max.) ¹	Up to 36ppm
Time to First Page ²	Less than 6.9 seconds
Print Resolution (max.)	Up to 1200 x 1200 dpi
Print Emulations	PCL6, BR-Script ³ , PDF Version 1.7
Scan	
Scan Speeds (max.) ⁴	Up to 23.6ppm / 7.9ppm (black / color)
Scan Resolution (max.)	ADF (optical): Up to 600 x 600 dpi Glass (optical): Up to 1200 x 1200 dpi Interpolated: Up to 19,200 x 19,200 dpi ⁵
Scan To Capability	PC (Image, Email, OCR, File), Network Folder ⁶ , Email Server ⁶ , SharePoint ⁶ , FTP, Cloud Services ⁶ , Mobile Devices ⁶ , Easy Scan to Email ⁶
Advanced Scanning Features	Auto deskew, File split, Multi-page to single-page, Base color removal, Scan Profiles
Duplex Scan	Yes
Copy	
Copy Speed / Copy Resolution (max.)	Up to 36 cpm / Up to 600 x 600 dpi
Copy Options	Sorting, N-in-1, Multi-copying (up to 99), Reduce / Enlarge 25 - 400% in 1% increments
Duplex Copy	Yes
Fax	
Fax Features	33.6K bps modem speed, Fax page memory: up to 400 pages ¹⁰ , Fax forward to: Network Folder ³ and Email, Internet Fax ⁹ , PC Fax ¹¹
Connectivity & Compatibility	
Standard Interfaces	Wireless 802.11b/g/n (2.4GHz) / 802.11a/n (5GHz), Ethernet, Hi-Speed USB 2.0
Operating Systems Compatibility ¹²	For the latest OS compatibility and to download drivers, visit support.brother.com.
Mobile Device Compatibility ⁸	AirPrint [®] , Mopria [®] , Brother Mobile Connect, Wi-Fi Direct [®]
Cloud Services ⁷	Google Drive [™] , Evernote [®] , OneDrive, OneNote, Dropbox, Box, SharePoint Online
Brother Cloud Apps ⁹	Easy Scan to Email, Scan to Mobile, Cloud Secure Print, Fax Forward to Cloud or Email, Scan to Searchable PDF, Scan to Word, Scan to Excel, Scan to PowerPoint, Email Print
Alexa Print	Yes
Security	
Security Features	Secure Function Lock, Enterprise Security (802.1x), TLS/SSL, IP Filter, SNMP v3, Secure Print, Setting Lock
Paper Handling	
Paper Input Capacity (max.) ¹³	250-sheets paper tray, Single-sheet manual feed slot
Output Capacity (max.) ¹³	100 sheets
Document Glass Size	Up to 8.5" x 11" (Letter)
Auto Document Feeder Capacity ¹³	50 pages
Paper Size	Standard Tray: Letter, Legal, Executive, A4, A5, A6, B5, B6, Folio Manual Feed Slot: Width 3" to 8.5", Length 5" to 14" Duplex: Letter, Legal, Folio
Media Types	Standard Tray: Plain Paper, Thin Paper, Thick Paper, Recycled Paper Manual Feed Slot: Plain Paper, Thin Paper, Thick Paper, Recycled Paper, Bond, Label, Envelope (single)
Media Weights	Standard Tray: 16 to 43 lbs ¹⁴ Manual Feed Slot: 16 to 61lb ADF: 16 to 28 lbs
General	
Automatic Duplex Capability	Print, plus single-pass copy / scan / fax
Display	3.5" Touchscreen
Customizable Shortcuts	18
Processor	600 MHz
Memory (std.)	256 MB
Included Software ⁸	Brother Mobile Connect for iOS [®] and Android [™] Brother iPrint&Scan (desktop) for Windows and Mac [®] BRAdmin Light, BRAdmin Pro, Status Monitor ⁵ , PaperPort [™] SE 14 ⁵
Refresh EZ Print Subscription Eligible	Yes
Energy Star [®] Qualified	Yes
EPEAT Certified	Yes (Silver Rated)
Maximum Monthly Duty Cycle ¹⁵	Up to 35,000 pages
Recommended Monthly Volume ¹⁶	Up to 2,500 pages
Warranty	1-year limited warranty

Replacement Supplies & Optional Accessories:



TN830	Standard Yield Toner Cartridge (1,200 pages) ¹⁷
TN830XL	High Yield Toner Cartridge (3,000 pages) ¹⁷
TN830V	Value High Yield Toner Cartridge (3,300 pages) ¹⁷
TN830XL 2PK	Twin Pack of High Yield Black Toner Cartridges (3,000 pages per cartridge) ¹⁷
DR830	Drum Unit (15,000 pages) ¹⁸

Dimensions / Weights:

Unit Dimensions / Weight	16.1" (W) x 16.6" (D) x 12.5" (H) / 25.9 lbs.
Carton Dimensions / Weight	23.6" (W) x 22.4" (D) x 17.1" (H) / 32.4 lbs.

Carton Contents:

Brother MFC-L2900DW, Starter Black Toner Cartridge (700 pages)¹⁷, DR830 Drum Unit (15,000 pages)¹⁸, AC Power Cord, Telephone Line Cord, Product Safety Guide, Reference Guide, Warranty Card, Quick Setup Guide



At your side support. One-year limited warranty with free online, live chat, or phone technical assistance for the life of your product.



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth.

COMPATIBLE WITH
WINDOWS



- Based on one sided printing. Change from default setting required.
- From ready mode and standard tray.
- BR-Script3 is PostScript®3™ compatible.
- Color and monochrome scan speeds in accordance with ISO/IEC 17991 with all advanced features turned off, using letter-sized paper at 200/300dpi.
- Windows only.
- Requires mail server support.
- Requires an Internet connection and an account with desired service.
- May require free download. Compatibility may vary by device and operating system. Requires connection to a wireless network.
- Requires an Internet connection.
- Using ITC-T Test Chart #1 with JBIG coding and standard resolution.
- B&W only. PC Fax Receive not available for Mac users.
- For the latest OS compatibility and to download drivers, visit support.brother.com. Printing or scanning via macOS requires the use of AirPrint. Mac printer drivers are not provided. Server 2012/2016/2019 network printing only.
- Maximum capacity based on using 20 lb. paper.
- Print speed may vary depending on size/type of paper used and paper source.
- Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.
- The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.
- Approximate toner cartridge yields in accordance with ISO/IEC 19752 (Letter/A4)
- Approximately 15,000 pages based on 1 page per job (letter/A4 single-sided pages). The number of pages may be affected due to a variety of factors including but not limited to media type and media size.