



SPECIFICATIONS

PANEL SIZE	24.5"
PANEL RESOLUTION	1920 x 1080 (FHD)
REFRESH RATE	120Hz
RESPONSE TIME	1ms (MPRT) / 4ms (GTG)
PANEL TYPE	IPS
BRIGHTNESS (NITS)	300 cd/m2
VIEWING ANGLE	178°(H) / 178°(V)
ASPECT RATIO	16:9
CONTRAST RATIO	1500:1
sRGB	99%
ACTIVE DISPLAY AREA (MM)	543.744(H) x 302.616(V)
PIXEL PITCH (H X V)	0.2832(H) x 0.2802(V)
SURFACE TREATMENT	Anti-glare
DISPLAY COLORS	16.7M
COLOR BIT	8 bits (6 bits + FRC)
HDR SUPPORT	HDR Ready
VIDEO PORTS	1x HDMI™ 2.0 (FHD@120Hz) 1x DisplayPort (1.4a) 1x D-Sub (VGA)
AUDIO PORTS	1x Headphone-out 1x Line-in
KENSINGTON LOCK	Yes
SPEAKER	2x 2W
VESA MOUNTING	100 x 100 mm
POWER TYPE	External Adaptor 12V 2.5A
POWER INPUT	100~240V, 50~60Hz
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
ADJUSTMENT (TILT)	-5° ~ 20°
DIMENSION (W X H X D)	556.89 x 413.91 x 188.2 mm (21.92 x 16.30 x 7.40 inch)
CARTON DIMENSION (W X H X D)	630 x 411 x 142 mm (24.8 x 16.18 x 5.59 inch)
WEIGHT (NW / GW)	2.7 kg (5.95 lbs) / 4.9 kg (10.8 lbs)
CERTIFICATES	CB/CE Energy Star

FEATURES




Perfect Edge

Set-up multi-display immensely with the 4-side edgeless design and enjoy the wider and more immersive view.



120Hz High Refresh Rate

Enjoy the high-quality entertainment with a smoother and flicker-free images.



Broadened Display

View your applications, spreadsheets and more with a perfect screen size for work desk that aligns with the visual's comfort zone.



IPS Grade Panel

Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best while creating your own on-line video



EyesErgo

An eye care solution designed with ergonomics in mind.



Eye-Q Check

Help have self-check eyes & remind to take a rest while using the monitor for a long time.



Built-In Speaker

Built-in speakers allow you to listen clearly without connecting external speakers.



VESA Mountable

To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.

VIDEO INPUT COMPATIBILITY

PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook

* All trademarks and the registered trademarks are the property of their respective owners.

Note

HDMI™: 1920 x 1080 (Up to 120Hz)

DisplayPort: 1920 x 1080 (Up to 120Hz)

D-Sub (VGA): 1920 x 1080 (Up to 60Hz)

HDMI™ CEC Support

*sRGB follow CIE1976 Standard

CONNECTIONS



1. 1x DC-in
2. 1x DisplayPort 1.4a
3. 1x HDMI™ 2.0 (FHD@120Hz)
4. 1x D-Sub (VGA)
5. 1x Line-in
6. 1x Headphone-out
7. 1x Kensington Lock
8. 1x 5-way navigator