

GC515
Capture Dock

X'TRA **GO**



Power and Record Your Handheld and Mobile Devices

Make it simple to play, record, stream and share

Features:



Dock for Various
Handheld/Mobile Device



PC Free



One-Click Recording

4K30

4K30 Capture



Charging, Displaying,
Connecting



USB Power Delivery



Mode Switch
Capture/Playback

Interfaces:



Specifications :

- **Interfaces:** USB-A (USB 3.2 Gen 1) x 2, USB-C x 3, HDMI x 1
- **Video Input (from console):** USB-C DP Alt Mode*
- **Video Output (Pass-through):** HDMI 2.0
- **Audio Output (Pass-through):** HDMI 2.0 / 3.5mm headphone jack (3-pole)
- **Max Pass-Through Resolution:** 2160p60*, 1080p120
- **Max. Recording Resolution:** 2160p30, 1440p60, 1080p120
- **Record Format:** MPEG4 (H.264/H.265)
- **Record File Format:** fMP4 (Fragmented MP4)
- **Supported Resolution:** 2160p, 1440p, 1080p, 720p, 576p, 480p
- **Micro SD Card Capacity (max.):** 1TB (exFAT format), not included
- **Dimensions (W x D x H):** 141 x 99.4 x 37.7 mm (5.55 x 3.91 x 1.48 in.)
- **Weight:** 176 g (6.21 oz.)

Note: X'TRA GO does not support viewing, recording, or streaming of HDCP protected signals.
* When passing through in 2160p60, the maximum recording resolution is capped at 1080p60.
* DisplayPort 1.4 supports up to 4K60 pass-through, while DisplayPort 1.2 only supports up to 4K30 pass-through.

System Requirements:

Windows® 10 x64 / 11 x64 or later

- Desktop:
Intel® Core™ i5-6XXX / AMD Ryzen™ 3 XXX or above
NVIDIA® GTX 1060 / AMD RX 5700 or above
- Laptop:
Intel® Core™ i7-7700HQ+NVIDIA® GeForce®
GTX 1050Ti or above
- 8 GB RAM recommended

macOS 13 / 14 or later

- Apple M1 or 3.6 GHz quad-core Intel Core i7
- Apple M1 or Radeon Pro 555 with 2 GB of VRAM
- 16 GB of 2400 MHz DDR4 memory

GC515 Black	
EAN (WW)	4711289502913
EAN (JP)	4711289502975
EAN (CN)	4711289502937
UPC (WW)	850061690098
GC515 White	
EAN (WW)	4711289502944
EAN (JP)	4711289503019
EAN (CN)	4711289503002
UPC	850061690135

What's in the box :

- X'TRA GO (GC515)
- HDMI 2.0 Cable
- Type-C to Type-A Cable
- Type-C to Type-C PD Cable
- Quick Start Guide

Package Dimensions

- Single Box (L x H x D): 185 x 130.8 x 86 mm
(7.83 x 5.94 x 2.05 in.)
- Carton (L x W x H): 39.5 x 28.0 x 47.5 cm
(16.54 x 12.40 x 11.44 in.)

Shipping Weights

- Single Box : 589 g (1.30 lbs.)
- Carton: 12.6 Kg (27.78 lbs.) (20 pcs per carton)

• Specifications are subject to change without prior notice.
• Please visit the AVerMedia official website at www.avermedia.com for the latest information.