



Poly Savi 7220 Stereo DECT 1920-1930 MHz Top (783Q6AA)

Overview

Move freely, get more done

Help office workers be more productive — it's easier than you think. The Savi 7200 office series of DECT™ wireless headsets for desk phones are crowd pleasers that let workers roam far. Compatible with 800+ desk phones, they're cost effective, too.

Hands-free productivity

Everyone in the office could use more flexibility. They can roam confidently 400 ft /120 m from the headset base with up to 12 hours of talk time. And collaboration is simple, since teams can conference up to four headsets on a single base.

DECT™ Adaptive Power

Optimize range, save power, and maximize office space with the DECT™ adaptive power system. It automatically adjusts wireless signal strength based on distance from the headset base.

Easy integration

Savi 7200 wireless headsets offer instant integration with over 800 analog and IP desk phones from industry leading makers — including a wide range of phones that Poly offers.

Features

Roam farther

Give workers more flexibility and hands-free productivity with a roaming range of up to 120 m / 400 ft from the headset base.^[1]

12 hours talk time

Build more confidence into every call with up to 12 hours of talk time with each charge.

Training made easy

Collaboration is easier with conferencing of up to 4 headsets on one base.

Charge indicator

Provide the peace of mind that comes from knowing headsets are always fully charged with the headset docking charge indicator.

Keep conversations private

Help make every conversation clearer, with a flexible noise-canceling microphone boom that's easy to adjust for optimal placement on every call.

Desk phone compatibility

Take advantage of one-stop shopping, since these headsets are compatible with the wide range of phones that Poly offers.

[1] Sold separately.

Specifications

Audio	Noise and echo reduction
Weight	0.138 kg
Weight	0.304 lb
Package dimensions (W x D x H)	175 x 149 x 55 mm
Package weight	255.67 g
Battery life	>12 hours (talk time)
Special features	UC certified; Noise reduction on outgoing voice audio
UPC number	(ABA) 197029632838; (ABB) 197497581232; (UUU) 197497581249
Manufacturer Warranty	Poly standard two-year limited warranty
What's in the box	Headset (top only)

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Battery type	Rechargeable Li-ion polymer
Button user controls	Power on/off; Call answer/end; Mute; Volume +/-
Cartons per layer	10
Cartons per pallet	80
Certified collaboration software	DECT™
Charge time	3 hours
Color	Black
Connection type	Bluetooth®
Country of origin	Made in Mexico
ECCN	5A992
Ear cushions	PU leather (surface material)
HTS code	8517620090
Headphone type	On-ear (stereo)
Indicator light	On call
Management Software	Plantronics Hub (desktop)
Microphone bandwidth	100 Hz to 7.8 kHz
Microphone type	Bidirectional
Multiple order quantity	20
Package dimensions (W x D x H)	6.88 x 5.86 x 2.16 in
Package weight	0.56 lb
Paired devices	Up to 4
Pallet (layers)	8
Pallet dimensions	40 x 48 x 74.37 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 188.9 cm
Pallet weight	213.01 kg
Pallet weight	469.6 lb
Products per pallet	400
Products per pallet layer	50
Sensitivity (microphone)	-45 +/-3 dB
Signal-to-noise ratio	>60 dB
Speaker bandwidth	80 Hz to 20 kHz
Speaker size	14.2 mm

Supported bluetooth profiles	AVRCP 1.6
UNSPSC code	43191638
Wireless range	Up to 120 m
Wireless range (imperial)	Up to 400 ft

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Oct 15, 2024 5:38 AM UTC+0000