

ViewSonic® PROJECTOR **M1X**

Key Features

- Patented 3-in-1 smart stand for 360° projection
- Side projection capability enabled by H/V keystone correction & 4-corner adjustment
- Powerful sound delivered by built-in Harman Kardon speakers
- Up to 4 hours of battery life with power bank compatibility
- Smart capabilities: Wi-Fi screen mirroring, USB-C streaming, and Bluetooth connectivity



Product Description

The M1X ultra-portable smart LED projector is your gateway to an exhilarating entertainment experience! Weighing less than 1kg and boasting signature ViewSonic M1 series designs, it features a patented 3-in-1 smart stand for a 360-degree customizable projection angle, lens cover, and auto-power-on. With vivid colors on a massive up-to-100" screen and Harman Kardon speakers, immerse yourself indoors or outdoors in unparalleled audio-visual bliss. Its 4-hour battery life, power bank compatibility, and comprehensive H/V keystone correction with 4-corner adjustments make this lightweight projector your ultimate entertainment companion. Enjoy seamless connectivity, including Bluetooth, Wi-Fi, USB-C for direct content display from mobile devices – including the latest iPhone. Alternatively, plug in popular streaming devices like Chromecast, Apple TV, and Fire TV Stick, powered through the M1X's USB-A port.

SPECIFICATION

Native Resolution:	854x480
Brightness:	360 (LED Lumens)
Contrast Ratio:	120000:1
Display Color:	1.07 Billion Colors
Light Source Type:	LED
Light Source Life (hours) with Normal Mode:	60000
Lens:	F=1.7, f=5.5mm
Projection Offset:	100%+/-5%
Throw Ratio:	1.2
Optical Zoom:	Fixed
Image Size:	24"-100"
Throw Distance:	0.64m-2.66m (38"@1m)
Keystone:	H: +/-40° , V: +/-40°
Audible Noise (Normal):	26dB
Audible Noise (Eco):	25dB
Local Storage:	Total 16GB (12GB available storage)
Input Lag:	73ms
Resolution Support:	VGA(640 x 480) to FullHD(1920 x 1080)
HDTV Compatibility:	480i, 480p, 576i, 576p, 720p, 1080i, 1080p
Horizontal Frequency:	15K-102KHz
Vertical Scan Rate:	23-120Hz

INPUT

HDMI:	1 (HDMI 1.4/ HDCP 1.4)
USB Type C:	1 (5V/1.5A)
Audio-in (Bluetooth):	1 (BT4.2)
USB Type A:	1 (USB2.0 Reader)
Wifi Input:	1 (5Gn)

OUTPUT

Audio-out (3.5mm):	1
Audio-out (Bluetooth):	1 (BT4.2)
Speaker:	3W Cube x2 (Full range x2)
USB Type A (Power):	1 (USB2.0 - 5V/1.5A, share with USB A Input)

CONTROL

USB Type A (Services):	1 (share with USB A Input)
------------------------	-------------------------------

OTHERS

Power Supply Voltage:	138 mm Power adaptor: Input: 100~240V Output: 19VDC / 3.26A
Power Consumption:	Battery: 12000mAh(4000mAh 3.7Vx3) (2.5hrs@Normal, 3hrs@Eco)
Operating Temperature:	Normal: 35W Standby: <0.5W
Carton:	Color
Net Weight:	0.8kg
Gross Weight:	1.87kg
Dimensions (WxDxH) with Adjustment Foot:	166x138x54mm
Packing Dimensions:	220x190x125mm
OSD Language:	English, French, Spanish, Thai, Korean, German, Italian, Russian, Swedish, Dutch, Polish, Czech, T-Chinese, S- Chinese, Japanese, Turkish, Portuguese, Finnish, Indonesian, Hindi, Arabic, Vietnamese, Greek, Total 23 languages
User Guide Language:	English, S-Chinese, T- Chinese, Indonesian, Finish, French, German, Italian, Japanese, Korean, Polish, Portuguese, Russian, Spanish, Swedish, Turkish, Arabic, Czech, Thai, Vietnamese, total 20 languages

STANDARD ACCESSORY

Power Cord:	1
USB-C Cable:	1 (1m)
Remote Control:	1 (BT w/o backlit)
QSG:	Yes
Warranty Card:	Yes (CN & JP)
Sleeve Bag:	Yes