

# ASUS VT169HE

## 10-point Multi-touch Monitor




*\*The final product outlook may change, depending on the panel design.*

### Key Features



Low Blue Light & Flicker Free

 Capacitive 10-point multi-touch capability ensures smooth and intuitive touch experience.



Features HDMI and VGA inputs for multimedia usage



Full HD panel(1920 x 1080 resolution ) and IPS technology deliver stunning color reproduction.



Ultra-low Blue Light

Four levels of Blue Light Filter help users effectively reduce harmful blue light from the screen by tasks.



Flicker-free

ASUS Flicker-Free Technology clears out the distracting flicker and brings viewing comfort.



With the best compatibility and reliability, VT169HE ensures outstanding accuracy and effortless control in Win. 10/11.



Tilt

-5° ~30° tilt angle, flexible enough for scenarios as a extend monito



Wall Mountable

Compatible with VESA Wall Mount Standard (75 x 75 mm).



Complied with ENERGY STAR®, TCO, EPEAT Silver(by country) for environmental protection & energy saving



# Specification

Display	Panel Size(diagonal)	15.6" (39.6cm)
	Display Viewing Area(HxV)	344.16 x 193.59 mm
	Panel Type	IPS
	Display Surface	Non-Glare
	True Resolution	1920x1080(Full HD)
	Pixel Pitch	0.179mm
	Brightness (typical)	220cd/m <sup>2</sup>
	Contrast Ratio (typical)	1000:1
	ASUS Smart Contrast Ratio(ASCR)	100,000,000:1
	Viewing Angle (CR ≥ 10)	170°/170°
	Display Colors	262K
	Response Time	5ms(GTG)
	Touch Screen	Yes (PCAP Touch)
	Flicker-free	Yes
Video Features	Splendid Video Intelligence Tech.	Yes
	Skin-Tone Selection	Yes
	Color Temperature Selection	Yes(4 modes)
	HDCP	Yes, v1.4
	QuickFit	Yes
	Blue Light Filter	Yes
Input/ Output		HDMI(v1.4) x 1, VGA x 1, USB-B x 1(for touch signal only)
Power	Power Consumption	7.38W*
	Power Saving/Off Mode	< 0.5W/ <0.3W
	Voltage	Voltage : 100-240V, 50/60Hz
Mechanical Design	Chassis Colors	Black
	Tilt(angle)	Yes (+30° ~ -5°)
	VESA Wall Mounting	75x75mm
Security	Kensington lock	Yes
Dimension	Phys. Dimension (WxHxD)	37.78 x 28.07 x 18.94 cm (14.87" x 11.05" x 7.46") (with stand), 37.78 x 23.59 x 4.40 cm(14.87" x 9.29" x 1.73") (without stand)
	Box Dimension (WxHxD)	43.4 x 35.0 x 12.2 cm(17.09" x 13.78" x 4.80")
Weight		Gross weight: 2.93Kg(6.46 lbs), Net weight: 1.46Kg(3.22 lbs)
Accessories		HDMI cable(optional), VGA cable(optional), Power cord, USB Type-B to A cable, Warranty card, Quick start guide
Compliance Standards		Energy Star®, FCC, cTUVus, ICES-003, CB, CE, ErP, WEEE, ISO 9241-307, UkrSEPRO, Ukraine Energy, CU, CCC, CEL, BSMI, RCM, AU MEPS, VCCI, PSE, PC Recycle, J-MOSS, KC, KCC, SDoC, KMEPS, TCO, RoHS, NOM, CEC, WHQL (Windows 10/11), EPEAT Silver(by country) **

\*measuring a screen brightness of 200 nits without audio/ USB connection

\*\*EPEAT registered where applicable. EPEAT registration varies by country. See [www.epeat.net](http://www.epeat.net) for registration status by country.

\*\*\*All specifications are subject to change without notice.