




# The essentials to enhance productivity

Dell 24 Monitor | **E2425H**  
Dell 24 Monitor | **E2425HS**

The world's # 1 monitor company\*



## Get the essentials to enhance productivity with these affordable 23.8-inch monitors certified by TÜV Rheinland® for 3-star eye comfort.

### Improved visual comfort

These monitors come with TÜV Rheinland® 3-star eye comfort certification<sup>1</sup> — the latest industry standard for eye comfort to help reduce signs of eye fatigue.

Benefit from ComfortView Plus, a built-in feature engineered to minimize harmful blue light emissions without compromising color.

### Functional, space-saving design

Get enhanced views in FHD resolution with 3000:1 contrast ratio for deeper blacks, brighter whites and vivid color. The improved design with slim bezels, small footprint and cable management offers a clutter-free set up and maximizes valuable desk space.

Height adjustability and built-in speakers are available on the E2425HS model for improved everyday ergonomics and productivity.

### Next-level productivity

Boost efficiency and productivity with Dell Display Manager 2.0 that lets you customize your monitor settings, organize your screen using Easy Arrange and simplify management.

Conveniently connect to current and legacy systems via VGA, DisplayPort and HDMI<sup>2</sup> ports. Make your workspace your own with VESA-compatible mounts and stands.

Experience reduced downtime with the 3-year Advanced Exchange Service<sup>3</sup> so that if a replacement becomes necessary, it will be shipped to you the next business day during your 3-year Limited Hardware Warranty.<sup>4</sup>

<sup>1</sup> TÜV Rheinland certified - Low Blue Light Hardware Solution and Flicker Free (ID 0217010014).

<sup>2</sup> HDMI is available with Dell 24 Monitor E2425HS only.

<sup>3</sup> Dell will send you a replacement monitor the next business day in most cases, if deemed necessary after phone/online diagnosis. Shipping times may vary by location and for monitors 55" and above. Fee charged for failure to return defective unit. See [dell.com/servicecontracts/global](http://dell.com/servicecontracts/global).

<sup>4</sup> For a copy of the Limited Hardware Warranty, write to Dell USA LP, Attention: Warranties One Dell Way, Round Rock, TX 78682 or see [dell.com/warranty](http://dell.com/warranty) for details.



**Improved visual comfort**

Experience firsthand benefits with ComfortView Plus, engineered to minimize harmful blue light emissions without compromising color. Coupled with a 75 Hz refresh rate, this monitor delivers a TÜV Rheinland 3-star<sup>1</sup> certified viewing experience.



**See your work clearly**

Work in FHD clarity and get consistent views across a wide 178°/178° viewing angle. Experience deeper blacks, brighter whites and vivid color with 3000:1 contrast ratio.



**Multi-task with ease**

Boost efficiency with Dell Display Manager that lets you organize multiple apps on your screen.



**Easy to connect**

Connect to current and legacy systems via VGA, DisplayPort and HDMI<sup>2</sup> ports.


**World's number 1 monitor company\***

We deliver world-class monitors that have gone through rigorous development processes and stringent tests to ensure dependable performance. Get peace of mind with unmatched warranty and support options. Being environmentally forward in thinking, our monitors adhere to environment standards and are made with sustainable materials.

\* Dell monitors are #1 Worldwide for 10 years! Source: IDC Worldwide Quarterly PC Monitor Tracker, Q1 2024. From 2014 to 2023. CLM-011283

1 TÜV Rheinland certified - Low Blue Light Hardware Solution and Flicker Free (ID 0217010014).

2 HDMI is available with Dell 24 Monitor E2425HS only



# Environmentally-forward thinking

## Material innovation

These monitors have been thoughtfully crafted with 85% post-consumer plastic and closed-loop ITE-derived plastic.<sup>1</sup> Using recycled materials helps conserve natural resources and contributes to a lower environmental footprint.

## Excellence in environmental standards

These monitors are certified ENERGY STAR®, carry the TCO Certified Edge designation, and are registered EPEAT Gold with Climate+.<sup>2</sup> With Climate+, these monitors meet industry best practices around decarbonization.<sup>2</sup>

## Low impact packaging

Ships in a box made with 100% renewable materials that is recyclable<sup>3</sup> to contribute to a lower environmental footprint.

<sup>1</sup> Based on internal analysis, June 2024. Designed with up to 35% post-consumer recycled plastic and 50% closed-loop IT equipment derived plastic. Percentage break up may vary by model.

<sup>2</sup> EPEAT Climate+ Designations achieved in all applicable countries. EPEAT registered where applicable. EPEAT registration varies by country. See [www.epeat.net](http://www.epeat.net) for registration status and tier levels by country.

<sup>3</sup> Applies to all Dell monitors launched since 2023. Made from FSC mix sources which is a mix of material from FSC certified forests, recycled content and/or FSC controlled wood. Based on internal analysis, August 2023.

# All day comfort



Get a seamless viewing experience and focus on your task with slim bezels and small footprint.



E2425HS

## Dell 24 Monitor – E2425H



### Connect with ease

Connect to current and legacy systems via VGA and DisplayPort interfaces.

## Dell 24 Monitor – E2425HS



The image shows the E2225HS

### Work comfortably

The height adjustable stand<sup>2</sup> allows you to tilt and swivel your monitor however you wish for improved everyday ergonomics and productivity.



### Conveniently connect

Connect to current and legacy systems via VGA, DisplayPort and HDMI<sup>1</sup> interfaces.



The image shows the E2225HS

1 HDMI is available with Dell 24 Monitor E2425HS only.  
2 Height adjustable stand is Dell 24 Monitor E2425HS only.



# Dell Display Manager

Boost efficiency with features that let you organize your screen, customize your monitor settings and simplify management.

## Multitask efficiently

Organize your screen with Easy Arrange and save profiles with Easy Arrange Memory.

## Easy management

Manage your fleet of monitors with remote management features that are automatic, and compatible with several tools.<sup>1</sup>

## Customize to your convenience

Quickly access your favorite features and functions with the menu launcher and hot keys.

[Download Dell Display Manager](#)

<sup>1</sup> Tools including SCCM/InTune and Command Line Interface scripts.

# Ports & Slots

## E2425H



## E2425HS



- 1 Security lock slot<sup>1</sup>
- 2 Power connector
- 3 DisplayPort
- 4 HDMI (available with the Dell E2425HS monitor only)
- 5 VGA
- 6 Built-in speakers

### Cables included

- Power cable
- DisplayPort cable with the Dell E2425H monitor only
- HDMI cable with the Dell E2425HS monitor only

<sup>1</sup> Based on Kensington Security Slot™

FEATURE	TECHNICAL SPECIFICATION	TECHNICAL SPECIFICATION
MODEL	Dell 24 Monitor - E2425H	Dell 24 Monitor - E2425HS
DIAGONAL VIEWING SIZE	604.70 mm (23.81 in.)	604.70 mm (23.81 in.)
PANEL TYPE	Vertical Alignment (VA) Technology	Vertical Alignment (VA) Technology
MAXIMUM PRESET RESOLUTION AND REFRESH RATE	1920 x 1080 up to 75 Hz	1920 x 1080 up to 75 Hz
VIEWING ANGLE	178° vertical 178° horizontal	178° vertical 178° horizontal
PIXEL PITCH	0.2745 mm x 0.2745 mm	0.2745 mm x 0.2745 mm
PIXEL PER INCH (PPI)	93	93
CONTRAST RATIO	3000:1 (typical)	3000:1 (typical)
ASPECT RATIO	16:9	16:9
BACKLIGHT TECHNOLOGY	LED Edgelight System	LED Edgelight System
BRIGHTNESS	250 cd/m <sup>2</sup> (typical)	250 cd/m <sup>2</sup> (typical)
RESPONSE TIME	<ul style="list-style-type: none"> <li>• 5 milliseconds (gray to gray - fast mode)</li> <li>• 8 milliseconds (gray to gray - normal mode)</li> </ul>	<ul style="list-style-type: none"> <li>• 5 milliseconds (gray to gray - fast mode)</li> <li>• 8 milliseconds (gray to gray - normal mode)</li> </ul>
COLOR GAMUT	NTSC minimum 72% (CIE 1931), NTSC minimum 83% (CIE 1976)	NTSC minimum 72% (CIE 1931), NTSC minimum 83% (CIE 1976)
COLOR DEPTH	16.7 Million colors	16.7 Million colors
TÜV RHEINLAND EYE COMFORT	3-Stars	3-Stars
CONNECTIVITY	<ul style="list-style-type: none"> <li>• One DisplayPort 1.2 (HDCP 1.4) (supports up to FHD 1920 x 1080 75 Hz)</li> <li>• One VGA connector</li> </ul>	<ul style="list-style-type: none"> <li>• One HDMI (HDCP 1.4) (supports up to FHD 1920 x 1080 75 Hz as per specified in HDMI 1.4)</li> <li>• One DisplayPort 1.2 (HDCP 1.4) (supports up to FHD 1920 x 1080 75 Hz)</li> <li>• One VGA connector</li> </ul>
ADJUSTABILITY	Tilt -5°/+21°	<ul style="list-style-type: none"> <li>• Height adjustable stand</li> <li>• Height adjustment up to 130 mm</li> <li>• Tilt -5°/+21°</li> <li>• Swivel -173°/+173°</li> </ul>
DISPLAY SCREEN COATING	Anti-glare with hard-coating 3H	Anti-glare with hard-coating 3H
SOFTWARE COMPATIBILITY	Dell Display Manager (DDM) for Windows operating system	Dell Display Manager (DDM) for Windows operating system
VOLTAGE REQUIRED	100 VAC to 240 VAC / 50 Hz or 60 Hz ± 3 Hz / 0.7 A (typical)	100 VAC to 240 VAC / 50 Hz or 60 Hz ± 3 Hz / 0.7 A (typical)
POWER CONSUMPTION	<ul style="list-style-type: none"> <li>• 0.3 W (Off mode)<sup>1</sup></li> <li>• 0.3 W (Standby mode)<sup>1</sup></li> <li>• 13.3 W (On mode)<sup>1</sup></li> <li>• 22 W (Max)<sup>2</sup></li> <li>• 13.4 W (Pon)<sup>3</sup></li> <li>• 42.8 kWh (TEC)<sup>3</sup></li> </ul>	<ul style="list-style-type: none"> <li>• 0.3 W (Off mode)<sup>1</sup></li> <li>• 0.3 W (Standby mode)<sup>1</sup></li> <li>• 13.0 W (On mode)<sup>1</sup></li> <li>• 25 W (Max)<sup>2</sup></li> <li>• 12.7 W (Pon)<sup>3</sup></li> <li>• 40.6 kWh (TEC)<sup>3</sup></li> </ul>
HEIGHT WITH STAND	420.35 mm (16.55 in.)	(Compressed ~ Extended) 382.56 mm (15.06 in.) - 512.07 mm (20.16 in.)
WIDTH WITH STAND	552.64 mm (21.76 in.)	538.64 mm (21.21 in.)
DEPTH WITH STAND	171.00 mm (6.73 in.)	209.46 mm (8.25 in.)
HEIGHT WITHOUT STAND	331.61 mm (13.06 in.)	324.21 mm (12.76 in.)
WIDTH WITHOUT STAND	552.64 mm (21.76 in.)	538.64 mm (21.21 in.)
DEPTH WITHOUT STAND	49.68 mm (1.96 in.)	48.90 mm (1.93 in.)

<sup>1</sup> As defined in EU 2019/2021 and EU 2019/2013.

<sup>2</sup> Max brightness and contrast setting.

<sup>3</sup> Pon: Power consumption of On mode as defined in Energy Star 8.0 version. TEC: Total energy consumption in kWh as defined in Energy Star 8.0 version.



FEATURE	TECHNICAL SPECIFICATION	TECHNICAL SPECIFICATION
MODEL	Dell 24 Monitor - E2425H	Dell 24 Monitor - E2425HS
WEIGHT (PANEL ONLY - FOR VESA MOUNT)	3.16 kg (6.96 lb)	2.88 kg (6.35 lb)
WEIGHT (WITH STAND ASSEMBLY AND CABLES)	3.93 kg (8.66 lb)	4.57 kg (10.07 lb)
WEIGHT (WITH PACKAGING)	5.47 kg (12.06 lb)	6.01 kg (13.25 lb)
FLAT PANEL MOUNT INTERFACE	VESA (100 mm x 100 mm)	VESA (100 mm x 100 mm)
BUILT-IN DEVICES	Not Applicable	Speaker 2 x 1W
SECURITY	Security lock slot (cable lock sold separately)	Security lock slot (cable lock sold separately)
COMPLIANT STANDARDS	<ul style="list-style-type: none"> <li>ENERGY STAR 8.0</li> <li>EPEAT Gold with Climate+</li> <li>TCO Certified and TCO Certified Edge</li> <li>RoHS Compliant</li> <li>Product Safety, EMC and Environmental Datasheets</li> <li>Dell Regulatory Compliance Home Page</li> <li>Dell and the Environment</li> <li>TÜV Rheinland Eye Comfort 3-Stars</li> <li>BFR/PVC reduce monitor. (The circuit boards are made from BFR/PVC-free laminates.)</li> <li>Meets NFPA 99 leakage current requirements.</li> <li>Arsenic-Free glass and Mercury-Free for the panel only.</li> </ul>	<ul style="list-style-type: none"> <li>ENERGY STAR 8.0</li> <li>EPEAT Gold with Climate+</li> <li>TCO Certified and TCO Certified Edge</li> <li>RoHS Compliant</li> <li>Product Safety, EMC and Environmental Datasheets</li> <li>Dell Regulatory Compliance Home Page</li> <li>Dell and the Environment</li> <li>TÜV Rheinland Eye Comfort 3-Stars</li> <li>BFR/PVC reduce monitor. (The circuit boards are made from BFR/PVC-free laminates.)</li> <li>Meets NFPA 99 leakage current requirements.</li> <li>Arsenic-Free glass and Mercury-Free for the panel only.</li> </ul>
TEMPERATURE RANGE	<ul style="list-style-type: none"> <li>Operating: 0°C to 40°C (32°F to 104°F)</li> <li>Non-operating: -20°C to 60°C (-4°F to 140°F)</li> </ul>	<ul style="list-style-type: none"> <li>Operating: 0°C to 40°C (32°F to 104°F)</li> <li>Non-operating: -20°C to 60°C (-4°F to 140°F)</li> </ul>
HUMIDITY RANGE	<ul style="list-style-type: none"> <li>Operating: 10% to 80% (non-condensing)</li> <li>Non-Operating: 5% to 90% (non-condensing)</li> </ul>	<ul style="list-style-type: none"> <li>Operating: 10% to 80% (non-condensing)</li> <li>Non-Operating: 5% to 90% (non-condensing)</li> </ul>
ALTITUDE	<ul style="list-style-type: none"> <li>Operating: 5,000 m (16,400 ft) maximum</li> <li>Non-operating: 12,191 m (40,000 ft) maximum</li> </ul>	<ul style="list-style-type: none"> <li>Operating: 5,000 m (16,400 ft) maximum</li> <li>Non-operating: 12,191 m (40,000 ft) maximum</li> </ul>
WHAT'S INCLUDED	<ul style="list-style-type: none"> <li>Monitor with stand</li> <li>Power cable</li> <li>One DisplayPort-DisplayPort cable - 1.8 m</li> <li>One VGA cable - 1.5 m (EMEA/Japan)</li> <li>Quick Start guide</li> <li>Safety Information</li> </ul>	<ul style="list-style-type: none"> <li>Monitor with stand</li> <li>Power cable</li> <li>One HDMI cable - 1.8 m</li> <li>One VGA cable - 1.5 m (Japan)</li> <li>Quick Start guide</li> <li>Safety Information</li> </ul>
STANDARD SERVICE PLAN	3-year Advanced Exchange Service <sup>1</sup> and 3-year Limited Hardware Warranty <sup>2</sup>	3-year Advanced Exchange Service <sup>1</sup> and 3-year Limited Hardware Warranty <sup>2</sup>
OPTIONAL SUPPORT SERVICES	Dell ProSupport for monitors <sup>3</sup> for 24x7 specialized technical phone support <sup>4</sup>	Dell ProSupport for monitors <sup>3</sup> for 24x7 specialized technical phone support <sup>4</sup>

1 Advanced Exchange Service: Dell will send you a replacement monitor the next business day in most cases, if deemed necessary after phone/online diagnosis. Shipping times may vary by location and for monitors 55" and above. Fee charged for failure to return defective unit. See [dell.com/servicecontracts/global](http://dell.com/servicecontracts/global) for details.

2 For a copy of the Limited Hardware Warranty, write to Dell USA LP, Attention: Warranties One Dell Way, Round Rock, TX 78682 or see [dell.com/warranty](http://dell.com/warranty) for details.

3 Availability varies, please visit [www.dell.com/support](http://www.dell.com/support) for details.

4 In some countries, hours for in-region support may vary. Support after local business hours may be provided in a language other than the local language.

# Steadfast reliability

As the No. 1 monitor company worldwide\*, we take pride in our unyielding commitment to quality and the utmost in customer satisfaction.



## Advanced Exchange Service

These monitors come with a 3-year Advanced Exchange Service<sup>1</sup> so that if a replacement becomes necessary, it will be shipped to you the next business day during your 3-year Limited Hardware Warranty.<sup>2</sup>

## ProSupport

Upgrade to 24x7 specialized technical phone support with the Dell ProSupport option.<sup>3</sup>

## Optimal integration

Dell Monitors are designed to work seamlessly with our PC and accessories. Visit the [support page](#) to find out more.

\* Dell monitors are #1 Worldwide for 10 years! Source: IDC Worldwide Quarterly PC Monitor Tracker, Q1 2024. From 2014 to 2023. CLM-011283.

- <sup>1</sup> Advanced Exchange: Dell will send you a replacement monitor the next business day in most cases, if deemed necessary after phone/online diagnosis. Shipping times may vary by location and for monitors 55" and above. Fee charged for failure to return defective unit. See [dell.com/servicecontracts/global](#).
- <sup>2</sup> For a copy of the Limited Hardware Warranty, write to Dell USA LP, Attention: Warranties One Dell Way, Round Rock, TX 78682 or see [dell.com/warranty](#) for details.
- <sup>3</sup> Availability varies, please visit [www.dell.com/support](#) for details. In some countries, hours for in-region support may vary. Support after local business hours may be provided in a language other than the local language.

Technical specifications subject to change without prior notice. Product availability varies by country. Please contact your Dell representative for more information.

© 2024 Dell Inc. or its subsidiaries. All Rights Reserved. Dell Technologies, Dell, EMC, Dell EMC and other trademarks are trademarks of Dell Inc. or its subsidiaries. Other trademarks may be trademarks of their respective owners. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. Thunderbolt and the Thunderbolt logo are trademarks of Intel Corporation in the U.S. and/or other countries.