

PERFORMANCE

Display Size

23.8"

View Area

527.0x296.5 mm

Panel

In-Plane Switching

Backlight

WLED

Aspect Ratio

16:9

Resolution

1920x1080

Pixel Pitch

0.2745x0.2745 mm

Dot / Pixel Per Inch

93 dpi

View Angle (H / V)

178° / 178°

Response Time

1ms (MPRT@100Hz) / 4ms (Extreme Mode) / 6ms (Normal Mode) / 14ms (Off Mode)

Color Support

16.7 Million

Refresh Rate

48Hz - 100Hz

Brightness

250 cd/m²

Contrast Ratio

1500:1

Color Gamut

99% sRGB

Screen Surface Treatment

Anti-glare

Curvature

None

Camera

None

Microphone

None

Speakers

3Wx2

Power Consumption (Typical / Maximum)

14W / 28W

Power Adapter

Integrated

Touchscreen

None

Smart System

None

DESIGN

Stand

Tilt

Case Color

Cloud Grey

Side Bezel Width

2.0 mm

Mounting

Supports VESA mount 100mm

ThinkCentre® M Series Support

None

Dimensions (WxDxH)^[1]

- Lowest Position | 539.4 x 182.9 x 433.8 mm (21.24 x 7.20 x 17.08 inches)
- Highest Position | 539.4 x 182.9 x 433.8 mm (21.24 x 7.20 x 17.08 inches)
- Head Only | 539.4 x 41.0 x 315.2 mm (21.24 x 1.61 x 12.41 inches)

Packaging Dimensions (WxDxH)

609.0 x 125.0 x 398.0 mm (23.98 x 4.92 x 15.67 inches)

Weight^[2]

- Monitor With Stand | 3.84 kg (8.47 lbs)
- Monitor Head Only | 3.01 kg (6.83 lbs)

Packaging Weight

5.82 kg (12.83 lbs)

CONNECTIVITY

USB Port

None

Video Connector

1x HDMI® 1.4, 1x VGA

Network Connectivity

None

SERVICE

Base Warranty

1-year

CERTIFICATIONS

Environmental Certification

RoHS, EU Energy Efficiency Level (Level-D), EPEAT™ Gold, ENERGY STAR® Certified

Ergonomic Certification

TÜV Low Blue Light (Hardware solution), TÜV Low Blue Light, TÜV Rheinland® Eye Comfort, Eyesafe® Display 2.0

Sync Technology

None

Special Features

- Lenovo® Artery (Lenovo® Accessories and Display Manager) Support
Lenovo® Artery supports Windows® 10 & 11, Mac OS, and Windows® On Arm (functions vary across systems).
Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center.
- Natural Low Blue Light

SOFTWARE

Operating System

Support Windows® 10, Windows® 11

ACCESSORIES

Video Cables

HDMI® cable

MODEL

Announce Date : 2024-07-03
EAN / UPC : 0197530466953 / 197530466953 / None
/ JAN



Product image is a sample, it may not match the real color of this model

Note:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to <https://psref.lenovo.com/Detail/2612?M=67BCKCC6US>

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkCentre Tiny VESA Mount II

4XFON03161

The ThinkCentre Tiny VESA Mount II is a unique design specific to house the Tiny PC while featuring the universal VESA mount configuration. The VESA standard enables this mount to attach to anything that is VESA comp...



NanoSaver Essential Cable Lock from Lenovo

4XE1F30276

The Lenovo Security Cable Lock allows customers to manage physical security access within the enterprise, offices, schools, libraries, or in other public spaces. Cable locks help reduce theft, and increase physical as...

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference