



## SPECIFICATIONS

<b>PANEL SIZE</b>	21.45"
<b>PANEL RESOLUTION</b>	1920 x 1080 (FHD)
<b>REFRESH RATE</b>	100Hz
<b>RESPONSE TIME</b>	1ms (MPRT) / 4ms (GtG)
<b>PANEL TYPE</b>	VA
<b>BRIGHTNESS (NITS)</b>	250 cd/m <sup>2</sup>
<b>VIEWING ANGLE</b>	178°(H) / 178°(V)
<b>ASPECT RATIO</b>	16:9
<b>CONTRAST RATIO</b>	3000:1
<b>sRGB</b>	99% (CIE 1976)
<b>ACTIVE DISPLAY AREA (MM)</b>	478.656 (H) x 260.28 (V)
<b>PIXEL PITCH (H X V)</b>	0.2493 (H) x 0.241 (V)
<b>SURFACE TREATMENT</b>	Anti-glare
<b>DISPLAY COLORS</b>	16.7M
<b>COLOR BIT</b>	8 bits (6 bits + FRC)
<b>VIDEO PORTS</b>	1x HDMI™ 1.4b (FHD@100Hz) 1x DisplayPort 1.2a
<b>AUDIO PORTS</b>	1x Headphone-out
<b>KENSINGTON LOCK</b>	Yes
<b>SPEAKER</b>	NA
<b>VESA MOUNTING</b>	75 x 75 mm
<b>POWER TYPE</b>	External Adaptor 12V 2.5A
<b>POWER INPUT</b>	100~240V, 50~60Hz
<b>DYNAMIC REFRESH RATE TECHNOLOGY</b>	Adaptive-Sync
<b>ADJUSTMENT (TILT)</b>	-5° ~ 20°
<b>DIMENSION (W X H X D)</b>	494.7 x 385.5 x 182 mm (19.48 x 15.18 x 7.17 inch)
<b>CARTON DIMENSION (W X H X D)</b>	558 x 367 x 116 mm (21.97 x 14.5 x 4.6 inch)
<b>WEIGHT (NW / GW)</b>	2.4 kg (5.29 lbs) / 4.1 kg (9.04 lbs)
<b>CERTIFICATES</b>	CB/CE Energy Star
<b>VIDEO INPUT COMPATIBILITY</b>	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook *All trademarks and the registered trademarks are the property of their respective owners.

## FEATURES

- 100Hz High Refresh Rate**  
 Experience smooth gaming with a blazing fast 100Hz refresh rate, that gives you the upperhand in fast moving games.
- EyesErgo**  
 An eye care solution designed with ergonomics in mind.
- Less Blue Light**  
 Effectively reduce blue light which could cause serious long-term damage to your eyes.
- Eye-Q Check**  
 Help have self-check eyes & remind to take a rest while using the monitor for a long time.
- VESA Mountable**  
 To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.
- Anti-Flicker technology**  
 MSI Anti-Flicker technology provides a very comfortable viewing experience by reducing the amount of screen flicker.

### Note

HDMI™: 1920 x 1080 (Up to 100Hz)  
D-Sub (VGA): 1920 x 1080 (Up to 60Hz)  
HDMI™ CEC Support  
\*sRGB follow CIE1976 Standard

## CONNECTIONS



1. 1x DC-in
2. 1x HDMI™ (1.4b)
3. 1x D-Sub (VGA)
4. 1x Headphone-out
5. 1x Kensington Lock
6. 1x OSD Button