



## SPECIFICATIONS

<b>PANEL SIZE</b>	27"
<b>PANEL RESOLUTION</b>	1920 x 1080 (FHD)
<b>REFRESH RATE</b>	120Hz
<b>RESPONSE TIME</b>	1ms (MPRT) / 4ms (GtG)
<b>PANEL TYPE</b>	IPS
<b>BRIGHTNESS (NITS)</b>	300 cd/m <sup>2</sup>
<b>VIEWING ANGLE</b>	178°(H) / 178°(V)
<b>ASPECT RATIO</b>	16:9
<b>CONTRAST RATIO</b>	1500:1
<b>sRGB</b>	116%
<b>ACTIVE DISPLAY AREA (MM)</b>	597.888 (H) x 336.312 (V)
<b>PIXEL PITCH (H X V)</b>	0.3114 (H) x 0.3114 (V)
<b>SURFACE TREATMENT</b>	Anti-glare
<b>DISPLAY COLORS</b>	16.7M
<b>COLOR BIT</b>	8 bits (6 bits + FRC)
<b>HDR SUPPORT</b>	HDR Ready
<b>VIDEO PORTS</b>	1x HDMI™ 1.4b (FHD@120Hz) 1x DisplayPort 1.2a 1x D-Sub (VGA)
<b>AUDIO PORTS</b>	1x Headphone-out
<b>KENSINGTON LOCK</b>	Yes
<b>SPEAKER</b>	2x 2W
<b>VESA MOUNTING</b>	100 x 100 mm
<b>POWER TYPE</b>	Internal Power Board
<b>POWER INPUT</b>	100~240V, 50~60Hz
<b>DYNAMIC REFRESH RATE TECHNOLOGY</b>	Adaptive-Sync
<b>ADJUSTMENT (TILT)</b>	-5° ~ 20°
<b>DIMENSION (W X H X D)</b>	612.18 x 431.79 x 206.8 mm (24.1 x 17 x 8.14 inch)
<b>CARTON DIMENSION (W X H X D)</b>	688 x 505 x 128 mm (27.09 x 19.88 x 5.04 inch)
<b>WEIGHT (NW / GW)</b>	3.82 kg (8.42 lbs) / 3.8 kg (8.4 lbs)
<b>CERTIFICATES</b>	CB/CE Energy Star
<b>VIDEO INPUT COMPATIBILITY</b>	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook *All trademarks and the registered trademarks are the property of their respective owners.

## FEATURES



### IPS Panel with Wide Viewing Angle

Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best.



### Perfect Edge

Set-up multi-display immensely with the 4-side edgeless design and enjoy the wider and more immersive view.



### 120Hz High Refresh Rate

Enjoy the high-quality entertainment with a smoother and flicker-free images.



### EyesErgo

An eye care solution designed with ergonomics in mind.



### Eye-Q Check

Help have self-check eyes & remind to take a rest while using the monitor for a long time.



### Built-In Speaker

Built-in speakers allow you to listen clearly without connecting external speakers.



### Accessory Slot Design

Enjoy a clean table with the accessory slot design where you can put MSI Pen or Smartphone, and you will not miss important messages anymore.



### VESA Mountable

To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.

**Note**

HDMI™: 1920 x 1080 (Up to 120Hz)  
DisplayPort: 1920 x 1080 (Up to 120Hz)  
D-Sub (VGA): 1920 x 1080 (Up to 60Hz)  
HDMI™ CEC Support  
\*sRGB follow CIE1976 Standard

**CONNECTIONS**

1. 1x AC-in
2. 1x Headphone-out
3. 1x DisplayPort 1.2a
4. 1x HDMI 1.4b (FHD@120Hz)
5. 1x D-Sub (VGA)
6. 1x Kensington Lock
7. 1x 5-way Navigator