



Modern 13 F1M

MODERN 13 F1MG-010US

Specification

Manufacturer Part #	MOD1314F1010
OS	Windows 11 Pro
CPU	Intel® Core™ 7 - 150U
CPU Speed	1.8 - 5.4 GHz
Chipset	-
Color	Platinum Gray
Screen Size	13.3" FHD 60Hz 45%NTSC IPS-Level
Resolution	(1920x1080) 16:9
GPU	Intel® Graphics
Video Memory	-
Keyboard	White backlight keyboard with Copilot Key
Speaker	2x Speakers 2W
Memory	16GB (8GB*2) DDR4 3200MHz
HDD Capacity	1TB NVMe SSD
HDD Interface	NVMe
TPM	-
LAN	RJ-45
WLAN	Intel WiFi 6E AX211 (2x2)
Bluetooth	BT 5.3
Card Reader	Micro SD
Webcam	720p HD Webcam
USB	2x USB 3.2 Gen 1
Type-C Port	1x USB 3.2 Gen 2 Type C
Video Port	HDMI 1.4 (4K @ 30Hz)
Audio Port	Mic-in/Headphone-out Combo
AC Power Adaptor	65W [DC-in]
Battery Pack	3 cell (45.6Whr) Li-Polymer
Dimension	12.14" x 8.29" x 0.78"
Weight	2.93 lbs
Manufacturer Warranty	3 year Limited warranty (Include 1 Year Global)